




LOC		DIST		REV		DATE		APD	
G	14	P	F	ZONE	LTR	DESCRIPTION	DATE	APD	18 DAP
				F	REV, RDRW, & SM	PKG PER 0720-0040-93	4-8-93		



AMP WIRE RANGE		UL E13288 Listed	
22-16 AWG	SOLID OR STRANDED	22-16 AWG	SOLID OR STRANDED
LR7189 Certified		MILITARY P/N AND CLASS	
22-16 AWG SOLID OR STRANDED		NOT APPLICABLE	



STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16

100	LOOSE PIECE BOX	8-320749-1
5000	ON TAPE	2-320749-2
----	LOOSE PIECE	320749
QUANTITY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE	
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm² [509-3,260] CIR MILS SOLID OR STRANDED	
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLG DEC ± 3 PLG DEC ±		DR 4-8-93 TA BRINKMAN	NAME AMP AMP Incorporated Harrisburg, PA 17105-3608	
MATERIAL COPPER PER ASTM B-152 ANNEALED		CHK 4-8-93 DA PATTERSON		
FINISH TIN PLATE 0.00254 [1.000100] MIN THK PER MIL-T-10727		APPD 4-8-93 DE MILLER		
APPLICATION SPEC		APPD 4-8-93 JL MECKLEY		
WEIGHT		SCALE 10:1	SIZE CAGE CODE 00779	DRAWING NO C=320749