








SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S91C4PS00LF	D09S91C6PS00LF
15	39.14	33.32	25.18	24.54	19.18	D15S91C4PS00LF	D15S91C6PS00LF
25	53.03	47.04	39.12	38.25	33.12	D25S91C4PS00LF	D25S91C6PS00LF
37	69.32	63.50	55.68	54.71	49.68	D37S91C4PS00LF	D37S91C6PS00LF
200 Matings							500 Matings

PC CARD LAYOUT




GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

LEAD FREE:ROHS INFORMATIONS

- The "LF" products meet European union Directives and other country regulations as described in GS-22-008.
- Termination plating spec: 0.5 to 3 µm Nickel, 0.5 to 1.5 µm Sn
- Packaging spec: see GS-14-920
- Shell plating : Copper + Nickel + bright pure tin
- Accessories: Copper + Nickel + bright pure tin

European Views

www.fciconnect.com				surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 		
				TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	C.JARRY	2003-11-08	ANGULAR		LINEAR		0.X	±0.1	size	A3	Scale 2:1
Eng	NIRMAL GEORGE	2009-10-13	0.XX' ±2°				0.XX	±0.1	ECN	-	
Chr	NIRMAL GEORGE	2009-10-13					0.XXX	±0.1			
Appr	SUDHIR VARMA	2009-10-13	Product family		D SUB		Spec ref -				



FEMALE DELTA D EUROPE
STRAIGHT COMPLIANT PRESS-FIT

C01-8646-0838

CUSTOMER sheet 1 of 1



Copyright FCI.