

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .040$	W $\pm .010$	C $\pm .020$	M $\pm .040$	H $\pm .010$
PNF 10-6LF-2K	#6	$\frac{1}{16}$ (.0625)	$\frac{3}{16}$ (.1875)	$\frac{1}{8}$ (.125)	$\frac{7}{16}$ (.4375)	$\frac{1}{4}$ (.25)
PNF 10-8LF-2K	#8	$\frac{1}{8}$ (.125)	$\frac{3}{16}$ (.1875)	$\frac{1}{8}$ (.125)	$\frac{7}{16}$ (.4375)	$\frac{1}{4}$ (.25)
PNF 10-10LF-2K	#10	$\frac{1}{8}$ (.125)	$\frac{3}{16}$ (.1875)	$\frac{1}{8}$ (.125)	$\frac{7}{16}$ (.4375)	$\frac{1}{4}$ (.25)
PNF 10-14LF-2K	1/4"	$\frac{1}{4}$ (.25)	$\frac{1}{2}$ (.5)	$\frac{3}{8}$ (.375)	$\frac{9}{16}$ (.5625)	$\frac{1}{2}$ (.5)




1. UL LISTED AND CSA CERTIFIED FOR :
 - A. 600 V MAX. VOLTAGE RATING
 - B. 221°F (105°C) MAX. TEMP. RATING
 - C. #12-10 AWG (2.5-6.0 mm²) SOLID OR STRANDED, COPPER WIRE
2. PACKAGE QTY. : 2K = 2000 PCS.
CONTINUOUS MOLDED CARRIER STRIP
3. MATERIAL :
 - A. STAMPING - .04" THK COPPER, TIN PLATED
 - B. HOUSING - YELLOW NYLON
 - C. SLEEVE - BRASS, TIN PLATED
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOLS :
 - A. PRESSES - CP-851, CP-860, CP-861
 - B. APPLICATOR - CA-800
 - C. DIE INSERTS - CD-800-3
6. WIRE STRIP LENGTH: $11/32^{+1/32}_{-0}$ (8.7^{+0.8}₋₀)

U

LIS

58

E52



05	1/01	KMD		FILE SPEC. WAS N41146AA_PCD_04					 PANDUIT CORP. TINLEY PARK, ILLINOIS			
04	5/99	ED		UPDATED "A"&"M" DIM.S. AND MODIFIED DIMENSIONAL TOLERANCES	07670							
03	1/97	JAMB	RLS	ADDED DIM., "MIN. WIRE INSULATION DIA.	05444		LA	DBH	TERMO 3PC. CONTINUOUSLY MOLDED NYLON (FUNNEL) INSULATED, 12-10 BARREL, LOCKING FORKS			
02	9/96	TSMA	RLS	REVISED DIMS AND TOLERANCES, ADD NOTE #6	05072		LA	DBH				
REV	DATE	BY	CHK	DESCRIPTION	ECN	QA	CUST	PM	DRAWN BY	CHK'D	SCALE	DRAWING NO.
									GRM	LA	NONE	A41146