


## Automotive-grade 450 V internally clamped IGBT E<sub>SCIS</sub> 300 mJ



### Features

- AEC-Q101 qualified
- SCIS energy of 300 mJ @ T<sub>J</sub> = 25 °C
- Parts are 100% tested in SCIS
- ESD gate-emitter protection
- Gate-collector high voltage clamping
- Logic level gate drive
- Very low saturation voltage
- High pulsed current capability
- Gate and gate-emitter resistor

### Applications

- Automotive ignition coil driver circuit

### Description

This application-specific IGBT utilizes the most advanced PowerMESH technology optimized for coil driving in the harsh environment of automotive ignition systems. These devices show very low on-state voltage and very high SCIS energy capability over a wide operating temperature range. Moreover, ESD-protected logic level gate input and an integrated gate resistor means no external protection circuitry is required.

#### Product status

STGB20N45LZAG

STGD20N45LZAG

#### Product summary

| Order code | STGB20N45LZAG      |
|------------|--------------------|
| Marking    | GB20N45LZ          |
| Package    | D <sup>2</sup> PAK |
| Packing    | Tape and reel      |
| Order code | STGD20N45LZAG      |
| Marking    | GD20N45LZ          |
| Package    | DPAK               |
| Packing    | Tape and reel      |

# 1 Electrical ratings

**Table 1. Absolute maximum ratings**

| Symbol                | Parameter                                                                     | Value                     | Unit |
|-----------------------|-------------------------------------------------------------------------------|---------------------------|------|
| $V_{CES}$             | Collector-emitter voltage ( $V_{GE} = 0\text{ V}$ )                           | $V_{CES(\text{clamped})}$ | V    |
| $V_{ECS}$             | Emitter-collector voltage ( $V_{GE} = 0\text{ V}$ )                           | 20                        | V    |
| $I_C$                 | Continuous collector current at $T_C = 25\text{ °C}$ , $V_{GE} = 4\text{ V}$  | 25                        | A    |
|                       | Continuous collector current at $T_C = 100\text{ °C}$ , $V_{GE} = 4\text{ V}$ | 25                        | A    |
| $I_{CP}^{(1)}$        | Pulsed collector current                                                      | 50                        | A    |
| $V_{GE}$              | Gate-emitter voltage                                                          | $V_{GE(\text{clamped})}$  | V    |
| $P_{TOT}$             | Total power dissipation at $T_C = 25\text{ °C}$                               | 150                       | W    |
| $E_{SCIS\_25}^{(2)}$  | Self-clamping inductive switching energy                                      | 300                       | mJ   |
| $E_{SCIS\_150}^{(3)}$ | Self-clamping inductive switching energy @ $T_J = 150\text{ °C}$              | 170                       | mJ   |
| ESD                   | Human body model, $R = 1.5\text{ k}\Omega$ , $C = 100\text{ pF}$              | 4                         | kV   |
|                       | Charged device model                                                          | 2                         | kV   |
| $T_{STG}$             | Storage temperature range                                                     | -55 to 175                | °C   |
| $T_J$                 | Operating junction temperature range                                          |                           | °C   |

1. Pulse width limited by maximum junction temperature.
2. Starting  $T_J = 25\text{ °C}$ ,  $L = 3\text{ mH}$ ,  $R_g = 1\text{ k}\Omega$ ,  $V_{cc} = 50\text{ V}$  during inductor charging and  $V_{cc} = 0\text{ V}$  during the time in clamp. Parts are 100% electrically tested in production.
3. Starting  $T_J = 150\text{ °C}$ ,  $L = 3\text{ mH}$ ,  $R_g = 1\text{ k}\Omega$ ,  $V_{cc} = 50\text{ V}$  during inductor charging and  $V_{cc} = 0\text{ V}$  during the time in clamp.

**Table 2. Thermal data**

| Symbol                | Parameter                           | Value              |      | Unit |
|-----------------------|-------------------------------------|--------------------|------|------|
|                       |                                     | D <sup>2</sup> PAK | DPAK |      |
| $R_{thj\text{-case}}$ | Thermal resistance junction-case    | 1                  |      | °C/W |
| $R_{thj\text{-amb}}$  | Thermal resistance junction-ambient | 62.5               | 100  | °C/W |

## 2 Electrical characteristics

$T_C = 25\text{ }^{\circ}\text{C}$  unless otherwise specified

**Table 3. Static characteristics**

| Symbol                    | Parameter                            | Test conditions                                                                                                              | Min. | Typ. | Max. | Unit          |
|---------------------------|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------|------|------|------|---------------|
| $V_{CES(\text{clamped})}$ | Collector-emitter clamped voltage    | $I_C = 2\text{ mA}$ , $V_{GE} = 0\text{ V}$                                                                                  |      | 450  |      | V             |
|                           |                                      | $I_C = 2\text{ mA}$ , $V_{GE} = 0\text{ V}$ ,<br>$T_J = -40\text{ }^{\circ}\text{C}$ to $175\text{ }^{\circ}\text{C}$        | 415  |      | 475  | V             |
| $V_{(BR)ECS}$             | Emitter-collector break-down voltage | $I_C = 75\text{ mA}$ , $V_{GE} = 0\text{ V}$                                                                                 | 20   |      |      | V             |
| $V_{GE(\text{clamped})}$  | Gate-emitter clamped voltage         | $I_G = \pm 2\text{ mA}$ , $T_J = -40\text{ }^{\circ}\text{C}$ to $175\text{ }^{\circ}\text{C}$                               | 12   |      | 16   | V             |
| $V_{CE(\text{sat})}$      | Collector-emitter saturation voltage | $V_{GE} = 4\text{ V}$ , $I_C = 6\text{ A}$                                                                                   |      | 1.1  | 1.25 | V             |
|                           |                                      | $V_{GE} = 4.5\text{ V}$ , $I_C = 10\text{ A}$ ,<br>$T_J = 175\text{ }^{\circ}\text{C}$                                       |      | 1.25 | 1.55 | V             |
| $V_{GE(\text{th})}$       | Gate-threshold voltage               | $V_{GE} = V_{CE}$ , $I_C = 1\text{ mA}$                                                                                      | 1.3  | 1.7  | 2.1  | V             |
|                           |                                      | $V_{GE} = V_{CE}$ , $I_C = 1\text{ mA}$ ,<br>$T_J = 175\text{ }^{\circ}\text{C}$                                             |      | 1.05 |      | V             |
| $I_{CES}$                 | Collector cut-off current            | $V_{CE} = 15\text{ V}$ , $V_{GE} = 0\text{ V}$ ,<br>$T_J = 150\text{ }^{\circ}\text{C}$                                      |      |      | 20   | $\mu\text{A}$ |
|                           |                                      | $V_{CE} = 200\text{ V}$ , $V_{GE} = 0\text{ V}$ ,<br>$T_J = 150\text{ }^{\circ}\text{C}$                                     |      |      | 100  | $\mu\text{A}$ |
| $I_{GES}$                 | Gate-emitter leakage current         | $V_{GE} = \pm 10\text{ V}$ , $V_{CE} = 0\text{ V}$                                                                           |      | 625  |      | $\mu\text{A}$ |
|                           |                                      | $V_{GE} = \pm 10\text{ V}$ , $V_{CE} = 0\text{ V}$ ,<br>$T_J = -40\text{ }^{\circ}\text{C}$ to $175\text{ }^{\circ}\text{C}$ | 450  |      | 900  | $\mu\text{A}$ |
| $R_{GE}$                  | Gate emitter resistance              |                                                                                                                              | 11   | 16   | 22   | k $\Omega$    |
| $R_G$                     | Gate resistance                      |                                                                                                                              |      | 120  |      | $\Omega$      |

**Table 4. Dynamic characteristics**

| Symbol    | Parameter                    | Test conditions                                                                | Min. | Typ. | Max. | Unit |
|-----------|------------------------------|--------------------------------------------------------------------------------|------|------|------|------|
| $C_{ies}$ | Input capacitance            | $V_{CE} = 25\text{ V}$ , $f = 1\text{ MHz}$ ,<br>$V_{GE} = 0\text{ V}$         | -    | 1011 | -    | pF   |
| $C_{oes}$ | Output capacitance           |                                                                                | -    | 87   | -    |      |
| $C_{res}$ | Reverse transfer capacitance |                                                                                | -    | 14   | -    |      |
| $Q_g$     | Total gate charge            | $V_{CE} = 13\text{ V}$ , $I_C = 10\text{ A}$ ,<br>$V_{GE} = 0$ to $5\text{ V}$ | -    | 26   | -    | nC   |

**Table 5. Resistive load switching characteristics**


| Symbol      | Parameter          | Test conditions                                                                                                                                                                                       | Min. | Typ. | Max. | Unit          |
|-------------|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|------|------|---------------|
| $t_{d(on)}$ | Turn-on delay time | $V_{CC} = 14\text{ V}$ , $V_{GE} = 5\text{ V}$ ,<br>$R_L = 1\ \Omega$ , $R_G = 1\text{ k}\Omega$<br>(see Figure 17. Test circuit for resistive load switching)                                        | -    | 1.1  | -    | $\mu\text{s}$ |
| $t_r$       | Current rise time  |                                                                                                                                                                                                       | -    | 3.6  | -    | $\mu\text{s}$ |
| $t_{d(on)}$ | Turn-on delay time | $V_{CC} = 14\text{ V}$ , $V_{GE} = 5\text{ V}$ ,<br>$R_L = 1\ \Omega$ , $R_G = 1\text{ k}\Omega$ ,<br>$T_J = 150\text{ }^\circ\text{C}$<br>(see Figure 17. Test circuit for resistive load switching) | -    | 1.06 | -    | $\mu\text{s}$ |
| $t_r$       | Current rise time  |                                                                                                                                                                                                       | -    | 3.5  | -    | $\mu\text{s}$ |

**Table 6. Inductive load switching characteristics**


| Symbol       | Parameter              | Test conditions                                                                                                                                                                                                              | Min. | Typ. | Max. | Unit                   |
|--------------|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|------|------|------------------------|
| $t_{d(off)}$ | Turn-off delay time    | $V_{CC} = 300\text{ V}$ , $L = 1\text{ mH}$ ,<br>$I_C = 10\text{ A}$ , $V_{GE} = 5\text{ V}$ ,<br>$R_G = 1\text{ k}\Omega$<br>(see Figure 16. Test circuit for inductive load switching)                                     | -    | 8.4  | -    | $\mu\text{s}$          |
| $t_f$        | Current fall time      |                                                                                                                                                                                                                              | -    | 5.5  | -    | $\mu\text{s}$          |
| $dV/dt$      | Turn-off voltage slope |                                                                                                                                                                                                                              | -    | 165  | -    | $\text{V}/\mu\text{s}$ |
| $t_{d(off)}$ | Turn-off delay time    | $V_{CC} = 300\text{ V}$ , $L = 1\text{ mH}$ ,<br>$I_C = 10\text{ A}$ , $V_{GE} = 5\text{ V}$ ,<br>$R_G = 1\text{ k}\Omega$ , $T_J = 150\text{ }^\circ\text{C}$<br>(see Figure 16. Test circuit for inductive load switching) | -    | 8.9  | -    | $\mu\text{s}$          |
| $t_f$        | Current fall time      |                                                                                                                                                                                                                              | -    | 8.2  | -    | $\mu\text{s}$          |
| $dV/dt$      | Turn-off voltage slope |                                                                                                                                                                                                                              | -    | 116  | -    | $\text{V}/\mu\text{s}$ |

## 2.1 Electrical characteristics (curves)


**Figure 1.  $V_{CE(sat)}$  vs junction temperature ( $I_C = 6$  A)**




**Figure 2.  $V_{CE(sat)}$  vs junction temperature ( $I_C = 10$  A)**




**Figure 3. Self-clamped inductive switching current**




**Figure 4. Output characteristics ( $T_J = 25$  °C)**












**Figure 5. Output characteristics ( $T_J = -40$  °C)**







**Figure 6. Output characteristics ( $T_J = 175$  °C)**



**Figure 7. Transfer characteristics**

**Figure 8. Collector current vs case temperature**

**Figure 9. Leakage current vs temperature**

**Figure 10. Normalized  $V_{CES(clamped)}$  vs temperature**

**Figure 11. Normalized  $V_{GE(th)}$  vs temperature**

**Figure 12. Gate charge vs gate-emitter voltage**


**Figure 13. Capacitance variations**

**Figure 14. Thermal impedance for D<sup>2</sup>PAK**

**Figure 15. Thermal impedance for DPAK**


### 3 Test circuits


**Figure 16. Test circuit for inductive load switching**

**Figure 17. Test circuit for resistive load switching**

**Figure 18. Gate charge test circuit**

**Figure 19. Switching waveform**


## 4 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: [www.st.com](http://www.st.com). ECOPACK is an ST trademark.

### 4.1 D<sup>2</sup>PAK (TO-263) type A package information


**Figure 20. D<sup>2</sup>PAK (TO-263) type A package outline**



0079457\_27

**Table 7. D<sup>2</sup>PAK (TO-263) type A package mechanical data**


| Dim. | mm    |      |       |
|------|-------|------|-------|
|      | Min.  | Typ. | Max.  |
| A    | 4.40  |      | 4.60  |
| A1   | 0.03  |      | 0.23  |
| b    | 0.70  |      | 0.93  |
| b2   | 1.14  |      | 1.70  |
| c    | 0.45  |      | 0.60  |
| c2   | 1.23  |      | 1.36  |
| D    | 8.95  |      | 9.35  |
| D1   | 7.50  | 7.75 | 8.00  |
| D2   | 1.10  | 1.30 | 1.50  |
| E    | 10.00 |      | 10.40 |
| E1   | 8.30  | 8.50 | 8.70  |
| E2   | 6.85  | 7.05 | 7.25  |
| e    |       | 2.54 |       |
| e1   | 4.88  |      | 5.28  |
| H    | 15.00 |      | 15.85 |
| J1   | 2.49  |      | 2.69  |
| L    | 2.29  |      | 2.79  |
| L1   | 1.27  |      | 1.40  |
| L2   | 1.30  |      | 1.75  |
| R    |       | 0.40 |       |
| V2   | 0°    |      | 8°    |

**Figure 21. D<sup>2</sup>PAK (TO-263) recommended footprint (dimensions are in mm)**


0079457\_Rev27\_footprint

## 4.2 DPAK (TO-252) type A2 package information


Figure 22. DPAK (TO-252) type A2 package outline



0068772\_type-A2\_rev35

**Table 8. DPAK (TO-252) type A2 mechanical data**

| Dim. | mm    |       |       |
|------|-------|-------|-------|
|      | Min.  | Typ.  | Max.  |
| A    | 2.20  |       | 2.40  |
| A1   | 0.90  |       | 1.10  |
| A2   | 0.03  |       | 0.23  |
| b    | 0.64  |       | 0.90  |
| b4   | 5.20  |       | 5.40  |
| c    | 0.45  |       | 0.60  |
| c2   | 0.48  |       | 0.60  |
| D    | 6.00  |       | 6.20  |
| D1   | 4.95  | 5.10  | 5.25  |
| E    | 6.40  |       | 6.60  |
| E1   | 5.10  | 5.20  | 5.30  |
| e    | 2.159 | 2.286 | 2.413 |
| e1   | 4.445 | 4.572 | 4.699 |
| H    | 9.35  |       | 10.10 |
| L    | 1.00  |       | 1.50  |
| L1   | 2.60  | 2.80  | 3.00  |
| L2   | 0.65  | 0.80  | 0.95  |
| L4   | 0.60  |       | 1.00  |
| R    |       | 0.20  |       |
| V2   | 0°    |       | 8°    |

**Figure 23. DPAK (TO-252) recommended footprint (dimensions are in mm)**



Notes:

- 1) This footprint is able to ensure insulation up to 630 Vrms (according to CEI IEC 664-1)
- 2) The device must be positioned within  $\Phi 0.05$  A B

FP\_0068772\_35

### 4.3 D<sup>2</sup>PAK packing information


Figure 24. D<sup>2</sup>PAK tape drawing (dimensions are in mm)




DM01095771\_1

## 4.4 DPAK packing information

Figure 25. DPAK tape outline



AM08852v1

**Figure 26. DPAK reel outline**


AM06038v1

**Table 9. DPAK tape and reel mechanical data**

| Tape |      |      | Reel      |      |      |
|------|------|------|-----------|------|------|
| Dim. | mm   |      | Dim.      | mm   |      |
|      | Min. | Max. |           | Min. | Max. |
| A0   | 6.8  | 7    | A         |      | 330  |
| B0   | 10.4 | 10.6 | B         | 1.5  |      |
| B1   |      | 12.1 | C         | 12.8 | 13.2 |
| D    | 1.5  | 1.6  | D         | 20.2 |      |
| D1   | 1.5  |      | G         | 16.4 | 18.4 |
| E    | 1.65 | 1.85 | N         | 50   |      |
| F    | 7.4  | 7.6  | T         |      | 22.4 |
| K0   | 2.55 | 2.75 |           |      |      |
| P0   | 3.9  | 4.1  | Base qty. |      | 2500 |
| P1   | 7.9  | 8.1  | Bulk qty. |      | 2500 |
| P2   | 1.9  | 2.1  |           |      |      |
| R    | 40   |      |           |      |      |
| T    | 0.25 | 0.35 |           |      |      |
| W    | 15.7 | 16.3 |           |      |      |

## Revision history

**Table 10. Document revision history**

| Date        | Revision | Changes                                                                                                                                                                                                                                                                         |
|-------------|----------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 30-Oct-2015 | 1        | First release.                                                                                                                                                                                                                                                                  |
| 01-Sep-2017 | 2        | Modified Table 2: "Absolute maximum ratings", Table 3: "Thermal data", Table 4: "Static characteristics" and Table 5: "Dynamic characteristics". Added Section 2.1: "Electrical characteristics (curves)".<br>Modified Section 4: "Package information".<br>Minor text changes. |
| 06-Sep-2017 | 3        | Modified Figure 2: " $V_{CE(sat)}$ vs. junction temperature ( $I_C = 6.0\text{ A}$ )", Figure 4: "Self clamped inductive switching current vs. inductance" and Figure 11: "Normalized $V_{CES(clamped)}$ vs. junction temperature".<br>Minor text changes.                      |
| 11-Sep-2017 | 4        | Modified Section 4.1: "D <sup>2</sup> PAK (TO-263) type A package information".<br>Minor text changes.                                                                                                                                                                          |
| 02-Nov-2017 | 5        | Updated Table 4: "Static characteristics".<br>Minor text changes                                                                                                                                                                                                                |
| 21-Feb-2018 | 6        | Removed maturity status indication from cover page. The document status is production data.<br>Updated Section 1 Electrical ratings, Table 2. Thermal data and Table 3. Static characteristics.<br>Minor text changes                                                           |
| 08-Feb-2023 | 7        | Updated Section 1 Electrical ratings.<br>Updated Table 6. Inductive load switching characteristics.                                                                                                                                                                             |
| 06-Oct-2023 | 8        | Updated Table 6. Inductive load switching characteristics.                                                                                                                                                                                                                      |
| 05-May-2025 | 9        | Updated Section 4: Package information.                                                                                                                                                                                                                                         |

## Contents

|          |                                                              |           |
|----------|--------------------------------------------------------------|-----------|
| <b>1</b> | <b>Electrical ratings .....</b>                              | <b>2</b>  |
| <b>2</b> | <b>Electrical characteristics.....</b>                       | <b>3</b>  |
| 2.1      | Electrical characteristics (curves).....                     | 5         |
| <b>3</b> | <b>Test circuits .....</b>                                   | <b>8</b>  |
| <b>4</b> | <b>Package information.....</b>                              | <b>9</b>  |
| 4.1      | D <sup>2</sup> PAK (TO-263) type A package information ..... | 9         |
| 4.2      | DPAK (TO-252) type A2 package information .....              | 12        |
| 4.3      | D <sup>2</sup> PAK packing information .....                 | 15        |
| 4.4      | DPAK packing information .....                               | 16        |
|          | <b>Revision history .....</b>                                | <b>18</b> |

**IMPORTANT NOTICE – READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to [www.st.com/trademarks](http://www.st.com/trademarks). All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved