

Signal lamps with integrated filament/neon lamp - 14 mm



Technical Data

General information		Electrical characteristics	
Form of lens	see order block	Voltage limit max.	see order block
Colour of lens	see order block	Power limit max.	1.2 W
Dimensions		Other specifications	
Dimensions of collar	see order block	Operating life	see order block
Overall height	4 mm	Degree of protection from front side	IP40
Mounting depth	see order block	Weight	5 g
Mounting hole	14 mm		
Mechanical design			
Mounting	pressing into hole		
Terminals	see order block		
Lamp socket	no		
Lamp	see order block		

3

integr.
Lamp


Approvals



VDE

VDET85° (only version with neon lamp)


Signal lamps with integrated neon lamp - 14 mm, round lens, 230 V



Voltage limit max.	Power limit max.	Lamp	Terminals	Operating life	Colour of lens	Order no.
230 V	-	neon lamp	quick connector 2.8 x 0.8	-	transparent colourless	1.02.614.502/1002
230 V	-	neon lamp	quick connector 2.8 x 0.8	-	transparent red	1.02.614.502/1301
230 V	-	neon lamp	quick connector 2.8 x 0.8	-	transparent yellow	1.02.614.502/1402
230 V	-	neon glow lamp	quick connector 2.8 x 0.8	-	transparent green	1.02.614.503/1502

Technical data see page 3 - 36

Signal lamps with integrated filament lamp - 14 mm, round lens, 28 V



Voltage limit max.	Power limit max.	Lamp	Terminals	Operating life	Colour of lens	Order no.
28 V	1.2 W	filament lamp	quick connector 2.8 x 0.8	10,000 h	transparent colourless	1.69.523.003/1002
28 V	1.2 W	filament lamp	quick connector 2.8 x 0.8	10,000 h	transparent red	1.69.523.003/1301
28 V	1.2 W	filament lamp	quick connector 2.8 x 0.8	10,000 h	transparent yellow	1.69.523.003/1402
28 V	1.2 W	filament lamp	quick connector 2.8 x 0.8	10,000 h	transparent green	1.69.523.003/1502

Technical data see page 3 - 36

3

integr.
Lamp