

DOC. NO.:	MINI DIN SPECIFICATION	FILE:
SERIES NO.:		REVISION: A
DATE:87.03.05		PAGE: 1 OF 1

MATERIAL / FINISHS

INSULATOR	Material	P.B.T & GLASS FILL REINFORCED UL-94V-0
CONTACT	Material	BRASS
	Plating	TIN PLATED OVER NICKEL
	Thickness	TIN: 80~100u" BASE NICKEL: 40u"
SHELL	Material	NO
	Plating	NO
	Thickness	NO
SCREWLOCK. BOARDLOCK. RIVET.GROUNDING.	Material	NO



SPECIFICATION

RATE CURRENT	3 AMP.
INSULATION RESISTANCE	3000 MEGOHM MIN. AT 500V DC
CONTACT RESISTANCE	15 MILLIOHM MAX
DIELECTRIC WITHSTANDING VOLTAGE	1000 V AC / 1 MINUTE
OP.TEMPERATURE	-55°C ~+105°C

REMARKS:

G18FA SERIES

DIVISION STAMP	APPROVED	CHECKED	DRAWN
	3/5	3/5	Candy3/5



ASSEMBLY TYPE MALE

3 PIN		4 PIN		5 PIN		6 PIN		7 PIN		8 PIN	
-------	--	-------	--	-------	--	-------	--	-------	--	-------	--

UNLESS OTHERWISE SPECIFIED TOLERANCES		DRAWN NAME:	
0.5	±0.5	MINI DIN SOLDER TYPE	
0.2	±0.2		
0.1	±0.1		
SCALE: 1:1		UNIT: mm	
DRAWN ROSIE		04/24/98	
CHECKED <i>Ben</i>		04/24/98	
APPROVED <i>Ben</i>		04/24/98	
DATE		DATE	
04/24/98		04/24/98	
DESCRIPTION		PRODUCT NO. G18FA 0X 1350	
REV. A		REV. A	