




		1					
LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E3	REVISED PER ECO-11-004587	11MAR2011	RK	HMR



PRELIMINARY	0.76µm GOLD	-	-	60.60	55.88	10	2-796859-6
PRELIMINARY	0.2µm GOLD		DETAIL G	35.20	30.48	5	2-796859-5
PRELIMINARY	TIN		DETAIL F	25.04	20.32	3	2-796859-4
	TIN	-	-	126.64	121.92	23	2-796859-3
	TIN	-	-	121.56	116.84	22	2-796859-2
	TIN	-	-	116.48	111.76	21	2-796859-1
	TIN	-	-	111.40	106.68	20	2-796859-0
	TIN	-	-	106.32	101.60	19	1-796859-9
	TIN	-	-	101.24	96.52	18	1-796859-8
	TIN	-	-	96.16	91.44	17	1-796859-7
	TIN	-	-	91.08	86.36	16	1-796859-6
	TIN	-	-	86.00	81.28	15	1-796859-5
	TIN	-	-	80.92	76.20	14	1-796859-4
	TIN	-	-	75.84	71.12	13	1-796859-3
	TIN	-	-	70.76	66.04	12	1-796859-2
	TIN	-	-	65.68	60.96	11	1-796859-1
	TIN	-	-	60.60	55.88	10	1-796859-0
	TIN	-	-	55.52	50.80	9	796859-9
	TIN	-	-	50.44	45.72	8	796859-8
	TIN	-	-	45.36	40.64	7	796859-7
	TIN	-	-	40.28	35.56	6	796859-6
	TIN	-	-	35.20	30.48	5	796859-5
	TIN	-	-	30.12	25.40	4	796859-4
	TIN	-	-	25.04	20.32	3	796859-3
	TIN	-	-	19.96	15.24	2	796859-2
TERMINAL PLATING	MARKING	SPECIAL	L	H	NO. OF POSN	PART NUMBER	

1. MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: GREEN.
TERMINAL: PHOSPHOR BRONZE, PLATING: SEE TABLE, OVER 2-3µm NICKEL
2. SUITABLE FOR 1,6-2, 4mm PC BOARD THICKNESS.
3. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE No. E60677.
4. IMQ CERTIFICATE WITH SURVEILLANCE ON CONFORMITY WITH IEC 998-1/998-2-1.
5. INK MARKING, COLOR: WHITE.
6. LABEL APPLIED OR INK MARKING AS SHOWN.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2
1 PLC ±0.00
2 PLC ±0.00
3 PLC ±0.000
4 PLC ±0.000
ANGLES ±
FINISH

DWN S. WELDON 12FEB2001
CHK D. BIEVENOUR 12FEB2001
APVD D. BIEVENOUR 12FEB2001

PRODUCT SPEC
APPLICATION SPEC
WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK, PLUG
90 DEGREE, WITH FLANGE,
5.08mm PITCH

SIZE
A200779

CAGE CODE
C-796859

DRAWING NO
C-796859

RESTRICTED TO
-


SCALE
2:1

SHEET
1


OF
2

REV
E3

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-



DETAIL F



DETAIL G

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. WELDON

CHK
D. BIEVENOUR

APVD
D. BIEVENOUR

12FEB2001

12FEB2001

12FEB2001

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.2

2 PLC ±0.00

3 PLC ±0.000

4 PLC ±0.0000

ANGLES ±

FINISH

MATERIAL

-

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

TERMINAL BLOCK, PLUG
90 DEGREE, WITH FLANGE,
5.08mm PITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-796859

SCALE 4:1

SHEET 2 OF 2

REV E3