

## TELECOMMUNICATION SYSTEM SECONDARY PROTECTION

- Ion-Implanted Breakdown Region  
Precise and Stable Voltage  
Low Voltage Overshoot under Surge

DEVICE	$V_{(Z)}$ V	$V_{(BO)}$ V
'4290	200	290

- Planar Passivated Junctions  
Low Off-State Current  $< 10 \mu\text{A}$
- Rated for International Surge Wave Shapes


WAVE SHAPE	STANDARD	$I_{TSP}$ A
8/20 $\mu\text{s}$	ANSI C62.41	150
10/160 $\mu\text{s}$	FCC Part 68	60
10/560 $\mu\text{s}$	FCC Part 68	45
0.2/310 $\mu\text{s}$	RLM 88	38
	FTZ R12	50
10/700 $\mu\text{s}$	VDE 0433	50
	CCITT IX K17/K20	50
10/1000 $\mu\text{s}$	REA PE-60	35

- UL Recognized, E132482

## description

The TISP4290 is designed specifically for telephone equipment protection against lightning and transients induced by a.c. power lines. These devices consist of a bidirectional suppressor element connecting the A and B terminals. They will suppress inter-wire voltage transients.


Transients are initially clipped by zener action until the voltage rises to the breakdown level, which causes the device to crowbar. The high crowbar holding current prevents d.c. latchup as the transient subsides.



Pin 1 is in electrical contact with the mounting base.

MD4XAB

## device symbol



These monolithic protection devices are fabricated in ion-implanted planar structures to ensure precise and matched breakdown control and are virtually transparent to the system in normal operation.

## PRODUCT INFORMATION

Information is current as of publication date. Products conform to specifications in accordance with the terms of Power Innovations standard warranty. Production processing does not necessarily include testing of all parameters.

**TISP4290**  
**SYMMETRICAL TRANSIENT**  
**VOLTAGE SUPPRESSORS**

APRIL 1987 - REVISED SEPTEMBER 1997

**absolute maximum ratings at 25°C case temperature (unless otherwise noted)**

RATING	SYMBOL	VALUE	UNIT
Non-repetitive peak on-state pulse current (see Notes 1, 2 and 3)	I <sub>TSP</sub>		A
8/20 µs (ANSI C62.41, open-circuit voltage wave shape 1.2/50 µs)		150	
10/160 µs (FCC Part 68, open-circuit voltage wave shape 10/160 µs)		60	
5/200 µs (VDE 0433, open-circuit voltage wave shape 2 kV, 10/700 µs)		50	
0.2/310 µs (RLM 88, open-circuit voltage wave shape 1.5 kV, 0.5/700 µs)		38	
5/310 µs (CCITT IX K17/K20, open-circuit voltage wave shape 2 kV, 10/700 µs)		50	
5/310 µs (FTZ R12, open-circuit voltage wave shape 2 kV, 10/700 µs)		50	
10/560 µs (FCC Part 68, open-circuit voltage wave shape 10/560 µs)		45	
10/1000 µs (REA PE-60, open-circuit voltage wave shape 10/1000 µs)		35	
Non-repetitive peak on-state current, 50 Hz, 2.5 s (see Notes 1 and 2)	I <sub>TSM</sub>	10	A rms
Initial rate of rise of on-state current, Linear current ramp, Maximum ramp value < 38 A	dI <sub>T</sub> /dt	250	A/µs
Junction temperature	T <sub>J</sub>	150	°C
Operating free - air temperature range		0 to 70	°C
Storage temperature range	T <sub>stg</sub>	-40 to +150	°C
Lead temperature 1.5 mm from case for 10 s	T <sub>lead</sub>	260	°C

NOTES: 1. Above 70°C, derate linearly to zero at 150°C case temperature

- This value applies when the initial case temperature is at (or below) 70°C. The surge may be repeated after the device has returned to thermal equilibrium.
- Most PTT's quote an unloaded voltage waveform. In operation the TISP essentially shorts the generator output. The resulting loaded current waveform is specified.

**electrical characteristics, T<sub>J</sub> = 25°C**

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
V <sub>Z</sub> Reference zener voltage	I <sub>Z</sub> = ± 1mA	± 200			V
^V <sub>Z</sub> Temperature coefficient of reference voltage			0.1		%/°C
V <sub>(BO)</sub> Breakover voltage	(see Notes 4 and 5)			± 290	V
I <sub>(BO)</sub> Breakover current	(see Note 4)	± 0.15		± 0.6	A
V <sub>TM</sub> Peak on-state voltage	I <sub>T</sub> = ± 5 A (see Notes 4 and 5)		± 1.9	± 3	V
I <sub>H</sub> Holding current	(see Note 4)	± 150			mA
dv/dt Critical rate of rise of off-state voltage	(see Note 6)			± 5	kV/µs
I <sub>D</sub> Off-state leakage current	V <sub>D</sub> = ± 50 V			± 10	µA
C <sub>off</sub> Off-state capacitance	V <sub>D</sub> = 0 f = 1 kHz	110	200		pF

NOTES: 4. These parameters must be measured using pulse techniques, t<sub>w</sub> = 100 µs, duty cycle ≤ 2%.

- These parameters are measured with voltage sensing contacts separate from the current carrying contacts located within 3.2 mm (0.125 inch) from the device body.
- Linear rate of rise, maximum voltage limited to 80 % V<sub>Z</sub> (minimum).

**thermal characteristics**

PARAMETER	MIN	TYP	MAX	UNIT
R <sub>θJA</sub> Junction to free air thermal resistance			62.5	°C/W

PARAMETER MEASUREMENT INFORMATION





Figure 1. VOLTAGE-CURRENT CHARACTERISTIC FOR TERMINALS A AND B

**TISP4290**  
**SYMMETRICAL TRANSIENT**  
**VOLTAGE SUPPRESSORS**

APRIL 1987 - REVISED SEPTEMBER 1997

**TYPICAL CHARACTERISTICS**  
**A and B terminals**




**Figure 2.**

## MECHANICAL DATA

DO-220

## 2-pin plastic flange-mount package

This single-in-line package consists of a circuit mounted on a lead frame and encapsulated within a plastic compound. The compound will withstand soldering temperature with no deformation, and circuit performance characteristics will remain stable when operated in high humidity conditions. Leads require no additional cleaning or processing when used in soldered assembly.



NOTES: A. Tie bar short stand off height according to package version.

Version 1, pin 1 is in electrical contact with the mounting tab via tie bar short - stand off height : 2,0 mm maximum.  
Version 2, pin 1 is in electrical contact with the mounting tab (no external tie bar short).

#### B. Mounting tab corner profile according to package version.

- B. Mounting tab corner profile according to package version.
- C. Typical fixing hole centre stand off height according to pac

C. Typical fixing hole centre stand off height according to package Version.  
Version 1: 18.0 mm, Version 2: 17.6 mm

Version 1, 18,0 mm. Version 2, 17,6 mm.

**TISP4290**  
**SYMMETRICAL TRANSIENT**  
**VOLTAGE SUPPRESSORS**

APRIL 1987 - REVISED SEPTEMBER 1997

---

**IMPORTANT NOTICE**

Power Innovations Limited (PI) reserves the right to make changes to its products or to discontinue any semiconductor product or service without notice, and advises its customers to verify, before placing orders, that the information being relied on is current.

PI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with PI's standard warranty. Testing and other quality control techniques are utilized to the extent PI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except as mandated by government requirements.

PI accepts no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein. Nor is any license, either express or implied, granted under any patent right, copyright, design right, or other intellectual property right of PI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used.

**PI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED, OR WARRANTED TO BE  
SUITABLE FOR USE IN LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS.**

Copyright © 1997, Power Innovations Limited

**PRODUCT INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bourns](#):

[TISP4290](#) [TISP4290-S](#)