


390-004 Water-Tight EMI/RFI Cable Sealing Backshell with Strain Relief Type A - Direct Coupling - Low Profile

CONNECTOR DESIGNATORS


A-B*-C-D-E-F
G-H-J-K-L-S

* Conn. Design. B See Note 6
DIRECT COUPLING



TYPE A OVERALL SHIELD TERMINATION



STYLE 2
(STRAIGHT
See Note 1)



STYLE C
Medium Duty
(Table X)



STYLE E
Medium Duty
(Table XI)



390-004
Water-Tight EMI/RFI Cable Sealing Backshell
with Strain Relief
Type A - Direct Coupling - Low Profile



39

See inside back cover fold-out or pages 13 and 14 for Tables I and II.

TABLE III: FRONT ADAPTER				
Shell Size	J Max - Conn. Designator			
	A-E-F		D-B-G-K	C
	J-H-L-S			
08/09	1.180 (30.0)	1.440 (36.6)		
10/11	1.180 (30.0)	1.440 (36.6)		
12/13	1.180 (30.0)	1.440 (36.6)	1.735 (44.1)	
14/15	1.180 (30.0)	1.440 (36.6)	1.915 (48.6)	
16/17	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)	
18/19	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)	
20/21	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)	
22/23	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)	
24/25	1.380 (35.0)	1.560 (39.6)	1.915 (48.6)	
28/29	1.610 (40.9)	1.560 (39.6)	1.915 (48.6)	
32/33	1.610 (40.9)	1.750 (44.5)	1.915 (48.6)	
36	1.610 (40.9)	1.750 (44.5)	1.915 (48.6)	
40	1.610 (40.9)	2.190 (55.6)	1.915 (48.6)	

TABLE IV: ELBOW DIMENSIONS									
Dash No.	E Max		F Max		G Max		H Max		
04	.630	(16.0)	1.250	(31.8)	.636	(16.2)	1.200	(30.5)	
06	.630	(16.0)	1.250	(31.8)	.710	(18.0)	1.320	(33.5)	
08	.692	(17.6)	1.312	(33.3)	.731	(18.6)	1.340	(34.0)	
10	.755	(19.2)	1.655	(42.0)	.825	(21.0)	1.660	(42.2)	
12	.848	(21.5)	1.765	(44.8)	.988	(25.1)	1.750	(44.5)	
16	1.036	(26.3)	1.952	(49.6)	1.087	(27.6)	1.925	(48.9)	
20	1.130	(28.7)	2.098	(53.3)	1.325	(33.7)	2.033	(51.6)	
24	1.255	(31.9)	2.155	(54.7)	1.337	(34.0)	2.250	(57.2)	
28	1.317	(33.5)	2.250	(57.2)	1.827	(46.4)	2.450	(62.2)	
32	1.348	(34.2)	2.343	(59.5)	2.027	(51.5)	2.450	(62.2)	

TABLE X: CABLE ENTRY							
Dash No.	T Max	W Max	X Ref	Cable Range			
				Min		Max	
03	1.219 (31.0)	.812 (20.6)	.135 (3.4)	.156	(4.0)	.219	(5.6)
04	1.219 (31.0)	.937 (23.8)	.203 (5.2)	.188	(4.8)	.312	(7.9)
06	1.219 (31.0)	1.062 (27.0)	.285 (7.2)	.281	(7.1)	.438	(11.1)
08	1.219 (31.0)	1.188 (30.2)	.350 (8.9)	.312	(7.9)	.531	(13.5)
10	1.281 (32.5)	1.312 (33.3)	.390 (9.9)	.375	(9.5)	.625	(15.9)
12	1.281 (32.5)	1.562 (39.7)	.460 (11.7)	.500	(12.7)	.750	(19.1)
16	1.406 (35.7)	1.750 (44.5)	.510 (13.0)	.625	(15.9)	.938	(23.8)
20	1.656 (42.1)	2.250 (57.2)	.695 (17.7)	.938	(23.8)	1.250	(31.8)
24	1.906 (48.4)	2.375 (60.3)	.715 (18.2)	1.000	(25.4)	1.375	(34.9)
28	1.906 (48.4)	2.625 (66.7)	.915 (23.2)	1.250	(31.8)	1.625	(41.3)
32	2.000 (50.8)	2.812 (71.4)	1.070 (27.2)	1.500	(38.1)	1.875	(47.6)

TABLE XI: CABLE ENTRY					
Dash No.	Y Max	Z Max	Cable Range		
			Min		Max
03	.739 (18.8)	.812 (20.6)	.156	(4.0)	.219 (5.6)
04	.739 (18.8)	.937 (23.8)	.188	(4.8)	.312 (7.9)
06	.739 (18.8)	1.062 (27.0)	.281	(7.1)	.438 (11.1)
08	.739 (18.8)	1.188 (30.2)	.312	(7.9)	.531 (13.5)
10	.791 (20.1)	1.312 (33.3)	.375	(9.5)	.625 (15.9)
12	.880 (22.4)	1.562 (39.7)	.500	(12.7)	.750 (19.1)
16	.901 (22.9)	1.750 (44.5)	.625	(15.9)	.938 (23.8)
20	1.031 (26.2)	2.250 (57.2)	.938	(23.8)	1.250 (31.8)
24	1.250 (31.8)	2.375 (60.3)	1.000	(25.4)	1.375 (34.9)
28	1.250 (31.8)	2.625 (66.7)	1.250	(31.8)	1.625 (41.3)
32	1.312 (33.3)	2.812 (71.4)	1.500	(38.1)	1.875 (47.6)

1. When maximum cable entry (page 22) is exceeded, Style 2 will be supplied. (Function S only).
2. Metric dimensions (mm) are indicated in parentheses.
3. Cable range is defined as the accommodations range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
4. Consult factory for shorter lengths on straight backshells.
5. Saddles are bottomed on Clamp Ears.
6. When using Connector Designator B refer to pages 18 and 19 for part number development.