






MATERIALS AND FINISHES

BODY BRASS
PLATED SEE TABLE

CENTER CONTACT BERYLLIUM COPPER
PLATED GOLD

INSULATOR TEFLON

COUPLING PROOF TORQUE:
0.90 N-m(8 IN-LB) MAXIMUM
WITH SUPPORT WRENCH



RECOMMENDED PCB LAYOUT

PS-89675-3670	PRODUCT SPECIFICATION
MIL-STD-348A, FIG. 310.2	INTERFACE
SPECIFICATION	DESCRIPTION

73251-3461	NICKEL
73251-3460	GOLD
PART NO.	PLATING/FINISH

CHG: UPDATE VIEW FOR INSULATOR LENGTH	EC NO: URF2009-0550 2009/03/24 DRWN: JWIENER 2009/03/24 CHKD: SSHAH 2009/03/24 APPR: JWIENER	DESCRIPTION	REV
C1			

GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
	mm	INCH	DRAWN BY	DATE	SMA JACK, PCB, EDMOUNT 50 OHMS, EWR3652 SMA-J/PCB		
4 PLACES	± ---	± ---	SSS	2008/06/13			
3 PLACES	± ---	± ---	CHECKED BY	DATE			
2 PLACES	± ---	± ---	AZR	2008/06/13			
1 PLACE	± ---	± ---	APPROVED BY	DATE		MOLEX INCORPORATED	
ANGULAR ± 2 °		JDW	2008/06/13				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.		SHEET NO.
			SEE TABLE		SD-73251-346		1 OF 1
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[73251-3460](#)