

ST180C..C SERIES

PHASE CONTROL THYRISTORS

Hockey Puk Version

Features

- Center amplifying gate
- Metal case with ceramic insulator
- International standard case TO-200AB (A-PUK)

Typical Applications

- DC motor controls
- Controlled DC power supplies
- AC controllers

Major Ratings and Characteristics

Parameters	ST180C..C	Units
$I_{T(AV)}$	350	A
@ T_{hs}	55	°C
$I_{T(RMS)}$	660	A
@ T_{hs}	25	°C
I_{TSM}	@ 50Hz	5000
	@ 60Hz	5230
I^2t	@ 50Hz	125
	@ 60Hz	114
V_{DRM}/V_{RRM}	400 to 2000	V
t_q typical	100	μs
T_J	- 40 to 125	°C

350A



case style TO-200AB (A-PUK)

ST180C..C Series

Bulletin I25164 rev. C 02/00

International
IOR Rectifier

ELECTRICAL SPECIFICATIONS

Voltage Ratings

Type number	Voltage Code	V_{DRM}/V_{RRM} , max. repetitive peak and off-state voltage V	V_{RSM} , maximum non-repetitive peak voltage V	I_{DRM}/I_{RRM} max. @ $T_J = T_J \text{ max}$ mA
ST180C..C	04	400	500	30
	08	800	900	
	12	1200	1300	
	16	1600	1700	
	18	1800	1900	
	20	2000	2100	

On-state Conduction

Parameter	ST180C..C	Units	Conditions
$I_{T(AV)}$ Max. average on-state current @ Heatsink temperature	350 (140) 55 (85)	A °C	180° conduction, half sine wave double side (single side) cooled
$I_{T(RMS)}$ Max. RMS on-state current	660		@ 25°C heatsink temperature double side cooled
I_{TSM} Max. peak, one-cycle non-repetitive surge current	5000	A	t = 10ms No voltage
	5230		t = 8.3ms reapplied
	4200		t = 10ms 100% V_{RRM}
	4400		t = 8.3ms reapplied
I^2t Maximum I^2t for fusing	125	KA ² s	t = 10ms No voltage
	114		t = 8.3ms reapplied
	88		t = 10ms 100% V_{RRM}
	81		t = 8.3ms reapplied
$I^2\sqrt{t}$ Maximum $I^2\sqrt{t}$ for fusing	1250	KA ² /s	t = 0.1 to 10ms, no voltage reapplied
$V_{T(TO)1}$ Low level value of threshold voltage	1.08	V	$(16.7\% \times \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)}), T_J = T_J \text{ max.}$
$V_{T(TO)2}$ High level value of threshold voltage	1.14		$(I > \pi \times I_{T(AV)}), T_J = T_J \text{ max.}$
r_{t1} Low level value of on-state slope resistance	1.18	mΩ	$(16.7\% \times \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)}), T_J = T_J \text{ max.}$
r_{t2} High level value of on-state slope resistance	1.14		$(I > \pi \times I_{T(AV)}), T_J = T_J \text{ max.}$
V_{TM} Max. on-state voltage	1.96	V	$I_{pk} = 750A, T_J = T_J \text{ max, } t_p = 10ms$ sine pulse
I_H Maximum holding current	600	mA	$T_J = T_J \text{ max, anode supply 12V resistive load}$
I_L Max. (typical) latching current	1000 (300)		

Switching

Parameter	ST180C..C	Units	Conditions
di/dt Max. non-repetitive rate of rise of turned-on current	1000	A/μs	Gate drive 20V, 20Ω, $t_r \leq 1\mu s$ $T_J = T_J \text{ max}$, anode voltage $\leq 80\% V_{DRM}$
t_d Typical delay time	1.0	μs	Gate current 1A, $di_g/dt = 1A/\mu s$ $V_d = 0.67\% V_{DRM}$, $T_J = 25^\circ C$
t_q Typical turn-off time	100		$I_{TM} = 300A$, $T_J = T_J \text{ max}$, $di/dt = 20A/\mu s$, $V_R = 50V$ $dv/dt = 20V/\mu s$, Gate 0V 100Ω, $t_p = 500\mu s$

Blocking

Parameter	ST180C..C	Units	Conditions
dv/dt Maximum critical rate of rise of off-state voltage	500	V/μs	$T_J = T_J \text{ max}$ linear to 80% rated V_{DRM}
I_{DRM} I_{RRM} Max. peak reverse and off-state leakage current	30	mA	$T_J = T_J \text{ max}$, rated V_{DRM}/V_{RRM} applied

Triggering

Parameter		ST180C..C		Units	Conditions	
P _{GM}	Maximum peak gate power	10	W	A	T _J = T _J max, t _p ≤ 5ms	
P _{G(AV)}	Maximum average gate power	2.0			T _J = T _J max, f = 50Hz, d% = 50	
I _{GM}	Max. peak positive gate current	3.0			T _J = T _J max, t _p ≤ 5ms	
+V _{GM}	Maximum peak positive gate voltage	20	V		T _J = T _J max, t _p ≤ 5ms	
-V _{GM}	Maximum peak negative gate voltage	5.0				
I _{GT}	DC gate current required to trigger	TYP.	MAX.	mA	Max. required gate trigger/ current/ voltage are the lowest value which will trigger all units 12V anode-to-cathode applied	
		180	-			
		90	150			
		40	-			
V _{GT}	DC gate voltage required to trigger	2.9	-	V		T _J = - 40°C
		1.8	3.0			T _J = 25°C
		1.2	-		T _J = 125°C	
I _{GD}	DC gate current not to trigger	10		mA	T _J = T _J max	Max. gate current/voltage not to trigger is the max. value which will not trigger any unit with rated V _{DRM} anode-to-cathode applied
V _{GD}	DC gate voltage not to trigger	0.25				

ST180C..C Series

Bulletin I25164 rev. C 02/00

International
IOR Rectifier

Thermal and Mechanical Specification

Parameter	ST180C..C	Units	Conditions
T_J Max. operating temperature range	-40 to 125	°C	
T_{stg} Max. storage temperature range	-40 to 150		
R_{thJ-hs} Max. thermal resistance, junction to heatsink	0.17 0.08	K/W	DC operation single side cooled DC operation double side cooled
R_{thC-hs} Max. thermal resistance, case to heatsink	0.033 0.017	K/W	DC operation single side cooled DC operation double side cooled
F Mounting force, $\pm 10\%$	4900 (500)	N (Kg)	
wt Approximate weight	50	g	
Case style	TO - 200AB (A-PUK)		See Outline Table

ΔR_{thJ-hs} Conduction

(The following table shows the increment of thermal resistance R_{thJ-hs} when devices operate at different conduction angles than DC)

Conduction angle	Sinusoidal conduction		Rectangular conduction		Units	Conditions
	Single Side	Double Side	Single Side	Double Side		
180°	0.015	0.015	0.011	0.011	K/W	$T_J = T_J \text{ max.}$
120°	0.018	0.019	0.019	0.019		
90°	0.024	0.024	0.026	0.026		
60°	0.035	0.035	0.036	0.037		
30°	0.060	0.060	0.060	0.061		

Ordering Information Table

Device Code							
ST 18 0 C 20 C 1							
	1	2	3	4	5	6	7
	8						
1	-	Thyristor					
2	-	Essential part number					
3	-	0 = Converter grade					
4	-	C = Ceramic Puk					
5	-	Voltage code: Code x 100 = V_{RRM} (See Voltage Rating Table)					
6	-	C = Puk Case TO-200AB (A-PUK)					
7	-	0 = Eyelet terminals (Gate and Auxiliary Cathode Unsoldered Leads)					
		1 = Fast-on terminals (Gate and Auxiliary Cathode Unsoldered Leads)					
		2 = Eyelet terminals (Gate and Auxiliary Cathode Soldered Leads)					
		3 = Fast-on terminals (Gate and Auxiliary Cathode Soldered Leads)					
8	-	Critical dv/dt: None = 500V/ μ sec (Standard value)					
		L = 1000V/ μ sec (Special selection)					

Outline Table





Fig. 1 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics

ST180C..C Series

Bulletin I25164 rev. C 02/00

International
IRF Rectifier




Fig. 3 - Current Ratings Characteristics




Fig. 4 - Current Ratings Characteristics




Fig. 5 - On-state Power Loss Characteristics




Fig. 6 - On-state Power Loss Characteristics




Fig. 7 - Maximum Non-Repetitive Surge Current
Single and Double Side Cooled




Fig. 8 - Maximum Non-Repetitive Surge Current
Single and Double Side Cooled




Fig. 9 - On-state Voltage Drop Characteristics




Fig. 10 - Thermal Impedance Z_{thJ-hs} Characteristics




Fig. 11 - Gate Characteristics