


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		F	REV PER ECN 0G3B-0514-03	11AUG03	SC	CJ

D


C

B

A



1. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
2. WIRE RANGE: 0.3 – 0.9MM² (22–18 AWG).
3. INSULATION RANGE: 1.50–2.39 [.059–.094] DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
5. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



SECTION A—A
SCALE 20:1

D

C

B

A

794220

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 11AUG2003	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105			
DIMENSIONS: INCHES		CHK C. JONES 11AUG2003				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. JONES 11AUG2003	NAME PIN, MINI UNIVERSAL MATE-N-LOK 2			
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 0.15 [.006] 4 PLC ± ANGLES ± FINISH	PRODUCT SPEC	SIZE A2			
MATERIAL SEE TABLE	SEE TABLE	APPLICATION SPEC	CAGE CODE 00779			
CUSTOMER DRAWING		WEIGHT	DRAWING NO C=794220			
		SCALE 10:1	SHEET 1 OF 1			
			REV F			