


Part Number: 79108-0058

2.00mm Pitch Milli-Grid™ Flex-to-Board Vertical Receptacle Dual Row Through-Hole, 0.76µm Gold (Au) Selective Plating, 18 Circuits, Tin/Lead

Image not available

Status:	OBsolete
Replacement:	791081058
Series:	79108
Category:	FFC/FPC Connectors
Overview:	Milli-Grid™ Connector System

Series image - Reference only

Product Environmental Compliance

EU RoHS: Not RoHS Compliant

China RoHS: 

REACH SVHC: Contains SVHC: No

Low-Halogen Status: Not Reviewed

Part Detail
General

Status	Obsolete
Category	FFC/FPC Connectors
Series	79108
Obsolete Date	2005/06/01
Overview	Milli-Grid™ Connector System
Product Name	Milli-Grid™

Physical

Circuits (Loaded)	18
Contact Position	Top
Durability (mating cycles max)	50
Entry Angle	90° Angle
Number of Rows	2
Orientation	Right Angle
PC Tail Length	1.27mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	0.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +105°C
Termination Interface: Style	Through Hole
Wire/Cable Type	FFC/FPC

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Voltage - Maximum	125V

Solder Process Data

Replacement RoHS Compliant Part Number	0791081058
--	------------

Material Info
Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application
Tooling

[Check our list of old tooling that used to be available for this part](#)

