








RECOMMEND P.C.B. LAYOUT



CIRCUIT, SPST
CONTACT CONFIGURATION

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 50mA, @12V DC
5. TRAVEL: 0.30±0.15mm
6. OPERATING FORCE: 160±50gf
7. CONTACT RESISTANCE: 100 milliohms Max.
8. ELECTRICAL LIFE: 100,000 CYCLES MIN.

E-SWITCH®			
TITLE			
TL 1100 D F160 Q (Was TL 1103)			
SCALE			
2:1			
DATE			
5/10/94			
DR			
MM			
DWG			
P001100			
REV			
C			