


GBU8 Series


Single Phase Bridge Rectifier



Features:

- Glass passivated device offering greater reliability at higher operating temperatures and improved moisture resistance capability.
- High case dielectric strength of 1500V_{RMS}.
- Ideal for printed circuit board.
- Typical I_R less than 0.5μA.
- Surge overload rating : 200 Amperes peak.
- High temperature soldering guaranteed : 260°C/10 seconds, 0.375" (9.5mm) lead length at 5lbs (2.3kg) tension.

GBU



Polarity shown on front side of case, positive lead by beveled corner

Dimensions : Inches (Millimetres)

Mechanical Data:

Case :

GBU8G - Moulded plastic body over passivated junctions.

GBUB, GBUJ, GBUK - Reliable low cost construction utilizing moulded plastic technique.

Terminals :

GBU8G - Plated leads solderable per MIL-STD-750, Method 2026.

GBUB, GBUJ, GBUK - Leads solderable per MIL-STD-202, Method 208.

Mounting position : Any (Note 3).

Mounting torque : 5 in. lb. Maximum.

Weight : 0.15 ounce, 4 grams.

Body		
Height	Width	Depth
18.8	22.3	3.56

Dimensions : Millimetres



GBU8 Series

Single Phase Bridge Rectifier



Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Parameters	Symbols	GBU8B	GBU8G	GBU8J	GBU8K	Units
Maximum repetitive peak reverse voltage	V _{RRM}	100	400	600	800	Volts
Maximum RMS voltage	V _{RMS}	70	280	420	560	
Maximum DC blocking voltage	V dc	100	400	600	800	
Maximum average forward rectified output current at T _C = 100°C (Note 1)	I _(AV)	8.0				Amps
Peak forward surge current single sine-wave superimposed on rated load (JEDEC Method) T _J = 150°C	I _{FSM}	200				
Rating for fusing (t<8.3ms)	I²t	166				A² seconds
Maximum instantaneous forward voltage drop per leg at 8.0A	V _F	1.0				Volts
Maximum DC reverse at rated DC blocking voltage per leg T _A = 25°C T _A = 100°C	I _R	5.0 500				µA
Typical junction capacitance (Note 2)	C _J	211		94.0		pF
Typical thermal resistance per leg (Note 1) (Note 2) (Note 3) (Note 4)	RθJC RθJA RθJL RθJA	2.2 18.0 3.0 21.0				°C/W
Operating and Storage temperature range	T _J , T _{STG}	-55 to +150				°C

Notes:

- Units case mounted on 3.2 x 3.2 x 0.12" thick (8.2 x 8.2 x 0.3cm) Aluminium plate heatsink - **GU8G**.
Units mounted on 3.0 x 3.0 x 0.11" thick (7.5 x 7.5 x 0.3cm) Aluminium plate heatsink - **GU8B, GU8J, GU8K**.
- Measured at 1.0MHz and applied reverse voltage of 4.0 Volts.
- Recommended mounting position is to bolt down on to a heatsink with silicone thermal compound for maximum heat transfer with number 6 screw.
- Units mounted in free air, no heatsink on PCB, 0.5 x 0.5" (12 x 12mm) copper pads, at 0.375" (9.5mm) lead length.


GBU8 Series

Single Phase Bridge Rectifier




Rating and Characteristics Curves

Figure 1 - Derating Curve for Output Rectified Current




GBU8G




GBU8B, GBU8J, GBU8K

Figure 2 - Maximum Non-Repetitive Peak Forward Surge Current per Leg



GBU8G




GBU8B, GBU8J, GBU8K

GBU8 Series


Single Phase Bridge Rectifier



Figure 3 - Typical Instantaneous Forward Characteristics per Element



GBU8G




GBU8B, GBU8J, GBU8K

GBU8 Series


Single Phase Bridge Rectifier



Figure 4 - Typical Reverse Leakage Characteristics per Leg




GBU8G




GBU8B, GBU8J, GBU8K

Figure 5 - Typical Junction Capacitance per Leg



GBU8G




GBU8B, GBU8J, GBU8K

GBU8 Series

Single Phase Bridge Rectifier



Figure 6 - Typical Transient Thermal Impedance



Specifications

V_{RRM} (V)	Maximum Input Voltage (V ac)	I_O at 40°C (A)	I_{FSM} (A)	Current Rating (A)	Part Number
100	70	8	200	8	GBU8B
400	280				GBU8G
600	420				GBU8J
800	560				GBU8K

GBU8 Series

Single Phase Bridge Rectifier



Notes:

International Sales Offices:



AUSTRALIA – Farnell InOne

Tel No: ++ 61 2 9645 8888
Fax No: ++ 61 2 9644 7898



FINLAND – Farnell InOne

Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



NETHERLANDS – Farnell InOne

Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND – Farnell InOne

Tel No: ++ 41 1 204 64 64
Fax No: ++ 41 1 204 64 54



AUSTRIA – Farnell InOne

Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE – Farnell InOne

Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



NEW ZEALAND – Farnell InOne

Tel No: ++ 64 9 357 0646
Fax No: ++ 64 9 357 0656



UK – Farnell InOne

Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



BELGIUM – Farnell InOne

Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY – Farnell InOne

Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NORWAY – Farnell InOne

Tel No: ++ 45 44 53 66 66
Fax No: ++ 45 44 53 66 02



UK – BuckHickman InOne

++ 44 8450 510 150
++ 44 8450 510 130



BRAZIL – Farnell-Newark InOne

Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG – Farnell-Newark InOne

Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



PORTUGAL – Farnell InOne

Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



UK – CPC

++ 44 8701 202 530
++ 44 8701 202 531



CHINA – Farnell-Newark InOne

Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



IRELAND – Farnell InOne

Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



SINGAPORE – Farnell-Newark InOne

Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300



EXPORT – Farnell InOne

Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



DENMARK – Farnell InOne

Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



ITALY – Farnell InOne

Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN – Farnell InOne

Tel No: ++ 34 93 475 8805
Fax No: ++ 34 93 474 5107



ESTONIA – Farnell InOne

Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



MALAYSIA – Farnell-Newark InOne

Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN – Farnell InOne

Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62

<http://www.farnellinone.com>

<http://www.buckhickmaninone.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2004.

