



250VDC/160VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.022	0.157" (4.0mm)	0.354" (9.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.027	0.157" (4.0mm)	0.354" (9.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.033	0.197" (5.0mm)	0.433" (11.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.039	0.197" (5.0mm)	0.433" (11.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.047	0.197" (5.0mm)	0.433" (11.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.056	0.236" (6.0mm)	0.472" (12.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.068	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.082	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.10	0.236" (6.0mm)	0.472" (12.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.12	0.236" (6.0mm)	0.472" (12.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.15	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.18	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.22	0.335" (8.5mm)	0.571" (14.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20

250VDC/160VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.27	0.374" (9.5mm)	0.689" (17.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.33	0.374" (9.5mm)	0.689" (17.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.39	0.335" (8.5mm)	0.669" (17.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.47	0.335" (8.5mm)	0.669" (17.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.56	0.394" (10.0mm)	0.748" (19.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.68	0.394" (10.0mm)	0.748" (19.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.82	0.453" (11.5mm)	0.846" (21.5mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
1.0	0.433" (11.0mm)	0.787" (20.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
1.2	0.512" (13.0mm)	0.866" (22.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
1.5	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
1.8	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
2.2	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18




400VDC/220VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.012	0.157" (4.0mm)	0.354" (9.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.015	0.157" (4.0mm)	0.354" (9.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.018	0.197" (5.0mm)	0.433" (11.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.022	0.197" (5.0mm)	0.433" (11.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.027	0.197" (5.0mm)	0.433" (11.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.033	0.236" (6.0mm)	0.472" (12.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.039	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.047	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.056	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.068	0.236" (6.0mm)	0.472" (12.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.082	0.236" (6.0mm)	0.472" (12.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.10	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.12	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20

400VDC/220VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.15	0.335" (8.5mm)	0.571" (14.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.18	0.276" (7.0mm)	0.630" (16.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.22	0.276" (7.0mm)	0.630" (16.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.27	0.335" (8.5mm)	0.669" (17.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.33	0.394" (10.0mm)	0.748" (19.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.39	0.394" (10.0mm)	0.748" (19.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.47	0.453" (11.5mm)	0.846" (21.5mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.56	0.433" (11.0mm)	0.787" (20.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.68	0.512" (13.0mm)	0.866" (22.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.82	0.512" (13.0mm)	0.866" (22.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
1.0	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
1.2	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18




630VDC/250VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.010	0.157" (4.0mm)	0.354" (9.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.012	0.197" (5.0mm)	0.433" (11.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.015	0.197" (5.0mm)	0.433" (11.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.018	0.197" (5.0mm)	0.433" (11.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.022	0.236" (6.0mm)	0.472" (12.0mm)	0.512" (13.0mm)	0.394" (10.0mm)	20
0.027	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.033	0.236" (6.0mm)	0.472" (12.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.039	0.236" (6.0mm)	0.472" (12.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.047	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.056	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.068	0.335" (8.5mm)	0.571" (14.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.082	0.335" (8.5mm)	0.571" (14.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20

630VDC/250VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.10	0.374" (9.5mm)	0.689" (17.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.12	0.276" (7.0mm)	0.630" (16.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.15	0.335" (8.5mm)	0.669" (17.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.18	0.394" (10.0mm)	0.748" (19.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.22	0.394" (10.0mm)	0.748" (19.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.27	0.453" (11.5mm)	0.846" (21.5mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.33	0.433" (11.0mm)	0.787" (20.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.39	0.512" (13.0mm)	0.866" (22.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.47	0.512" (13.0mm)	0.866" (22.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.56	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
0.68	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
0.82	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18




1000VDC/400VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.0010	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0012	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0015	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0018	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0022	0.236" (6.0mm)	0.472" (12.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0027	0.236" (6.0mm)	0.472" (12.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0033	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0039	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0047	0.335" (8.5mm)	0.571" (14.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0056	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0068	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0082	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.010	0.276" (7.0mm)	0.630" (16.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20

1000VDC/400VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.012	0.335" (8.5mm)	0.669" (17.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.015	0.335" (8.5mm)	0.669" (17.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.018	0.394" (10.0mm)	0.748" (19.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.022	0.394" (10.0mm)	0.748" (19.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.027	0.453" (11.5mm)	0.846" (21.5mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.033	0.433" (11.0mm)	0.787" (20.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.039	0.433" (11.0mm)	0.787" (20.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.047	0.512" (13.0mm)	0.866" (22.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.056	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
0.068	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
0.082	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
0.10	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
0.12	0.709" (18.0mm)	1.299" (33.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18




1250VDC/500VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.0010	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0012	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0015	0.236" (6.0mm)	0.472" (12.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0018	0.236" (6.0mm)	0.472" (12.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0022	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0027	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0033	0.335" (8.5mm)	0.571" (14.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0039	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0047	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0056	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0068	0.276" (7.0mm)	0.630" (16.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20

1250VDC/500VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.0082	0.276" (7.0mm)	0.630" (16.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.010	0.335" (8.5mm)	0.669" (17.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.012	0.394" (10.0mm)	0.709" (18.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.015	0.394" (10.0mm)	0.709" (18.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.018	0.453" (11.5mm)	0.846" (21.5mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.022	0.453" (11.5mm)	0.846" (21.5mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.027	0.433" (11.0mm)	0.787" (20.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.033	0.512" (13.0mm)	0.866" (22.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.039	0.512" (13.0mm)	0.866" (22.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.047	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
0.056	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18



1600VDC/600VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.0010	0.197" (5.0mm)	0.433" (11.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0012	0.236" (6.0mm)	0.472" (12.0mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0015	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0018	0.295" (7.5mm)	0.531" (13.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0022	0.335" (8.5mm)	0.571" (14.5mm)	0.709" (18.0mm)	0.591" (15.0mm)	20
0.0027	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0033	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0039	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0047	0.276" (7.0mm)	0.630" (16.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0056	0.276" (7.0mm)	0.630" (16.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20

1600VDC/600VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.0068	0.335" (8.5mm)	0.669" (17.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0082	0.335" (8.5mm)	0.669" (17.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.010	0.394" (10.0mm)	0.748" (19.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.012	0.453" (11.5mm)	0.846" (21.5mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.015	0.453" (11.5mm)	0.846" (21.5mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.018	0.433" (11.0mm)	0.787" (20.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.022	0.512" (13.0mm)	0.866" (22.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.027	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
0.033	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
0.039	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18



2000VDC/660VAC					
CAP (MFD)	T MAX	H MAX	L MAX	LS ± 0.031" (± 0.8mm)	LEAD AWG
0.0010	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0012	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0015	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0018	0.236" (6.0mm)	0.591" (15.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0022	0.276" (7.0mm)	0.630" (16.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0027	0.276" (7.0mm)	0.630" (16.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0033	0.335" (8.5mm)	0.669" (17.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0039	0.335" (8.5mm)	0.669" (17.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0047	0.394" (10.0mm)	0.748" (19.0mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0056	0.453" (11.5mm)	0.846" (21.5mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0068	0.453" (11.5mm)	0.846" (21.5mm)	1.043" (26.5mm)	0.886" (22.5mm)	20
0.0082	0.433" (11.0mm)	0.787" (20.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.010	0.433" (11.0mm)	0.787" (20.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.012	0.512" (13.0mm)	0.866" (22.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.015	0.512" (13.0mm)	0.866" (22.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	20
0.018	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18
0.022	0.591" (15.0mm)	1.181" (30.0mm)	1.260" (32.0mm)	1.083" (27.5mm)	18

GENERAL SPECIFICATIONS

PHYSICAL CHARACTERISTICS

CONSTRUCTION: FOR VOLTAGE RATINGS BELOW 1000VDC, CONSTRUCTION IS NON-INDUCTIVE WOUND METALLIZED POLYPROPYLENE. FOR VOLTAGE RATINGS 1000VDC AND ABOVE, CONSTRUCTION IS METALLIZED POLYPROPYLENE FILM AND FOIL HYBRID.

CASE: FLAME RETARDANT PREFORMED CASE WITH EPOXY FILL.

LEAD MATERIAL: SOLDER COATED OR TINNED SOLID WIRE. AWG AS SPECIFIED IN TABLES.

DIMENSIONS: AS SPECIFIED IN TABLES. OTHER LEAD LENGTHS, LEAD SPACINGS, AND CRIMP STYLES AVAILABLE UPON REQUEST.

ELECTRICAL CHARACTERISTICS

CAPACITANCE: AS SPECIFIED IN TABLES $\pm$ REQUESTED TOLERANCE WHEN MEASURED AT OR REFERRED TO 1000 ± 20 HZ AND 25 ± 5 °C.

TOLERANCE: $\pm 5\%$, $\pm 10\%$, AND $\pm 20\%$ AVAILABLE. OTHER TOLERANCES AVAILABLE UPON REQUEST.

DISSIPATION FACTOR: SHALL NOT BE GREATER THAN 0.1% FOR VALUES BELOW 1.0 μ F OR 0.2% FOR VALUES 1.0 μ F AND GREATER WHEN MEASURED AT OR REFERRED TO 1000 ± 20 HZ AND 25 ± 5 °C.

INSULATION RESISTANCE: SHALL BE GREATER THAN 9,000 M Ω FOR CAPACITANCE VALUES 0.33 μ F AND LESS OR 3,000 M Ω $\times$ μ F FOR CAPACITANCE VALUES GREATER THAN 0.33 μ F WHEN MEASURED AFTER 1 MINUTE ELECTRIFICATION AT 100VDC AND 25 ± 5 °C.

DIELECTRIC STRENGTH: 150% RATED VOLTAGE FOR 1 MINUTE THROUGH A LIMITING RESISTANCE OF 100 OHMS/VOLT AT 25 ± 5 °C.

RATED VOLTAGE: 250VDC/160VAC, 400VDC/220VAC, 630VDC/250VAC, 1000VDC/400VAC, 1250VDC/500VAC, 1600VDC/600VAC, AND 2000VDC/660VAC AVAILABLE.

TEMPERATURE: -55 °C TO +85 °C AT FULL RATED VOLTAGE.

ADDITIONAL INFORMATION

ORDERING INFORMATION: ALL ASC CAPACITORS ARE ORDERED BY "FAMILY CAP-TOL-VOLT" DESIGNATION. (I.E. TO ORDER AN X378 0.1 μ F, $\pm 10\%$, 1000VDC CAPACITOR, REQUEST PART NUMBER "X378 .1-10-1000")

SEE ALSO: "GENERAL INFORMATION - POLYPROPYLENE CAPACITORS" DOCUMENT FOR ADDITIONAL PHYSICAL, ELECTRICAL, AND PERFORMANCE CHARACTERISTICS NOT MENTIONED IN THIS FILE.

WARNING: INFORMATION ON THIS FILE IS SUBJECT TO CHANGE WITHOUT NOTICE AT ASC'S DISCRETION.

LAST MODIFIED: 09/14/01