


1 Amp. Glass Passivated Fast Recovery Rectifier

Dimensions in mm. DO-41 (Plastic)  Mounting instructions 1. Min. distance from body to soldering point, 4 mm. 2. Max. solder temperature, 350 °C. 3. Max. soldering time, 3.5 sec. 4. Do not bend lead at a point closer than 2 mm. to the body.	Voltage 50 to 600 V. Current 1.0 A. at 75 °C.  • Glass passivated junction • High current capability • The plastic material carries U/L recognition 94 V-0 • Terminals: Axial Leads • Polarity: Color band denotes cathode
--	--

Maximum Ratings, according to IEC publication No. 134


		1N4933GP	1N4934GP	1N4935GP	1N4936GP	1N4937GP
V_{RRM}	Peak recurrent reverse voltage (V)	50	100	200	400	600
$I_{F(AV)}$	Forward current at $T_{amb} = 75\text{ °C}$	1.0 A				
I_{FRM}	Recurrent peak forward current	10 A				
I_{FSM}	8,3 ms. peak forward surge current (Jedec Method)	30 A				
t_{rr}	Max. reverse recovery time from $I_F = 0.5\text{ A}$ $I_R = 1\text{ A}$ $I_{RR} = 0.25\text{ A}$	150 ns				
T_j	Operating temperature range	– 65 to + 175 °C				
T_{stg}	Storage temperature range	– 65 to + 175 °C				
E_{RSM}	Maximum non repetitive peak reverse avalanche energy. $I_R = 0.5\text{ A}$; $T_j = 25\text{ °C}$	20 mJ				

Electrical Characteristics at $T_{amb} = 25\text{ °C}$



V_F	Max. forward voltage drop at $I_F = 1\text{ A}$	1.2 V
I_R	Max. reverse current at V_{RRM} at 25 °C at 125 °C	5 $\mu\text{ A}$ 100 $\mu\text{ A}$
R_{thj-a}	Thermal resistance ($l = 10\text{ mm.}$) Max. Typ.	60 °C/W 45 °C/W

Rating And Characteristic Curves

TYPICAL FORWARD CHARACTERISTIC



FORWARD CURRENT DERATING CURVE

MAXIMUM NON REPETITIVE
PEAK FORWARD SURGE CURRENT

TYPICAL JUNCTION CAPACITANCE

