



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : DDM-208-034 REV: 1.0

2.3" 5*8 Dot Matrix Displays

MODEL NO : ELM-2081SURWA/S530-A2 ECN : Page: 1/5

■ Features :

- Large emitting dot 0.2" diameter.
- Low power/high brightness.

■ Applications:

- Instrument panels
- Digital read out display

■ Description :

- The ELM-2081 series are a large emitting area(5.0mm diameter)LED sources configured in a 40 dots 5*8 matrix array.
- These device is made with white dots and gray surface.

PART NO	CHIP		C.C. or C.A.
	Material	Emitted Color	
ELM-2081SURWA/S530-A2	AlGaInP	Hyper Red	C.C.

OFFICE : NO. 25,Lane 76,Sec.3, Chung Yang Rd., Tucheng 236, Taipei, Taiwan, R.O.C.

TEL : 886-2-2267-2000,2267-9936

FAX : 886-2-2267-6244,22676189,22676306


<http://www.everlight.com>



2.3" 5*8 Dot Matrix Displays

MODEL NO : ELM-2081SURWA/S530-A2 ECN : _____ Page: 2/5

Package Dimension:



NOTES:

- 1.All dimensions are millimeters , tolerance is 0.25mm unless otherwise noted.
 - 2.Above specification may be changed without notice.
- Supplier will reserve authority on material change for above specification.



2.3" 5*8 Dot Matrix Displays

■ Absolute maximum ratings at Ta = 25°C :

Parameter	Symbol	Rating	Unit
Reverse Voltage	V _r	5	V
Forward Current	I _f	25	mA
Operating Temperature	T _{opr}	-40 to +85	°C
Storage Temperature	T _{stg}	-40 to +100	°C
Soldering Temperature	T _{sol}	260 ± 5	°C
Electrostatic Discharge	ESD	2000	V
Power Dissipation	P _d	60	mW
Peak Forward Current(Duty 1/10 @ 1KHZ)	I _f (Peak)	160	mA

■ Electronic optical characteristics :

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition
Luminous Intensity	I _v	1.05	3.2	----	mcd	I _f =2mA
Luminous Intensity	I _v	7.8	21.1	----	mcd	I _f =10mA
Peak Wavelength	λ _p	----	632	----	nm	I _f =20mA
Dominant Wavelength	λ _d	----	624	----	nm	I _f =20mA
Spectrum Radiation Bandwidth	△λ	----	20	----	nm	I _f =20mA
Forward Voltage	V _f	----	2.0	2.4	V	I _f =20mA
Reverse Current	I _r	----	----	10	μA	V _r =5V



REV: 1.0

2.3" 5*8 Dot Matrix Displays

MODEL NO ELM-2081SURWA/S530-A2 ECN: Page: 4/5

Reliability test item and condition:

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 PCS	0/1
2	Temperature Cycle	H : +85°C 30min ∫ 5 min L : -55°C 30min	50 CYCLE	76 PCS	0/1
3	Thermal Shock	H : +100°C 5min ∫ 10 sec L : -10°C 5min	50 CYCLE	76 PCS	0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 PCS	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 PCS	0/1
6	DC Operating Life	If = 10 mA	1000 HRS	76 PCS	0/1
7	High Temperature / High Humidity	85°C /85% RH	1000 HRS	76 PCS	0/1



2.3" 5*8 Dot Matrix Displays

MODEL NO: ELM-2081SURWA/S530-A2 ECN: Page: 5/5

■ Typical Electro-Optical Characteristic Curves:

