


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		Y	REVISED PER ECO-12-011709	26JUN2012	RW	SY

D

C

B

A



- 1 .000050 MIN THK NICKEL UNDERPLATE OVER ENTIRE CONTACT.
- 2 .000150 MIN BRIGHT TIN/LEAD OVER ENTIRE CONTACT.
- 3 .000100 MIN THK BRIGHT TIN/LEAD IN ZONE 1.
- 4 GOLD FLASH IN LOCALIZED GOLD PLATE AREA.
- 5 .000015 MIN GOLD IN LOCALIZED GOLD PLATE AREA
- 6 .000030 MIN GOLD IN LOCALIZED GOLD PLATE AREA
- 7. TO BE APPLIED PER AMP APPLICATION SPEC 114-16015.
- 8. RECOMMENDED HOLE SIZE IS .031-.035 DIA.
- 9 FOR SOLDERABILITY SEE AMP PRODUCT SPEC 108-9024.
- 10 .000150 MIN TIN-LEAD IN ZONE 2.
- 11 AREA TO BE UNPLATED (-9 ONLY).
- 12 GOLD FLASH IN ZONE 1. .000150 MIN TIN IN ZONE 3.
- 13 GOLD FLASH IN ZONE 1.
- 14 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL IN THIS AREA.




D


C


88997

B

A

	1-88997-4
	1-88997-3
	1-88997-2
	88997-9
	88997-5
	88997-4
	88997-3
	88997-2
FINISH	PART NO



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER CHK S. BOLASH APVD M. WALMSLEY PRODUCT SPEC 108-9024 APPLICATION SPEC 114-16015 WEIGHT — CUSTOMER DRAWING	10MAR04 10MAR04 10MAR04	 TE Connectivity		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
	0 PLC ± —	APVD M. WALMSLEY 10MAR04		CONTACT, SOLDER TAB, FFC, .100 ⌀		
	1 PLC ± —	PRODUCT SPEC 108-9024				
	2 PLC ± —	APPLICATION SPEC 114-16015				
	3 PLC ± .005	SIZE A2				
	4 PLC ± —	CAGE CODE 00779				
MATERIAL PH. BRONZE .010 THK	FINISH SEE TABLE	RESTRICTED TO —		DRAWING NO C=88997		
		SCALE 10:1		SHEET 1 of 1		
		REV Y				