



# Leaded Inductors

**Series/Type: B82144A**

The following products presented in this data sheet are being withdrawn.

Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B82144A2984A000		2016-02-26	2016-08-31	2017-02-28
B82144A2686J000		2025-08-22	2026-08-31	2027-02-28
B82144A2685J009		2025-08-22	2026-08-31	2027-02-28
B82144A2686J009		2025-08-22	2026-08-31	2027-02-28



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B82144A2685J000		2025-08-22	2026-08-31	2027-02-28
B82144A2684J009		2025-08-22	2026-08-31	2027-02-28
B82144A2684J000		2025-08-22	2026-08-31	2027-02-28
B82144A2683J009		2025-08-22	2026-08-31	2027-02-28
B82144A2683J000		2025-08-22	2026-08-31	2027-02-28
B82144A2682K009		2025-08-22	2026-08-31	2027-02-28
B82144A2682K000		2025-08-22	2026-08-31	2027-02-28
B82144A2535A300		2016-02-26	2016-08-31	2017-02-28
B82144A2476J009		2025-08-22	2026-08-31	2027-02-28
B82144A2476J000		2025-08-22	2026-08-31	2027-02-28
B82144A2475J009		2025-08-22	2026-08-31	2027-02-28
B82144A2475J000		2025-08-22	2026-08-31	2027-02-28
B82144A2474J009		2025-08-22	2026-08-31	2027-02-28
B82144A2474J000		2025-08-22	2026-08-31	2027-02-28
B82144A2473J009		2025-08-22	2026-08-31	2027-02-28
B82144A2473J000		2025-08-22	2026-08-31	2027-02-28
B82144A2472K009		2025-08-22	2026-08-31	2027-02-28
B82144A2472K000		2025-08-22	2026-08-31	2027-02-28
B82144A2336J009		2025-08-22	2026-08-31	2027-02-28
B82144A2336J000		2025-08-22	2026-08-31	2027-02-28
B82144A2335J009		2025-08-22	2026-08-31	2027-02-28
B82144A2335J000		2025-08-22	2026-08-31	2027-02-28
B82144A2334J009		2025-08-22	2026-08-31	2027-02-28
B82144A2334J000		2025-08-22	2026-08-31	2027-02-28
B82144A2333J009		2025-08-22	2026-08-31	2027-02-28
B82144A2333J000		2025-08-22	2026-08-31	2027-02-28
B82144A2332K009		2025-08-22	2026-08-31	2027-02-28
B82144A2332K000		2025-08-22	2026-08-31	2027-02-28
B82144A2305A500		2016-02-26	2016-08-31	2017-02-28
B82144A2265A000		2016-02-26	2016-08-31	2017-02-28
B82144A2226J009		2025-08-22	2026-08-31	2027-02-28
B82144A2226J000		2025-08-22	2026-08-31	2027-02-28
B82144A2225J009		2025-08-22	2026-08-31	2027-02-28
B82144A2225J000		2025-08-22	2026-08-31	2027-02-28
B82144A2224J009		2025-08-22	2026-08-31	2027-02-28
B82144A2224J000		2025-08-22	2026-08-31	2027-02-28
B82144A2223K009		2025-08-22	2026-08-31	2027-02-28
B82144A2223K000		2025-08-22	2026-08-31	2027-02-28



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B82144A2222K009		2025-08-22	2026-08-31	2027-02-28
B82144A2222K000		2025-08-22	2026-08-31	2027-02-28
B82144A2156J009		2025-08-22	2026-08-31	2027-02-28
B82144A2156J000		2025-08-22	2026-08-31	2027-02-28
B82144A2155J009		2025-08-22	2026-08-31	2027-02-28
B82144A2155J000		2025-08-22	2026-08-31	2027-02-28
B82144A2154J009		2025-08-22	2026-08-31	2027-02-28
B82144A2154J000		2025-08-22	2026-08-31	2027-02-28
B82144A2153K009		2025-08-22	2026-08-31	2027-02-28
B82144A2153K000		2025-08-22	2026-08-31	2027-02-28
B82144A2152K009		2025-08-22	2026-08-31	2027-02-28
B82144A2152K000		2025-08-22	2026-08-31	2027-02-28
B82144A2145A500		2016-02-26	2016-08-31	2017-02-28
B82144A2107J009		2025-08-22	2026-08-31	2027-02-28
B82144A2107J000		2025-08-22	2026-08-31	2027-02-28
B82144A2106J009		2025-08-22	2026-08-31	2027-02-28
B82144A2106J000		2025-08-22	2026-08-31	2027-02-28
B82144A2105J009		2025-08-22	2026-08-31	2027-02-28
B82144A2105J000		2025-08-22	2026-08-31	2027-02-28
B82144A2104J009		2025-08-22	2026-08-31	2027-02-28
B82144A2104J000		2025-08-22	2026-08-31	2027-02-28
B82144A2103K009		2025-08-22	2026-08-31	2027-02-28
B82144A2103K000		2025-08-22	2026-08-31	2027-02-28
B82144A2102K009		2025-08-22	2026-08-31	2027-02-28
B82144A2102K000		2025-08-22	2026-08-31	2027-02-28

Please contact your nearest TDK sales office if you need support in selecting a suitable substitute. The addresses of our worldwide sales network are presented at [www.tdk-electronics.tdk.com/sales](http://www.tdk-electronics.tdk.com/sales).

## LBC series, 5.2 x 12 (mm)


## LBC choke (Large Bobbin Core)

Rated inductance 1 ... 100 000  $\mu$ H

Rated current 20 ... 2200 mA

## Construction

- Large ferrite drum core
- Winding: enamel copper wire
- Flame-retardant lacquer coating



## Features

- Very wide inductance range
- High rated current
- Suitable for wave soldering
- RoHS-compatible

## Applications

- RF blocking and filtering
- Decoupling and interference suppression
- For telecommunications (12- or 16-kHz blocking filter),  
automotive electronics, energy-saving lamps,  
entertainment electronics

## Terminals

- Central axial leads
- Base material CuAg0.1
- Electroplated with nickel and pure tin

## Marking


Inductance indicated by color bands to IEC 60062

## Delivery mode and packing units

- Taped, Ammo and reel packing
- Packing units:


	Ammo (pcs./pack.)	Reel (pcs./reel)
Axial	1250	1500

## Dimensional drawing




Dimensions in mm  
Minimum lead spacing 15 mm

## Packing



n (mm): 72 +1  
w (mm): 84 max

Dimensions in mm



L × W × H (max. mm): 275 × 80 × 140

## Technical data and measuring conditions

Rated inductance $L_R$	Measured with LCR meter Agilent 4284A or impedance analyzer Agilent 4294A Measuring frequency: $L_R \leq 10 \mu\text{H}$ = 1 MHz $10 \mu\text{H} < L_R \leq 4700 \mu\text{H}$ = 100 kHz $L_R > 4700 \mu\text{H}$ = 10 kHz Measuring current: $\leq 1 \text{ mA}$ Measuring temperature: $+20^\circ\text{C}$
Q factor $Q_{\min}$	Measured with precision impedance analyzer Agilent 4294A, $+20^\circ\text{C}$
Rated temperature $T_R$	$+40^\circ\text{C}$
Rated current $I_R$	Maximum permissible DC current at rated temperature
Inductance decrease $\Delta L/L_0$	$\leq 10\%$ (referred to initial value) at $I_R$ , $+20^\circ\text{C}$
DC resistance $R_{\max}$	Measured at $+20^\circ\text{C}$
Resonance frequency $f_{\text{res},\min}$	Measured with Agilent 4294A or 8753ES, $+20^\circ\text{C}$
Solderability (lead-free)	Sn95.5Ag3.8Cu0.7: $+(245 \pm 5)^\circ\text{C}$ , $(3 \pm 0.3) \text{ s}$ Wetting of soldering area $\geq 90\%$ (to IEC 60068-2-20, test Ta)
Resistance to soldering heat	$+(260 \pm 5)^\circ\text{C}$ , 10 s (to IEC 60068-2-20, test Tb)
Tensile strength of leads	$\geq 20 \text{ N}$ (to IEC 60068-2-21, test Ua)
Climatic category	55/125/56 (to IEC 60068-1)
Storage conditions	Mounted: $-55^\circ\text{C} \dots +125^\circ\text{C}$ Packaged: $-25^\circ\text{C} \dots +40^\circ\text{C}$ , $\leq 75\% \text{ RH}$
Weight	Approx. 1.1 g

 Mounting information

When bending the leads, take care that the start-of-winding areas at the face ends (protected by glue and lacquer) are not subjected to any mechanical stress.

## Characteristics and ordering codes

$L_R$ $\mu H$	Tolerance <sup>1)</sup>	$Q_{min}$	$f_Q$ MHz	$I_R$ mA	$R_{max}$ $\Omega$	$f_{res,min}$ MHz	Ordering code (reel packing) <sup>2)</sup>
1.0	$\pm 10\% \triangle K$	40	7.96	2200	0.08	200	B82144A2102K000
1.5		40	7.96	2100	0.09	190	B82144A2152K000
2.2		40	7.96	1900	0.11	140	B82144A2222K000
3.3		40	7.96	1750	0.13	120	B82144A2332K000
4.7		40	7.96	1600	0.16	100	B82144A2472K000
6.8		40	7.96	1500	0.19	80	B82144A2682K000
10		60	2.52	1400	0.22	60	B82144A2103K000
15		60	2.52	1250	0.28	20	B82144A2153K000
22		50	2.52	1100	0.35	12	B82144A2223K000
33	$\pm 5\% \triangle J$	40	2.52	900	0.43	8.0	B82144A2333J000
47		40	2.52	800	0.50	5.0	B82144A2473J000
68		30	2.52	700	0.60	4.5	B82144A2683J000
100		50	0.796	600	0.70	3.5	B82144A2104J000
150		50	0.796	500	0.90	3.0	B82144A2154J000
220		50	0.796	400	1.60	2.4	B82144A2224J000
330		50	0.796	330	1.90	2.0	B82144A2334J000
470		40	0.796	280	2.50	1.5	B82144A2474J000
680		30	0.796	240	2.80	1.3	B82144A2684J000
1000		60	0.252	200	3.80	1.2	B82144A2105J000
1500		60	0.252	160	6.00	1.0	B82144A2155J000
2200		60	0.252	120	9.00	0.8	B82144A2225J000
3300		60	0.252	110	12.0	0.6	B82144A2335J000
4700		60	0.252	90	20.0	0.5	B82144A2475J000
6800		60	0.252	80	30.0	0.4	B82144A2685J000
10000		50	0.0796	60	42.0	0.35	B82144A2106J000
15000		50	0.0796	50	68.0	0.30	B82144A2156J000
22000		50	0.0796	40	120	0.26	B82144A2226J000
33000		50	0.0796	35	150	0.22	B82144A2336J000
47000		40	0.0796	30	230	0.18	B82144A2476J000
68000		40	0.0796	25	290	0.15	B82144A2686J000
100000		30	0.0796	20	420	0.12	B82144A2107J000

1) Closer tolerances on request.


2) For Ammo pack the last digit has to be a »9«. Example: B82144A2102K009

## Characteristics and ordering codes


$L_R$ $\mu H$	Tolerance	$Q_{min}$	$f_Q$ MHz	$I_R$ mA	$R_{max}$ $\Omega$	$f_{res,min}$ MHz	Ordering code (reel packing) <sup>1)</sup>
For telecommunications in the blocking filter for 12-kHz and 16-kHz counting pulses							
980	$\pm 3\% \triangleq A$	25	0.016	200	3.8	1.2	B82144A2984A000
1450		25	0.016	140	6.0	1.0	B82144A2145A500
2600		20	0.012	120	11.0	0.7	B82144A2265A000
3050		25	0.016	100	12.0	0.6	B82144A2305A500
5330		20	0.012	90	25.0	0.5	B82144A2535A300

1) For Ammo pack the last digit has to be a »9«. Example: B82144A2336J009


**Impedance  $|Z|$  versus frequency  $f$**   
 measured with impedance analyzer Agilent 4294A or S-parameter network analyzer Agilent 8753ES, typical values at +20 °C




**Q factor versus frequency  $f$**   
 measured with impedance analyzer Agilent 4294A, typical values at +20 °C



**Inductance  $L$  versus DC load current  $I_{DC}$**   
 measured with LCR meter Agilent 4284A, typical values at +20 °C



**Current derating  $I_{op}/I_R$  versus ambient temperature  $T_A$**   
 (rated temperature  $T_R = +40$  °C)



## Cautions and warnings

- Please note the recommendations in our Inductors data book (latest edition), online catalogs and in the data sheets.
  - Particular attention should be paid to the derating curves, if given. Derating applies in the case the ambient temperature in application exceeds the rated temperature of the component.
  - Ensure the operation temperature of the component in application not to exceed the maximum specified value or the upper climatic category temperature.
  - The soldering conditions should also be observed. Temperatures quoted in relation to wave soldering refer to the pins only. Temperatures specified in relation to reflow soldering can also refer to the pins or terminals for products with larger thermal mass, as in such cases, the temperature difference to the top of the component is too big (e.g., high proportion of core within the component).
- If the components are to be washed or varnished it is necessary to check whether the washing or varnish agent that is used has a negative effect on the wire insulation, any plastics that are used, or on glued joints. It is possible for washing or varnish agent residues to have a negative effect in the long-term on wire insulation.  
Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g. ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.
- The following points must be observed if the components are potted, sealed, or varnished in customer applications:
  - Many potting, sealing, or varnishing materials shrink as they harden. They therefore exert a pressure on the plastic housing or core. This pressure can have a deleterious effect on electrical properties, and in extreme cases can damage the core or plastic housing mechanically.
  - It is necessary to check whether the potting, sealing, or varnishing materials used attack or destroy the wire, wire insulation, plastics or glue.
  - The effect of the potting, sealing, or varnishing materials may change the high-frequency behavior of the components.
  - Many coating materials have a negative effect (chemically and mechanically) on the winding wires, insulation materials and connecting points. Customers are always obliged to determine whether and to what extent their coating materials influence the component. Customers are responsible and bear all risk for the use of the coating material. TDK Electronics does not assume any liability for failures of our components that are caused by the coating material.
- Magnetic core materials such as ferrites are sensitive to direct impact. This can cause the core material to flake or lead to breakage of the magnetic core material.
- Any type of tension or pressure on the product may result in damage and affect its functionality and reliability.
  - The products are only to be attached to fixings or mounting holes provided for this purpose in accordance with the data sheet.
  - If additional mechanical forces are applied to the component, e.g., application of gap pads, it is necessary to check whether they attack or destroy any part of the component.
  - It is not permitted for the product specified in the data sheet to assume a mechanical function in the final application.
- Inductance value can drop if external metallic or magnetic parts will be put close to the coil or into the air gap of the coil or core or magnetic material.
- Even for customer-specific products, conclusive validation of the component in the circuit can only be carried out by the customer.

## Cautions and warnings

### Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. **The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.** Detailed information can be found on the Internet under [www.tdk-electronics.tdk.com/orderingcodes](http://www.tdk-electronics.tdk.com/orderingcodes).

## Important notes

The following applies to all products named in this publication:

- 1 Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that **such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2 We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3 **The warnings, cautions and product-specific notes must be observed.**
- 4 In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet ([www.tdk-electronics.tdk.com/material](http://www.tdk-electronics.tdk.com/material)). Should you have any more detailed questions, please contact our sales offices.
- 5 We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.  
We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6 Unless otherwise agreed in individual contracts, **all orders are subject to our General Terms and Conditions of Supply**.
- 7 **Our manufacturing sites serving the automotive business apply the IATF 16949 standard**. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that **only requirements mutually agreed upon can and will be implemented in our Quality Management System**. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.

## Important notes

8 The trade names EPCOS, CarXield, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, FilterCap, FormFit, InsuGate, LeaXield, MediPlas, MiniBlue, MiniCell, MKD, MKK, ModCap, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PiezoBrush, PlasmaBrush, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SurfIND, ThermoFuse, WindCap, XieldCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at [www.tdk-electronics.tdk.com/trademarks](http://www.tdk-electronics.tdk.com/trademarks).

Release 2024-02