



Series 120 Tubular Solenoid



GENERAL DESCRIPTION

● DC operated



● Noise reduction feature

● Tubular solenoid

PERFORMANCE


Electrical	ITEM	SPECIFICATION
	Closed power (continuous ratings)	4.0W
	Maximum permissible voltage	160V DC
	Dielectric strength	1KV RMS 50Hz
Mechanical	Insulation	1KV
	Weight	Total: 23g Plunger: 4.9g
	Ambient temperature	The information given on this page is based on a working temperature of 20°C.
	Force/stroke curve	This force stroke curve shows average performance only with coil at ambient temperature. In addition to normal manufacturing tolerances, deviations can be expected at some voltages due to the coil winding tolerances.

FORCE/STROKE CURVE AND RESPONSE TIME




DIMENSIONS (mm)

Push type - shown energised



Pull type - shown energised

Thread: 0.375" - 32 UNEF



Leads: 26 AWG UL1007
Length: 152.0 minimum

COIL DATA

Pull Type	Push Type	Resistance (20°C) Ω ±10%	Cont. (100%) Vdc	50% Vdc	25% Vdc	10% Vdc
120 420 610 540	120 420 620 540	9	6	8.5	12	19
120 420 610 620	120 420 620 620	36	12	17	24	38
120 420 610 720	120 420 620 720	144	24	34	48	76
Watts at 20°C			4	8	16	40
Max. on time (Secs)			∞	50	5	2

Other voltages available on request

Duty cycle (%) =

“ON” time

“ON” time + “OFF” time

x 100%

