


P.C.JACK-CLOSED ENTRY-SWAGE MOUNT

09-9051-X-XX

P.C. JACK FOR .016 THRU .019

BASIC PART NO. FINISH

OR .020 ONLY PINS*



PART NO.	L	BOARD THK.
09-9051-1	.041	1/32
09-9051-2	.072	1/16
09-9051-3	.104	3/32
09-9051-4	.135	1/8

INSTALLATION TOOLS

ANVIL	PUNCH
TA94-62-20	TP72-T40


RECOMMENDED MOUNTING HOLE .076±.002(#48 DRILL)

*ONCE AN .020 PIN IS INSERTED, THE USE OF .016 THRU .019 PINS IS NO LONGER RECOMMENDED.

09-9035-X-XX

P.C. JACK FOR .025 PIN

BASIC PART NO. FINISH



*FOR -1 ONLY .040

PART NO.	L	BOARD THK.
09-9035-1	.062	1/32
09-9035-2	.094	1/16
09-9035-3	.125	3/32
09-9035-4	.156	1/8

INSTALLATION TOOLS


ANVIL	PUNCH
TA94-62-20	TP72-T40

RECOMMENDED MOUNTING HOLE .067±.002(#51 DRILL)

09-9045-X-XX

P.C. JACK FOR .025 PIN

BASIC PART NO. FINISH



PART NO.	L	A	H	BOARD THK.
09-9045-2	.094	.062	.106	1/16
09-9045-3	.125	.031	.075	3/32
09-9045-4	.156	.031	.075	1/8
09-9045-6	.219	.031	.075	3/16

INSTALLATION TOOLS


ANVIL	PUNCH
TA125-77-31	TP92-T62

RECOMMENDED MOUNTING HOLE .094±.002/-.001 DIA.(#42 DRILL)

09-9037-X-XX

P.C. JACK FOR .030, .031 AND .032 PINS*

BASIC PART NO. FINISH



PART NO.	L	BOARD THK.
09-9037-1	.062	1/32
09-9037-2	.094	1/16
09-9037-3	.125	3/32
09-9037-4	.156	1/8
09-9037-6	.219	3/16

INSTALLATION TOOLS

ANVIL	PUNCH
TA125-94-23	TP93-T66


RECOMMENDED MOUNTING HOLE .094±.002/-.001(#42 DRILL)

*INTERCHANGING OF .030, .031 AND .032 SIZED PINS IS NOT RECOMMENDED FOR REPEATED USAGE

09-9020-X-XX

P.C. JACK FOR .025 PIN

BASIC PART NO. FINISH



PART NO.	L	BOARD THK.
09-9020-1	.062	1/32
09-9020-2	.094	1/16
09-9020-3	.125	3/32
09-9020-4	.156	1/8

INSTALLATION TOOLS


ANVIL	PUNCH
TA94-74-45	TP62-44

RECOMMENDED MOUNTING HOLE .062±.002

09-9004-X-XX

P.C. JACK FOR .040 PIN

BASIC PART NO. FINISH



PART NO.	L	BOARD THK.
09-9004-1	.062	1/32
09-9004-2	.094	1/16
09-9004-3	.125	3/32
09-9004-4	.156	1/8
09-9004-6	.219	3/16

INSTALLATION TOOLS

ANVIL	PUNCH
TA125-94-23	TP93-T66

RECOMMENDED MOUNTING HOLE .094±.002/-.001 DIA.(#42 DRILL)

MATERIAL

Body: Brass per ASTM B16

Spring Contact: Beryllium Copper per ASTM B194

FINISH

Part Number/Finish Code	Body Finish	Spring Contact Finish
09-9XXX-X-03	Gold per ASTM B488	Gold per ASTM B488
04	Electro-Tin per ASTM B545	Electro-Tin per ASTM B545
06	Electro-Tin per ASTM B545	Gold per ASTM B488
063	Bright Tin-Lead per ASTM B545	Gold per ASTM B488
088	Bright Tin-Lead per ASTM B545	Bright Tin-Lead per ASTM B545

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

CONCORD