

MATERIALS AND FINISHES




BODY: BRASS
PLATED NICKEL

CONTACT FEMALE: PHOSPHOR BRONZE
PLATED TIN

CONTACT MALE: BRASS
PLATED TIN

INSULATORS: POLYPROPYLENE

GASKET/O-RING: SILICONE RUBBER



PART # 73100-0079

PS-89675-3640	ELEC/MECH PERFORMANCE
SPECIFICATION	DESCRIPTION

CHG: REDREW IN SD
AND LOADED INTO
WM.
EC NO: URF2009-0736
DRAWN: ROBERTSON 2009/06/10
CHKD: SSS 2009/06/10
APPR: JWIENER 2009/06/10
REV B1

QUALITY
SYMBOLS
=0
=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± ---
2 PLACES ± --- ± ---
1 PLACE ± --- ± ---
ANGULAR ± 2 °
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN
DRAWN BY DATE
CM DENG 1993/07/08
CHECKED BY DATE
R FIELDS 1993/07/08
APPROVED BY DATE
MATERIAL NO.
731000079
SIZE C

SCALE
DESIGN UNITS
METRIC
THIRD ANGLE
PROJECTION
F JACK
RECEPTACLE
F-JR
molex MOLEX INCORPORATED
DOCUMENT NO.
SD-73100-0079
SHEET NO.
1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION