


DESIGNED & DIMENSIONED
IN MILLIMETERS
(INCHES FOR REFERENCE ONLY)

DO NOT
SCALE FROM
THIS PRINT



MEC6-1XX-XX-X-DV-XX

No OF POSITIONS

-10, -20, -30, -40,
-50, -60, -70

CARD THICKNESS
-02: 1.57mm [.062]
THICK CARD

PLATING SPECIFICATION



-L: LIGHT SELECTIVE GOLD/MATTE TIN (USE C-182-02-L)
-S: SELECTIVE GOLD/MATTE TIN (USE C-182-02-S)

OPTION

-A: ALIGNMENT PINS (SEE FIG. 3)
(USE MEC6-XX-XX-DV-A)
-LC: LOCKING CLIP
(USE LC-05-TM)
-K: POLYIMIDE FILM PAD
(USE K-DOT-.217-.313-.005)(SEE FIG. 4)
-TR: TAPE & REEL

ROW SPECIFICATION

-DV: DUAL VERTICAL
(USE MEC6-XX-XX-DV)



SECTION "A"-"A"

FIG 1
-LC OPTION SHOWN
MEC6-130-02-X-DV-LC SHOWN
(FOR POSITIONS -10, -20, -30 & -40)

TABLE 1

No OF POS	COPLANARITY
-10 THRU -50	0.102 [.0040]
-60 & -70	0.152 [.0060]

NOTES:

1. Ⓢ REPRESENTS A CRITICAL DIMENSION.
2. MAXIMUM BURR ALLOWANCE: 0.038[.0015].
3. MINIMUM PUSHOUT FORCE: 2.22 N [.5 LB].
4. PARTS TO BE PACKAGED IN TRAYS, UNLESS -TR OPTION IS SPECIFIED.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN MILLIMETERS.

TOLERANCES ARE:

DECIMALS ANGLES
.X: ± 0.3 [.01] 2°
.XX: ± 0.13 [.005]
.XXX: ± 0.051 [.0020]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING
INSULATOR: LCP, COLOR: BLACK
CONTACT: PHOS BRONZE

SHEET SCALE: 1:0.4

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.635mm VERTICAL MOUNT MINI-EDGE CARD ASSEMBLY

DWG. NO.
MEC6-1XX-XX-X-DV-XX

BY: DEAN P 05/17/2005 SHEET 1 OF 2

REVISION F






FIG 2

MEC6-150-02-X-DV-A SHOWN
FOR POSITIONS -50 THRU 70
(SAME AS FIG 1, UNLESS OTHERWISE STATED)

TABLE 2

No OF POS	"A" REF	"B"	"C"	"D" REF
-50	21.055[.8289]	30	19.050[.7500]	36.490[1.4366]
-60	24.865[.9789]	36	22.860[.9000]	42.840[1.6866]
-70	28.675[1.1289]	42	26.670[1.0500]	49.190[1.9366]

FIG 3

-A OPTION

MEC6-140-02-X-DV-A SHOWN
(FOR POSITIONS -10, -20, -30 & -40)




FIG 4

-K OPTION
(USE K-DOT-.217-.313-.005)




TABLE 3

No OF POS	"R"	"S"
-10 THRU -40	(No OF POS x 0.635[.0250]) + 4.77[.188] REF	(("R" - 5.50[.217]) / 2) +/- 0.51[.020]
-50 THRU -70	(No OF POS x 0.635[.0250]) + 7.94[.313] REF	

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1:0.444444

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.635mm VERTICAL MOUNT MINI-EDGE CARD ASSEMBLY

DWG. NO.
MEC6-1XX-XX-X-DV-XX

BY: DEAN P 05/17/2005 SHEET 2 OF 2