

## 7-outlet, 6-ft cord, 1080 joule strip, RJ11 protection - Protect It! Surge Suppressor

MODEL NUMBER: **SUPER6TEL**



### Description

Tripp Lite's SUPER6TEL surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. High-grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. SUPER6TEL offers 7 total outlets, 6 foot cord with a space-saving right angle plug and diagnostic LEDs to warn of wiring problems and suppressor damage. Heavy grade AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive white suppressor housing with keyhole mounting tabs and 3 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$50,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only). PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/6-ft. AC line cord ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle) FORMAT: Corded multi-outlet strip with 3 transformer spaced outlets SUPPRESSION: AC: 150V RMS Clamping/1080 joules/400V UL1449 Let-through Phone: Single telephone line surge suppression (RJ11 jacks, 2 wire, 1 line)

### Features

- 1080 joules AC surge suppression shields equipment from the strongest surges and line noise
- 7 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ11 jacks, 2 wire, 1 line, includes 6 ft phone cable)
- 6 foot cord with space-saving right-angle plug
- Built-in power switch and 15 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- UL1449 3rd Edition Rated (400V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$50,000 Ultimate Lifetime connected equipment insurance (U.S., Canada, and Puerto Rico only)

### Specifications

### Highlights

- 7 outlets / 6-ft. cord
- 1080 joule rating
- Modem/fax surge protection
- \$50,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)

### Applications

- Ideal for any desktop, network or home computing application requiring AC and dialup or DSL modem line protection.

### Package Includes

- SUPER6TEL Surge Suppressor
- 6-ft. telephone cord
- Instruciton manual with warranty information

#### OVERVIEW

Intended Application	Home/Office
Style	Strip

#### OUTPUT

Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Circuit Breaker (amps)	15
Outlet Quantity / Type	7 NEMA 5-15R
Number of Outlets	7
Transformer Accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 5 transformers total
Outlet Orientation	Single row of 5, plus 2 side mounted outlets

#### INPUT

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000

#### LEDS ALARMS & SWITCHES

Switches	Two position on/off power switch
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green) status

#### SURGE / NOISE SUPPRESSION

AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Up to 20 dB

DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	12.40 x 5.90 x 1.77
Shipping Dimensions (hwd / cm)	31.50 x 14.99 x 4.50
Shipping Weight (lbs.)	1.56
Shipping Weight (kg)	0.71
Unit Dimensions (hwd / in.)	1.54 x 2.72 x 10.3
Unit Dimensions (hwd / cm)	3.91 x 6.91 x 26.16
Unit Weight (lbs.)	1.39
Unit Weight (kg)	0.63
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Outlets Measurement (Center to Center)	Between Standard Outlets = 29mm; Between Transformer Outlets = 48mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between slots = 78mm; Distance between slot height = 24mm
SPECIAL FEATURES	
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications

#### **WARRANTY**

Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 <a href="#">Ultimate Lifetime Insurance</a>

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.