



**●Features**

- 1) Open structure built in for superior flame retardance characteristics.
- 2) Advanced wire bonding technology enable to make compact packages.
- 3) Eco-friendly halogen-free products.
- 4) Screening by thermal shock.

**●Dimensions****●Part No. Explanation**

① Series name

TCFG

② Case style

B : 3528-21 (1411) size

③ Rated voltage

Rated voltage (V)	4	6.3	10	16	20	25
CODE	0G	0J	1A	1C	1D	1E

④ Nominal capacitance

Nominal capacitance in pF in 3 digits:  
2 significant figures followed by the figure  
representing the number of 0's.

⑤ Capacitance tolerance

M : ± 20%

⑥ Taping

8 : Reel width : 8mm  
R : Positive electrode on the side opposite to sprocket hole

\*This specification has possibility of change, due to underdevelopment product.

Please ask for latest specification to our sales.

### ●Rated table

Capacitance ( $\mu$ F)	Rated voltage (V.DC)					
	4	6.3	10	16	20	25
3.3 (335)				B		B
4.7 (475)				B		B
10 (106)				B	B	
15 (156)				B		
22 (226)		B	B	B		
33 (336)		B	B	B		
47 (476)		B	B			
100 (107)	B	B	B			
220 (227)	B	B				
330 (337)	☆B					

Remark) Case size codes (B) in the above show products line-up.

☆ Under development

### ●Marking

The indications listed below should be given on the surface of a capacitor.

- (1) Polarity : The polarity should be shown by □ bar. (on the anode side)
- (2) Rated DC voltage : A voltage code is shown as below table.
- (3) Capacitance : A capacitance code is shown as below table.


Visual typical example

voltage code and capacitance code are variable with parts number.

[B case]

EX.)  $\frac{10}{(1)} \frac{16V}{(2)}$



(1) capacitance (2) voltage



## ●Characteristics

Item		Performance							Test conditions (based on JIS C5101-1 and JIS C5101-3)															
Operating Temperature	-55 °C to +125 °C							Voltage reduction when temperature exceeds +85°C																
Maximum operating temperature with no voltage derating	+85 °C																							
Rated Voltage (V.DC)	4	6.3	10	16	20	25		at 85°C																
Category Voltage (V.DC)	2.5	4	6.3	10	13	16		at 125°C																
Surge Voltage	5.0	8	13	20	26	32		at 85°C																
DC leakage current	Shall be satisfied the value on "Standard list"							As per 4.9 JIS C 5101-1 As per 4.5.1 JIS C 5101-3 Voltage : Rated voltage for 1 min																
Capacitance tolerance	Shall be satisfied allowance range. ±20%							As per 4.7 JIS C 5101-1 As per 4.5.2 JIS C 5101-3 Measuring frequency : 120±12Hz Measuring voltage : 0.5Vrms, +1.5V.DC Measuring circuit : DC Equivalent series circuit																
Tangent of loss angle (Df, tanδ)	Shall be satisfied the value on "Standard list"							As per 4.8 JIS C 5101-1 As per 4.5.3 JIS C 5101-3 Measuring frequency : 120±12Hz Measuring voltage : 0.5Vrms, +1.5V.DC Measuring circuit : DC Equivalent series circuit																
Impedance	Shall be satisfied the value on "Standard list"							As per 4.10 JIS C 5101-1 As per 4.5.4 JIS C 5101-3 Measuring frequency : 100±10kHz Measuring voltage : 0.5Vrms or less Measuring circuit : DC Equivalent series circuit																
Resistance to soldering heat	Appearance	There should be no significant abnormality. The indications should be clear.							As per 4.14 JIS C 5101-1 As per 4.6 JIS C 5101-3															
	L.C	TCFGB0G227M8R : Less than 150% of initial limit TCFGB0J227M8R : Less than 150% of initial limit TCFGB1A107M8R : Less than 150% of initial limit TCFGB1E475M8R : Less than 150% of initial limit Others : Less than initial limit							Dip in the solder bath Solder temp : 260±5°C Duration : 5±0.5s Repetition : 1 After the specimens, leave it at room temperature for over 24h and then measure the sample.															
	ΔC / C	TCFGB0G227M8R : Within ±15% of initial value TCFGB0J227M8R : Within ±15% of initial value TCFGB1A107M8R : Within ±15% of initial value TCFGB1E475M8R : Within ±10% of initial value Others : Within ± 5% of initial value																						
	tanδ	3.3 to 33μF : Less than initial limit 47 to 150μF : Less than 150% of initial limit TCFGB0G227M8R : Less than 150% of initial limit TCFGB0J227M8R : Less than 150% of initial limit TCFGB1A107M8R : Less than 150% of initial limit TCFGB1C336M8R : Less than 150% of initial limit																						
Fail-Safe open unit actuation		Within 320°C – 20s							Dip in the solder bath Solder temp : 320±5°C															
Temperature cycle	Appearance	There should be no significant abnormality.							As per 4.16 JIS C 5101-1 As per 4.10 JIS C 5101-3															
	L.C	TCFGB0G227M8R : Less than 150% of initial limit TCFGB0J227M8R : Less than 200% of initial limit TCFGB1A107M8R : Less than 200% of initial limit TCFGB1E475M8R : Less than 150% of initial limit Others : Less than initial limit							Repetition : 5 cycles (1 cycle : steps 1 to 4) without discontinuation.															
	ΔC / C	TCFGB0G227M8R : Within ±15% of initial value TCFGB0J227M8R : Within ±20% of initial value TCFGB1A107M8R : Within ±20% of initial value Others : Within ±10% of initial value							<table border="1"> <thead> <tr> <th>Step</th><th>Temp.</th><th>Time</th></tr> </thead> <tbody> <tr> <td>1</td><td>-55±3°C</td><td>30±3min</td></tr> <tr> <td>2</td><td>Room temp.</td><td>3min. or less</td></tr> <tr> <td>3</td><td>125±2°C</td><td>30±3min</td></tr> <tr> <td>4</td><td>Room temp.</td><td>3min. or less</td></tr> </tbody> </table>		Step	Temp.	Time	1	-55±3°C	30±3min	2	Room temp.	3min. or less	3	125±2°C	30±3min	4	Room temp.
Step	Temp.	Time																						
1	-55±3°C	30±3min																						
2	Room temp.	3min. or less																						
3	125±2°C	30±3min																						
4	Room temp.	3min. or less																						
tanδ	3.3 to 33μF : Less than initial limit 47 to 150μF : Less than 150% of initial limit TCFGB0G227M8R : Less than 150% of initial limit TCFGB0J227M8R : Less than 200% of initial limit TCFGB1A107M8R : Less than 200% of initial limit TCFGB1C336M8R : Less than 150% of initial limit							After the specimens, leave it at room temperature for over 24h and then measure the sample.																

Item		Performance	Test conditions (based on JIS C 5101-1 and JIS C 5101-3)
Moisture resistance	Appearance	There should be no significant abnormality. The indications should be clear.	As per 4.22 JIS C 5101-1 As per 4.12 JIS C 5101-3
	L.C	TCFGB0G227M8R : Less than 150% of initial limit TCFGB0J227M8R : Less than 200% of initial limit TCFGB1A107M8R : Less than 200% of initial limit TCFGB1E475M8R : Less than 150% of initial limit Others : Less than initial limit	After leaving the sample under such atmospheric condition that the temperature and humidity are $40\pm2^\circ\text{C}$ and 90 to 95%RH, respectively, for $500\pm12\text{h}$ level it at room temperature for over 24h and then measure the sample.
	$\Delta C / C$	TCFGB0G227M8R : Within $\pm15\%$ of initial value TCFGB0J227M8R : Within $\pm20\%$ of initial value TCFGB1A107M8R : Within $\pm20\%$ of initial value Others : Within $\pm10\%$ of initial value	
	$\tan\delta$	3.3 to $33\mu\text{F}$ : Less than initial limit 47 to $150\mu\text{F}$ : Less than 150% of initial limit TCFGB0G227M8R : Less than 150% of initial limit TCFGB0J227M8R : Less than 200% of initial limit TCFGB1A107M8R : Less than 200% of initial limit TCFGB1C336M8R : Less than 150% of initial limit	
	Temp.	-55°C	As per 4.29 JIS C 5101-1 As per 4.13 JIS C 5101-3
	$\Delta C / C$	TCFGB0G227M8R : Within 0/-15% of initial value TCFGB0J227M8R : Within 0/-30% of initial value TCFGB1A107M8R : Within 0/-30% of initial value Others : Within 0/-12% of initial value	
	$\tan\delta$	Shall be satisfied the value on Table5	
	L.C	—	
	Temp.	+85°C	
Temperature Stability	$\Delta C / C$	TCFGB0G227M8R : Within $+12/0\%$ of initial value TCFGB0J227M8R : Within $+15/0\%$ of initial value TCFGB1A107M8R : Within $+15/0\%$ of initial value Others : Within $+10/0\%$ of initial value	
	$\tan\delta$	Shall be satisfied the value on Table5	
	L.C	Less than 1000% of intial limit	
	Temp.	+125°C	
	$\Delta C / C$	TCFGB0J227M8R : Within $+20/0\%$ of initial value TCFGB1A107M8R : Within $+20/0\%$ of initial value TCFGB1C336M8R : Within $+20/0\%$ of initial value Others : Within $+15/0\%$ of initial value	
	$\tan\delta$	Shall be satisfied the value on Table5	
	L.C	Less than 1250% of initial limit	
	Appearance	There should be no significant abnormality. The indications should be clear.	As per 4.26 JIS C 5101-1 As per 4.14 JIS C 5101-3
	L.C	TCFGB0G227M8R : Less than 150% of initial limit TCFGB0J227M8R : Less than 200% of initial limit TCFGB1A107M8R : Less than 200% of initial limit TCFGB1E475M8R : Less than 150% of initial limit Others : Less than initial limit	Apply the specified surge voltage via the serial resistance of $1\text{k}\Omega$ every $5\pm0.5\text{min}$ . for $30\pm5$ s. each time in the atmospheric condition of $85\pm2^\circ\text{C}$ . Repeat this procedure 1,000 times. After the specimens, leave it at room temperature for over 24h and then measure the sample.
Surge Voltage	$\Delta C / C$	TCFGB0G227M8R : Within $\pm15\%$ of initial value TCFGB0J227M8R : Within $\pm20\%$ of initial value TCFGB1A107M8R : Within $\pm20\%$ of initial value Others : Within $\pm10\%$ of initial value	
	$\tan\delta$	3.3 to $33\mu\text{F}$ : Less than initial limit 47 to $150\mu\text{F}$ : Less than 150% of initial limit TCFGB0G227M8R : Less than 200% of initial limit TCFGB0J227M8R : Less than 200% of initial limit TCFGB1A107M8R : Less than 200% of initial limit TCFGB1C336M8R : Less than 150% of initial limit	


Item		Performance	Test conditions (based on JIS C 5101-1 and JIS C 5101-3)
Loading at High temperature	Appearance	There should be no significant abnormality. The indications should be clear.	As per 4.23 JIS C 5101-1 As per 4.15 JIS C 5101-3
	L.C	TCFGB0G227M8R : Less than 150% of initial limit TCFGB0J227M8R : Less than 200% of initial limit TCFGB1A107M8R : Less than 200% of initial limit TCFGB1E475M8R : Less than 150% of initial limit Others : Less than initial limit	After applying the rated voltage for 2000+72/0h without discontinuation via the serial resistance of 3Ω or less at a temperature of 85±2°C, leave the sample at room temperature/humidity for 1 to 2h and measure the value. After the specimens, leave it at room temperature for over 24h and then measure the sample.
	ΔC / C	TCFGB0G227M8R : Within ±15% of initial value TCFGB0J227M8R : Within ±20% of initial value TCFGB1A107M8R : Within ±20% of initial value Others : Within ±10% of initial value	
Terminal Strength	tanδ	3.3 to 33μF : Less than initial limit 47 to 100μF : Less than 150% of initial limit TCFGB0G227M8R : Less than 200% of initial limit TCFGB0J227M8R : Less than 200% of initial limit TCFGB1A107M8R : Less than 200% of initial limit TCFGB1C336M8R : Less than 150% of initial limit	
	Capacitance	The measured value should be stable.	As per 4.35 JIS C 5101-1 As per 4.9 JIS C 5101-3
	Appearance	There should be no significant abnormality.	A force is applied to the terminal until it bends to 1mm and by a prescribed tool maintain the condition for 5s. (See the figure below.)
			
Adhesiveness		The terminal should not come off.	As per 4.34 JIS C 5101-1 As per 4.8 JIS C 5101-3 Apply force of 5N in the two directions shown in the figure below for 10±1s after mounting the terminal on a circuit board.
			
Dimensions		Be based on "External dimensions"	Measure using a caliper of JIS B 7505 Class 2 or higher grade.
Resistance to solvents		The indication should be clear.	As per 4.32 JIS C 5101-1 As per 4.18 JIS C 5101-3 Dip in the isopropyl alcohol for 30±5s, at room temperature.
Solderability		3/4 or more surface area of the solder coated terminal dipped in the soldering bath should be covered with the new solder.	As per 4.15.2 JIS C 5101-1 As per 4.7 JIS C 5101-3 Dip speed = 25±2.5mm/s Pre-treatment (accelerated aging) : Leave the sample on the boiling distilled water for 1h. Solder temp. : 245±5°C Duration : 3±0.5s Solder : M705 Flux : Rosin 25%, IPA 75%
Vibration	Capacitance	Measure value should not fluctuate during the measurement.	As per 4.17 JIS C 5101-1 Frequency : 10 to 55 to 10Hz/min. Amplitude : 1.5mm Time : 2h each in X and Y directions Mounting : The terminal is soldered on a print circuit board.
	Appearance	There should be no significant abnormality.	

## ●Standard products list


Part No.	Rated voltage 85°C (V)	Category voltage 125°C (V)	Surge voltage 85°C (V)	Cap. 120Hz (μF)	Tolerance (%)	Leakage current 25°C 1WV.60s (μA)	Df 120Hz (%)			Impedance 100kHz (Ω)
							-55°C	25°C 85°C	125°C	
TCFG B 0G 107 M8R	4	2.5	5	100	± 20	4.0	30	12	16	1.6
TCFG B 0G 227 M8R	4	2.5	5	220	± 20	8.8	40	20	30	1.3
* TCFG B 0G 337 M8R	4	2.5	5	330	± 20	66	60	30	45	1.3
TCFG B 0J 226 M8R	6.3	4	8	22	± 20	1.4	12	8	10	2.5
TCFG B 0J 336 M8R	6.3	4	8	33	± 20	2.1	12	8	10	2.0
TCFG B 0J 476 M8R	6.3	4	8	47	± 20	3.0	14	10	12	1.9
TCFG B 0J 107 M8R	6.3	4	8	100	± 20	6.3	30	12	16	1.5
TCFG B 0J 227 M8R	6.3	4	8	220	± 20	70	60	30	45	1.3
TCFG B 1A 226 M8R	10	6.3	13	22	± 20	2.2	12	8	10	2.0
TCFG B 1A 336 M8R	10	6.3	13	33	± 20	3.3	14	10	12	1.9
TCFG B 1A 476 M8R	10	6.3	13	47	± 20	4.7	14	10	12	1.6
TCFG B 1A 107 M8R	10	6.3	13	100	± 20	20	40	20	30	1.5
TCFG B 1C 335 M8R	16	10	20	3.3	± 20	0.5	10	6	8	4.2
TCFG B 1C 475 M8R	16	10	20	4.7	± 20	0.8	10	6	8	3.0
TCFG B 1C 106 M8R	16	10	20	10	± 20	1.6	10	6	8	2.5
TCFG B 1C 156 M8R	16	10	20	15	± 20	2.4	10	6	8	2.0
TCFG B 1C 226 M8R	16	10	20	22	± 20	3.5	10	6	8	1.9
TCFG B 1C 336 M8R	16	10	20	33	± 20	5.3	16	14	16	1.9
TCFG B 1D 106 M8R	20	13	26	10	± 20	2.0	12	8	10	15.0
TCFG B 1E 335 M8R	25	16	32	3.3	± 20	0.83	10	6	8	4.2
TCFG B 1E 475 M8R	25	16	32	4.7	± 20	1.2	10	6	8	3.0

\* = Under development

## ●Packaging specifications



## ●Reel dimensions



## Notes

- 1) The information contained herein is subject to change without notice.
- 2) Before you use our Products, please contact our sales representative and verify the latest specifications :
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Products beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
- 7) The Products specified in this document are not designed to be radiation tolerant.
- 8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 9) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 11) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrant that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting from non-compliance with any applicable laws or regulations.
- 13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations.  
More detail product informations and catalogs are available, please contact us.

### ROHM Customer Support System

<http://www.rohm.com/contact/>