




Technical drawing of a U-shaped part. The drawing shows a cross-section of a U-shaped component with a flat base and two vertical sides. The dimensions and tolerances are as follows:

- Top left dimension: $3.56^{+0.13}_{-0.25}$
- Top right dimension: $3.30^{+0.25}_{-0.13}$ TYP
- Left side dimension: $[.140^{+.005}_{-.010}]$
- Right side dimension: $[.130^{+.010}_{-.005}]$

SECTION B-B

- | |
|----------|
| OBSOLETE |
| OBSOLETE |
| OBSOLETE |

STANDARD		CU-NI ALLOY	1-66359-9	1-66361-6
STANDARD		CU-NI ALLOY	1-66359-7	1-66361-5
STANDARD		CU-NI ALLOY	1-66359-6	1-66361-4
SMALL PACK		BRASS	1-66359-4 OR 1-66359-8	1-66361-3
STANDARD		BRASS	1-66359-4 OR 1-66359-8	1-66361-2
SMALL PACK		BRASS	66359-4	1-66361-1
SMALL PACK		BRASS	66359-2	1-66361-0
E- STANDARD		BRASS	1-66359-3	66361-9
E- STANDARD		PHOSPHOR BRONZE	1-66359-2	66361-8
E- STANDARD		PHOSPHOR BRONZE	1-66359-1	66361-7
STANDARD		BRASS	66359-4	66361-4
STANDARD		BRASS	66359-3	66361-3
STANDARD		BRASS	66359-2	66361-2
STANDARD		BRASS	66359-1	66361-1
PACKAGING	BODY FINISH	BODY MATERIAL	STRIP P/N REF	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 06/03/92		 TE Connectivity			
		CHK W.LENKER 6-11-92					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PIN ASSEMBLY, LOOSE PIECE, TYPE III+			
		APVD G.STEINHAUER 7-8-92					
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE CALLOUTS		SEE TABLE		A2	00779	C-66361	—
CUSTOMER DRAWING				SCALE	SHEET		REV
				8:1	1 OF 1		K1