



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		B	REVISED PER ECO 07-002853	21MAR2007	DW	JL



PCB CONFIGURATION

- 1 ZINC PER QQ-Z-363.
- 2 PTFE PER ASTM D 1710.
- 3 COPPER-IRON ALLOY PER ASTM B 465.
- 4 COPPER PER QQ-C-576.
- 5 COPPER-NICKEL ALLOY PER ASTM B 122.
- 6 NICKEL PLATE PER QQ-N-290
3.81 μm [.000150] MINIMUM THICK.
- 7 GOLD PLATE PER ASTM B 488
0.76 μm [.000030] MINIMUM THICK.
- 8 TIN PLATE PER ASTM B 545,
2.54 μm [.000100] MIN THICK.
- 9 BERYLLIUM COPPER PER ASTM B 643.
- 10. INTERFACE DIMENSIONS PER LUCENT SPEC WP-92009.
- 11. CONNECTOR PRESS FIT IS DESIGNED TO PROVIDE 100 LB. MINIMUM AXIAL RETENTION TO PCB COMPLIANT WITH TYCO APPLICATION SPEC 114-12001. AS A RESULT, DEFORMATION OF PLATED THROUGH HOLES WILL OCCUR. CUSTOMER VALIDATION AND ACCEPTANCE OF THIS DEFORMATION IS RECOMMENDED PRIOR TO SPECIFYING USE OF THIS PRODUCT.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ—DOCK5 CHK J. HAVENER APVD J. LIPPERT 22APR2005 22APR2005 22APR2005		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105—3608				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME				
		0 PLC ± —		JACK, PCB, HIGH RETENTION				
		1 PLC ± —		PRESS FIT, 75 OHM, BNC				
		2 PLC ± 0.05 [.002]						
		3 PLC ± —						
4 PLC ± —		APPLICATION SPEC						
ANGLES ± —		—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL		FINISH		WEIGHT	A2 00779 C=5414088			—
NOTES 1–5, 9		NOTES 6–8		CUSTOMER DRAWING				SCALE 5:1
						SHEET 1 of 1		REV B

5414088-1
PART NUMBER