




LOC	DIST	REVISIONS					
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECO-11-004820	11MAR11	RK	HMR



RECOMMENDED HOLE LAYOUT

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.

 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.

 HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.

5 FINISH: 0.00254-0.00508 [.000100-.000200] BRIGHT TIN-LEAD
OVER 0.00127 [.000050] NICKEL ENTIRE POST.

6 FINISH: 0.00254-0.00508 [.000100-.000200] MATTE TIN
OVER 0.00127 [.000050] NICKEL ENTIRE POST.

6	101.19 [3.984]	99.06 [3.900]	39	80	9-146505-0
6	98.65 [3.884]	96.52 [3.800]	38	78	8-146505-9
6	96.11 [3.784]	93.98 [3.700]	37	76	8-146505-8
6	93.57 [3.684]	91.44 [3.600]	36	74	8-146505-7
6	91.03 [3.584]	88.90 [3.500]	35	72	8-146505-6
6	88.49 [3.484]	86.36 [3.400]	34	70	8-146505-5
6	85.95 [3.384]	83.82 [3.300]	33	68	8-146505-4
6	83.41 [3.284]	81.28 [3.200]	32	66	8-146505-3
6	80.87 [3.184]	78.74 [3.100]	31	64	8-146505-2
6	78.33 [3.084]	76.20 [3.000]	30	62	8-146505-1
6	75.79 [2.984]	73.66 [2.900]	29	60	8-146505-0
6	73.25 [2.884]	71.12 [2.800]	28	58	7-146505-9
6	70.71 [2.784]	68.58 [2.700]	27	56	7-146505-8
6	68.17 [2.684]	66.04 [2.600]	26	54	7-146505-7
6	65.63 [2.584]	63.50 [2.500]	25	52	7-146505-6
6	63.09 [2.484]	60.96 [2.400]	24	50	7-146505-5
6	60.55 [2.384]	58.42 [2.300]	23	48	7-146505-4
6	58.01 [2.284]	55.88 [2.200]	22	46	7-146505-3
6	55.47 [2.184]	53.34 [2.100]	21	44	7-146505-2
6	52.93 [2.084]	50.80 [2.000]	20	42	7-146505-1
6	50.39 [1.984]	48.26 [1.900]	19	40	7-146505-0
6	47.85 [1.884]	45.72 [1.800]	18	38	6-146505-9
6	45.31 [1.784]	43.18 [1.700]	17	36	6-146505-8
6	42.77 [1.684]	40.64 [1.600]	16	34	6-146505-7
6	40.23 [1.584]	38.10 [1.500]	15	32	6-146505-6
6	37.69 [1.484]	35.56 [1.400]	14	30	6-146505-5
6	35.15 [1.384]	33.02 [1.300]	13	28	6-146505-4
6	32.61 [1.284]	30.48 [1.200]	12	26	6-146505-3
6	30.07 [1.184]	27.94 [1.100]	11	24	6-146505-2
6	27.53 [1.084]	25.40 [1.000]	10	22	6-146505-1
6	24.99 [.984]	22.86 [.900]	9	20	6-146505-0
6	22.45 [.884]	20.32 [.800]	8	18	5-146505-9
6	19.91 [.784]	17.78 [.700]	7	16	5-146505-8
6	17.37 [.684]	15.24 [.600]	6	14	5-146505-7
6	14.83 [.584]	12.70 [.500]	5	12	5-146505-6
6	12.29 [.484]	10.16 [.400]	4	10	5-146505-5
6	9.75 [.384]	7.62 [.300]	3	8	5-146505-4
6	7.21 [.284]	5.08 [.200]	2	6	5-146505-3
6	4.67 [.184]	2.54 [.100]	1	4	5-146505-2
6	2.13 [.084]	-	-	2	5-146505-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

△ ₅	101.9 [3.984]	99.06 [3.900]	39	80	4-146505-0
△ ₅	98.65 [3.884]	96.52 [3.800]	38	78	3-146505-9
△ ₅	96.11 [3.784]	93.98 [3.700]	37	76	3-146505-8
△ ₅	93.57 [3.684]	91.44 [3.600]	36	74	3-146505-7
△ ₅	91.03 [3.584]	88.90 [3.500]	35	72	3-146505-6
△ ₅	88.49 [3.484]	86.36 [3.400]	34	70	3-146505-5
△ ₅	85.95 [3.384]	83.82 [3.300]	33	68	3-146505-4
△ ₅	83.41 [3.284]	81.28 [3.200]	32	66	3-146505-3
△ ₅	80.87 [3.184]	78.74 [3.100]	31	64	3-146505-2
△ ₅	78.33 [3.084]	76.20 [3.000]	30	62	3-146505-1
△ ₅	75.79 [2.984]	73.66 [2.900]	29	60	3-146505-0
△ ₅	73.25 [2.884]	71.12 [2.800]	28	58	2-146505-9
△ ₅	70.71 [2.784]	68.58 [2.700]	27	56	2-146505-8
△ ₅	68.17 [2.684]	66.04 [2.600]	26	54	2-146505-7
△ ₅	65.63 [2.584]	63.50 [2.500]	25	52	2-146505-6
△ ₅	63.09 [2.484]	60.96 [2.400]	24	50	2-146505-5
△ ₅	60.55 [2.384]	58.42 [2.300]	23	48	2-146505-4
△ ₅	58.01 [2.284]	55.88 [2.200]	22	46	2-146505-3
△ ₅	55.47 [2.184]	53.34 [2.100]	21	44	2-146505-2
△ ₅	52.93 [2.084]	50.80 [2.000]	20	42	2-146505-1
△ ₅	50.39 [1.984]	48.26 [1.900]	19	40	2-146505-0
△ ₅	47.85 [1.884]	45.72 [1.800]	18	38	1-146505-9
△ ₅	45.31 [1.784]	43.18 [1.700]	17	36	1-146505-8
△ ₅	42.77 [1.684]	40.64 [1.600]	16	34	1-146505-7
△ ₅	40.23 [1.584]	38.10 [1.500]	15	32	1-146505-6
△ ₅	37.69 [1.484]	35.56 [1.400]	14	30	1-146505-5
△ ₅	35.15 [1.384]	33.02 [1.300]	13	28	1-146505-4
△ ₅	32.61 [1.284]	30.48 [1.200]	12	26	1-146505-3
△ ₅	30.07 [1.184]	27.94 [1.100]	11	24	1-146505-2
△ ₅	27.53 [1.084]	25.40 [1.000]	10	22	1-146505-1
△ ₅	24.99 [.984]	22.86 [.900]	9	20	1-146505-0
△ ₅	22.45 [.884]	20.32 [.800]	8	18	146505-9
△ ₅	19.91 [.784]	17.78 [.700]	7	16	146505-8
△ ₅	17.37 [.684]	15.24 [.600]	6	14	146505-7
△ ₅	14.83 [.584]	12.70 [.500]	5	12	146505-6
△ ₅	12.29 [.484]	10.16 [.400]	4	10	146505-5
△ ₅	9.75 [.384]	7.62 [.300]	3	8	146505-4
△ ₅	7.21 [.284]	5.08 [.200]	2	6	146505-3
△ ₅	4.67 [.184]	2.54 [.100]	1	4	146505-2
△ ₅	2.13 [.084]	-	-	2	146505-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO. BRANDBERG 11-NOV-96		 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHG. NO. G. DUBNICZKI 11-NOV-96 APP'D. G. DUBNICZKI 11-NOV-96			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 0.51[.02] 3 PLC ± 0.127[.005] 4 PLC ± 0.0254[.001] ANGLES ± 0.025°[.001]		NAME		PRODUCT SPEC APPLICATION SPEC	
MATERIAL  SEE TABLE		WEIGHT —		SIZE CASE CODE DRAWING NO A1 00779 C-146505	
		CUSTOMER DRAWING		RESTRICTED TO — SCALE 4:1 SHEET 1 OF 1 REV A	