





LOC		DIST		REVISONS			
AA		00		DESCRIPTION	DATE	DWN	APVD
L1		REV PER ECO-09-021826			07JAN10	KK	AEG

- MATERIAL:
HOUSING: GLASS FILLED POLYESTER; COLOR: BLACK.
CONTACT: PHOS BRONZE
- FINISH:
0.00076[.000030] MIN GOLD PLATE IN CONTACT AREA,
0.00254[.000100] MIN TIN-LEAD ON SOLDER POSTS, ALL
OVER 0.00127[.000050] MIN NICKEL
- AMP LOGO, TE PART NUMBER, DATE CODE AND CSA LOGO INK
STAMPED WHITE (HOT STAMPED OR LAZER PRINTED) IN THE APPROXIMATE
AREA SHOWN, EITHER SIDE PERMISSABLE, WHEN HOUSING SIZE PERMITS
- DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- OBsolete PARTS: OBsolete CIS STREAMLINING PER D.RENAUD/D.SINISI



SUPERCEDED	145539-6
SUPERCEDED	145539-4
OBsolete	145539-3

PART NUMBER

31.57 [1.243]	59.51 [2.343]	57.15 [2.250]	2,3,33,34, 37,38,68,69	3.18 [.125]	-	23,24	35	145539-7
77.29 [3.043]	13.79 [.543]	11.43 [.450]	2,3,33,34, 37,38,68,69	3.18 [.125]	67	5,6	35	145539-5
31.57 [1.243]	59.51 [2.343]	57.15 [2.250]	-	3.81 [.150]	14	23,24	35	145539-2
82.37 [3.243]	8.71 [.343]	6.35 [.250]	-	3.81 [.150]	5	3,4	35	145539-1
C	B	A	RETENTION FEATURE LOCATION	W	OMITTED PIN	MOLDED-IN KEYING FEATURE LOCATED BETWEEN PINS	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.M./L.A.MAYER 09JUL99	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	
		1 P/LC ± .005	CONNECTOR ASSEMBLY,	
		2 P/LC ± .015 [.005]	STANDARD EDGE II, KEYED, 35 DUAL	
		3 P/LC ± .015 [.005]	2.54 [.100] CENTERLINE	
MATERIAL SEE NOTE 1	FINISH SEE NOTE 2	4 P/LC ± .015 [.005]	SIZE	
		5 P/LC ± .015 [.005]	CAGE CODE	
		6 P/LC ± .015 [.005]	DRAWING NO	
		RESTRICTED TO		
		WEIGHT	A1 00779	
		CUSTOMER DRAWING	SCALE 5:1	
			SHEET 1 OF 1	
			REV L1	