


[illegible]

Stud	L	M
Short stud 2-56	0.29 [7.4]	0.45 [11.43]
Long stud 2-56	0.36 [9.1]	0.52 [13.21]
Stud M2.5	0.18 [4.6]	0.34 [8.6]

Note: unit in inch [mm]

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL		DATE		Amphenol	
U.S. METRIC		DRAWN ALEX.LEE		07/18/05			
.X +/- .020 0.51		CHECKED TSUI		07/18/05			
.XX +/- .010 0.25		CHECKED					
.XXX +/- .008 0.13							
FRACTIONS +/-						TITLE	
ANGLES +/- 2.5° 2.5°						816 Protected Header	
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE : DRAWING 816.CB16.DWG					
REMOVE SHARP EDGES		ANGLE OF PROJECTION				SIZE DRAWING NO. REV.	
DIMENSIONS				A3 C816-XXXX-XXX		T	
U.S.	INCHES						
METRIC	MM						
				SCALE	NONE	SHEET	1 OF 2

This document is the property of Amphenol Corporation and is loaned on the express condition that it is not to be distributed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without the prior express written consent. No right is granted to disclose or to use any information in this document.

ORDERING INFORMATION

E 842 - 816 - XX XX - X XX X

Date code _____
Nil - No date code
E - Date code printed Δ

No. of contact _____

Body & pin configuration
(Refer to Table III)

Lock & Eject (L&E) and mounting stud options

0 - no L&E, no stud
1 - short L&E, no stud
2 - short L&E, short stud
3 - short L&E, long stud
4 - long L&E, no stud
5 - long L&E, short stud
6 - long L&E, long stud
F - long L&E, M2.5 stud


Nil - standard
S - standard with polarizing
key slot for size 10 Δ

Plating
AA - gold flash duplex
19 - 15 ? gold plated duplex
35 - 30 ? gold plated duplex

Table III

Standard product - four side grey	Non-standard product - three side grey (specific quantity required)	K
30 - straight solder tail, for 0.062" [1.6 mm] PCB	20 - obsolete	0.109 ± 0.007 [2.61 ± 0.34] coined tail
31 - straight solder tail, for 0.125" [3.2 mm] PCB	21 - obsolete	0.171 ± 0.009 [4.14 ± 0.36] coined tail
32 - right angle solder tail, for 0.062" [1.6 mm] PCB	22 - obsolete	0.109 ± 0.007 [2.61 ± 0.34] coined tail
33 - right angle solder tail, for 0.125" [3.2 mm] PCB	23 - obsolete	0.171 ± 0.009 [4.14 ± 0.36] coined tail
37 - straight wire wrap tail	27 - obsolete	0.61 ± 0.015 [15.49 ± 0.38] square tail
39 - right angle wire wrap tail	29 - obsolete	0.61 ± 0.015 [15.49 ± 0.38] square tail

Recommended PCB layout



REVISIONS

SYM	ECN	DESCRIPTION	DATE	APPROVED
		SEE SHEET 1		

Notes:

- Connectors purchased under this drawing will mate with MIL-C-83503/7B socket connector with strain relief or without strain relief and Amphenol's 812 connector.
- This assembly is designed to meet requirements of MIL-C-83503.
- Δ The polarizing key slot on this end does not exist on size 10 and 14.
- Δ Prefix "E" only applies to the four-sided version & polarizing key slot is available for all size including size 10.
- Δ Suffix "S" only applies to the size 10 since the polarizing key slot is absent from the standard size 10.
- This connector is both UL and CSA approved.
- Refer to Amphenol 5-816-001 for product specification.
- MATERIAL SHOULD BE FULFILLED AMPHENOL SPEC#SSN001.

Table IV

Size	A	B	C	D	E	F
10	1.26 [32.07]	1.10 [27.94]	0.860 [21.84]	0.708 [17.98]	0.400 [10.16]	4
14	1.46 [37.08]	1.30 [33.02]	1.080 [26.92]	0.908 [23.06]	0.600 [15.24]	6
16	1.56 [39.62]	1.40 [35.56]	1.160 [29.46]	1.008 [25.60]	0.700 [17.78]	7
20	1.76 [44.70]	1.60 [40.64]	1.360 [34.54]	1.208 [30.68]	0.900 [22.86]	9
28	2.06 [52.32]	1.90 [48.26]	1.660 [42.16]	1.508 [38.30]	1.200 [30.40]	12
30	2.26 [57.40]	2.10 [53.34]	1.860 [47.24]	1.708 [43.38]	1.400 [35.56]	14
34	2.46 [62.48]	2.30 [58.42]	2.060 [52.32]	1.908 [48.46]	1.600 [40.64]	16
40	2.76 [70.10]	2.60 [66.04]	2.360 [59.94]	2.208 [56.08]	1.900 [48.26]	18
50	3.26 [82.80]	3.10 [78.74]	2.860 [72.64]	2.708 [68.78]	2.400 [60.96]	24
60	3.76 [95.50]	3.60 [91.44]	3.360 [85.34]	3.208 [81.48]	2.900 [73.66]	28
64	3.96 [100.58]	3.80 [96.52]	3.560 [90.42]	3.408 [86.60]	3.100 [78.74]	31

Customer Drawing

UNLESS OTHERWISE SPECIFIED TOLERANCES U.S. METRIC X +/- .020 0.51 3X +/- .010 0.25 30X +/- .008 0.13 FRACTIONS +/- 2.5 2.5 ANGLES +/- 2.5 2.5	APPROVAL DRAWN ALEXJEE CHECKED TSUN CHECKED	DATE 07/18/04 07/18/04	TITLE 816 Protected Header
FOR MATERIALS AND FINISHES SEE NOTES REMOVE SHARP EDGES	DRAWING FILE: DRAWING\816\816.DWG	ANGLE OF PROJECTION 	SIZE DRAWING NO. A3 C816-XXXX-XXX
DIMENSIONS U.S. INCHES METRIC MM			REY. T
			SCALE NONE SHEET 2 OF 2