

FNA Series

13/32" x 1-1/2" 250Vac Pin indicating time-delay supplemental fuses



Description

Pin indicating time-delay supplemental fuse.

Catalog symbol / color code

- FNA - Green (250Vac max voltage 1/10 to 6A)
- Blue (125Vac max voltage 6-1/4 to 15A)
- Grey (32Vac max voltage 20 to 30A)

Ratings

Fuse Amp Range	Interrupting Rating at System Voltage			Agency Information	
	250 Vac	125 Vac	32 Vac	UL	CSA
1/10 to 8/10	35A	10kA	-	X	X
1 to 6	200A	10kA	-	X	X
6-1/4 to 15	-	10kA	-	X	X
20 to 30	-	-	1kA	-	-

Agency information

- CE
- UL Listed 1/10 to 8/10A @ 125/250Vac, 1-15A @ 125Vac, Guide JDYX, File E19180
- CSA Certified 1/10 to 10A @ 125Vac, Class 1422-01, File 53787


Catalog numbers (amps)

FNA-1/10	FNA-1	FNA-3	FNA-9
FNA-1/8	FNA-1-1/8	FNA-3-2/10	FNA-10
FNA-15/100	FNA-1-1/4	FNA-3-1/2	FNA-12
FNA-2/10	FNA-1-4/10	FNA-4	FNA-15
FNA-1/4	FNA-1-1/2	FNA-4-1/2	FNA-20
FNA-3/10	FNA-1-6/10	FNA-5	FNA-25
FNA-4/10	FNA-1-8/10	FNA-5-6/10	FNA-30
FNA-1/2	FNA-2	FNA-6	
FNA-6/10	FNA-2-1/4	FNA-6-1/4	
FNA-3/4	FNA-2-1/2	FNA-7	
FNA-8/10	FNA-2-8/10	FNA-8	

Carton quantity

Amps	Qty.
1/10 to 30	10

Dimensions - in



Features

- Color coded by maximum voltage rating
- Pin indication for visual indication of open fuse condition
- Dual-element, time-delay performance permits close sizing on control transformers and relays
- Silver-plated pin for positive, electrical signal activation
- 12 amp and more versions are dual-tube construction

Typical applications

- Power electronic circuits with high inrush currents and fuse openings must be quickly apparent
- Inductive load circuits where pin indication of open fuse condition is desired

Recommended fuse blocks/fuse holders


Series	Description	Data Sheet #
Blocks		
BMM Series	1-, 2- & 3-Pole modular blocks with optional covers	10235
BM Series	1-, 2- & 3-Pole blocks	1104
3839	4-Pole signaling block	*
Panel Mount Holders		
HPF-C	1-Pole holder**	2114
Fuseclips		
1A3400, 5956 & 5960 Series	PCB Fuseclips	2132

* Call Bussmann Application Engineering for details.

** 1/10 to 10A single tube fuses only.

Bussmann
by **EATON**

Time-current characteristic curves – average melt



The only controlled copy of this Data Sheet is the electronic read-only version located on the Bussmann Network Drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Eaton's Bussmann Business

114 Old State Road
Ellisville, MO 63021
United States
www.Bussmann.com

© 2014 Eaton
All Rights Reserved
Publication No. 2029 - BU-SB14292
April 2014

Eaton is a registered trademark.

All other trademarks are property of their respective owners.