

Customer Information Sheet

DRAWING No.: M50-490XX45

SHEET 2 OF 2


IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



SPECIFICATIONS:

MATERIAL:

MOULDING = LCP UL94V-0, BLACK

CONTACT = COPPER ALLOY

FINISH:

CONTACT = GOLD

ELECTRICAL:

CURRENT RATING = 1A

VOLTAGE PROOF = 300V AC/DC

CONTACT RESISTANCE = 20m Ω MAX

INSULATION RESISTANCE = 1,000M Ω MIN

MECHANICAL:

DURABILITY = 100 CYCLES MIN

ENVIRONMENTAL:

OPERATING TEMPERATURE = -40°C TO +105°C

PACKING:

TUBE

FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C029XX (LATEST ISSUE)

ORDER CODE:

M50-490XX45

No. OF CONTACTS PER ROW: 05 TO 50

FINISH: GOLD ALL OVER CONTACT

SB	8	27.08.13	11873
NAME	ISS.	DATE	C/NOTE
APPROVED: S.BENNETT			
CHECKED: S.FLOWER			
DRAWN: J. ENRIGHT			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES

X = ± 1 mm
X.X = ± 0.25 mm
X.XX = ± 0.10 mm
X.XXX = ± 0.01 mm
ANGLES = $\pm 5^\circ$
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE:

1.27mm PITCH DIL
SMT PIN HEADER ASSY

DRAWING NUMBER:

M50-490XX45

SHT
2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[M50-4902345](#) [M50-4903145](#) [M50-4902745](#) [M50-4903945](#) [M50-4901545](#) [M50-4903745](#) [M50-4901345](#) [M50-4902545](#) [M50-4901745](#) [M50-4902945](#) [M50-4903345](#) [M50-4902145](#) [M50-4904045](#) [M50-4900645](#) [M50-4900845](#) [M50-4900745](#) [M50-4900945](#) [M50-4900545](#) [M50-4901445](#) [M50-4903845](#) [M50-4902645](#) [M50-4903045](#) [M50-4901845](#) [M50-4903445](#) [M50-4901045](#) [M50-4902245](#) [M50-4902045](#) [M50-4903245](#) [M50-4902845](#) [M50-4901645](#) [M50-4903645](#) [M50-4901245](#) [M50-4902445](#) [M50-4901945](#) [M50-4903545](#) [M50-4901145](#) [M50-4905045](#)