

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		D1	ECR-13-017177	05NOV13	PKS	RRP

D

C

B

A



- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08[.220±.003] CENTERS
- 2 SLOT TERMINATES EITHER A SINGLE OR DOUBLE MAGNET WIRE OF THE SAME SIZE AND TYPE. COPPER RANGE: 0.36_0.57mm [#27-#23] AWG.
- 3 AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.
- 4 VARNISH RESIST OVER TIN PER MIL-T-10727.
- 5 TIN PLATED

D

C

B

A

5	63664-2
4	63664-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 8/26/92	 TE Connectivity										
DIMENSIONS: INCHES		CHK JEFF R. RUTH 8/26/92											
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME NELSON E. NEFF 8/28/92		TERMINAL, TAB, 4.75 [.187] FASTON, MAG-MATE								
	0 PLC ± -												
	1 PLC ± -												
	2 PLC ± 0.25 [.010]												
	3 PLC ± -												
	4 PLC ± -												
	ANGLES ± -												
	FINISH												
MATERIAL BRASS		SEE TABLE		WEIGHT -		A2		00779		DRAWING NO C-63664		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 10:1		SHEET 1 of 1		REV D1					