



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 6602: ADDED NOTES, REVISED FORMAT, LOGO, COLOR	1/14/13	D.FRISIELLO
F	ECN 7241: ADDED 1.0 FT LENGTH, REVISED ROHS AND FORMAT	1/20/14	D.FRISIELLO



SECTION A-A

SUPPLIED WITH THUMBSCREWS IN PLACE.
NOTE: SUPPLIED WITH OPTIONAL USE HARDWARE AND INSTRUCTIONS.
CABLE INTERCONNECTION HARDWARE: (4) SCREWLOCKS, H= .191"
PANEL MOUNT HARDWARE: (4) SCREWLOCKS, H= .160"

NOTES:


1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

WIRING MAP		
J1	WIRE COLOR	P1
1	BLACK	1
2	GRAY	2
3	RED	3
4	GREEN	4
5	BROWN	5
6	BLUE	6
7	ORANGE	7
8	YELLOW	8
9	PURPLE	9
SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FEET	METERS
CRMN9MF-1	1.0	0.31
CRMN9MF-2.5	2.5	0.76
CRMN9MF-5	5.0	1.52
CRMN9MF-10	10.0	3.05
CRMN9MF-15	15.0	4.57
CRMN9MF-25	25.0	7.62

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13]	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY T CLARK	3/10/2004			CATEGORY D-SUBMINIATURE	
	CHECKED BY D PARHAM	3/10/2004				
	APPROVED BY C McCORMICK	3/31/2004	PRODUCT DESCRIPTION CA, DB9M / DB9F REVERSIBLE HDWR			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. CRMN9MF	REV. F
	COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: CRMN9MF.SLDDRW	SHEET 1 OF 1	
	CRMN-FS01					