






SPECIFICATIONS					
WIRING	INPUT		OUTPUT		
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD	
				MAX. AMPS	MAX. KVA
SINGLE PHASE	120	50/60	0-140	4	0.56

UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ±

DECIMALS	Holes	ANGLES	DRAFT	UNITS
.XX, .XXX, .005	.06, .002, .01	1°	1-1/2°	IN [mm]

MATERIAL: ALL DIMENSIONS APPLY AFTER PLATING

The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.

DRAWN BY
S.A. SMITH

CHECKER

ENGINEER

DATE
6/4/96

DATE

DATE

FIRST USED ON
3PNJ401B

WEIGHT APPROX.
21 LBS

SCALE
1=1

DO NOT SCALE DWG.

CODE IDENT. NO.
83008

SHEET 1 OF 1

CUSTOMER APPROVAL

DATE

TITLE:
SPEC. CONTROL DRAWING
VARIABLE TRANSFORMER
MODEL: 3PNJ401B

STACO
ENERGY PRODUCTS CO.
A COMPONENTS CORPORATION OF AMERICA COMPANY
DAYTON, OHIO U.S.A.

DWG. NO.
031-8875

DWG. SIZE
D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

[3PNJ401B](#)