

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

REVISIONS

| P | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
|   | H   | REVISED PER ECO-15-011611 | 05NOV2015 | NK  | MZ   |
|   | J   | REVISED PER ECO-17-013721 | 15NOV2017 | RS  | MZ   |

2.5  
[.10]  
REF

FREE DIA

STYLE B  
(MALE)

LENGTH  
MIN

2.5[.10]  
REF

STYLE C  
(STRIP)

LH  
(LOUVER HEIGHT)

1

FINISH-SILVER PLATE 200μIN THICK MIN.

2

FINISH-NICKEL PLATE 40μIN THICK MIN.

3

FINISH-GOLD PLATE 10μIN THICK MIN.

4

FINISH-GOLD PLATE 20μIN THICK MIN.

5

PLATING NOTES ARE TO BE INTERPRETED AS FOLLOWS, 3-2 AS 3 OVER 2.

6

PRODUCT IS SOLD BY THE FOOT.

7

72 INCH STRIP WOUND TO A ONE INCH INSIDE DIAMETER.

8

MATERIAL-BeCu (CDA172).

9

PRELIMINARY PART NUMBER

10

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

|                                        |               |          |        |        |              |                |                    |          |                                         |            |            |            |  |  |  |  |  |  |
|----------------------------------------|---------------|----------|--------|--------|--------------|----------------|--------------------|----------|-----------------------------------------|------------|------------|------------|--|--|--|--|--|--|
| OBSOLETE                               | B             | .375     | --     | [.014] | 8            | 9.5[.375]      | 4-2                | 40       | 0.10[.004]                              | --         | 2-192048-6 |            |  |  |  |  |  |  |
| 10                                     | OBSOLETE      | B        | [.06]  | --     | [.012]       | 8              | 1.7[.067]          | 1-2      | 5                                       | 0.10[.004] | 2-192048-5 |            |  |  |  |  |  |  |
|                                        | B             | [.20]    | --     | [.014] | --           | --             | 3-2                | 20       | 0.10[.004]                              | --         | 2-192048-4 |            |  |  |  |  |  |  |
| 10                                     | OBSOLETE      | --       | --     | --     | --           | --             | --                 | --       | --                                      | --         | 2-192048-3 |            |  |  |  |  |  |  |
|                                        | --            | --       | --     | --     | --           | --             | --                 | --       | --                                      | --         | 2-192048-2 |            |  |  |  |  |  |  |
|                                        | B             | [.06]    | --     | [.012] | 8            | --             | UNPL               | 5        | 0.10[.004]                              | --         | 2-192048-1 |            |  |  |  |  |  |  |
|                                        | C             | --       | NOTE 6 | [.014] | 8            | --             | UNPL               | --       | 0.10[.004]                              | --         | 2-192048-0 |            |  |  |  |  |  |  |
| OBSOLETE                               | NOT AVAILABLE |          |        |        |              |                |                    |          |                                         |            | 06802      | 1-192048-9 |  |  |  |  |  |  |
| OBSOLETE                               | B             | [.65]    | --     | [.012] | 8            | 16.6[.655]     | 2                  | 71       | 0.10[.004]                              | 06050      | 1-192048-8 |            |  |  |  |  |  |  |
| 10                                     | B             | [.65]    | --     | [.012] | 8            | 16.6[.655]     | UNPL               | 71       | 0.10[.004]                              | 06049      | 1-192048-7 |            |  |  |  |  |  |  |
| OBSOLETE                               | NOT AVAILABLE |          |        |        |              |                |                    |          |                                         |            | 06036      | 1-192048-6 |  |  |  |  |  |  |
| OBSOLETE                               | B             | [.59]    | --     | [.012] | 8            | 15.2[.600]     | UNPL               | 65       | 0.10[.004]                              | 06030      | 1-192048-5 |            |  |  |  |  |  |  |
|                                        | B             | [.28]    | --     | [.012] | 8            | 7.3[.288]      | UNPL               | 30       | 0.10[.004]                              | 06028      | 1-192048-4 |            |  |  |  |  |  |  |
| 10                                     | B             | [.16]    | --     | [.012] | 8            | 4.4[.175]      | 3-2                | 17       | 0.10[.004]                              | 06038      | 1-192048-3 |            |  |  |  |  |  |  |
|                                        | B             | [.16]    | --     | [.012] | 8            | 4.4[.175]      | UNPL               | 17       | 0.10[.004]                              | 06039      | 1-192048-2 |            |  |  |  |  |  |  |
|                                        | B             | [.13]    | --     | [.016] | 8            | 3.2[.127]      | 4-2                | 11       | 0.10[.004]                              | 06031      | 1-192048-1 |            |  |  |  |  |  |  |
|                                        | B             | [.13]    | --     | [.016] | 8            | 3.2[.127]      | UNPL               | 11       | 0.10[.004]                              | 06034      | 1-192048-0 |            |  |  |  |  |  |  |
| OBSOLETE                               | B             | --       | --     | [.016] | 8            | 3.2[.127]      | 4-2                | 11       | 0.08[.003]                              | 06072      | 192048-9   |            |  |  |  |  |  |  |
| 10                                     | B             | [.13]    | --     | [.016] | 8            | 3.2[.127]      | UNPL               | 11       | 0.08[.003]                              | 06071      | 192048-8   |            |  |  |  |  |  |  |
|                                        | B             | [.06]    | --     | [.012] | 8            | 1.7[.067]      | 4-2                | 5        | 0.10[.004]                              | 06060      | 192048-7   |            |  |  |  |  |  |  |
| OBSOLETE                               | B             | [.05]    | --     | [.016] | 8            | 1.3[.051]      | 4-2                | 4        | 0.10[.004]                              | 06058      | 192048-6   |            |  |  |  |  |  |  |
| 10                                     | OBSOLETE      | B        | [.05]  | --     | [.016]       | 8              | 1.3[.051]          | UNPL     | 4                                       | 0.10[.004] | 06015      | 192048-5   |  |  |  |  |  |  |
| OBSOLETE                               | NOT AVAILABLE |          |        |        |              |                |                    |          |                                         |            | 06059      | 192048-4   |  |  |  |  |  |  |
| OBSOLETE                               | C             | --       | NOTE 7 | [.014] | 8            | --             | 4-2                | --       | 0.10[.004]                              | 06032      | 192048-3   |            |  |  |  |  |  |  |
| 10                                     | C             | --       | NOTE 6 | [.014] | 8            | --             | 3-2                | --       | 0.10[.004]                              | 06051      | 192048-2   |            |  |  |  |  |  |  |
| OBSOLETE                               | C             | --       | NOTE 7 | [.014] | 8            | --             | UNPL               | --       | 0.10[.004]                              | 06033      | 192048-1   |            |  |  |  |  |  |  |
| STYLE                                  |               | FREE DIA | LENGTH | LH     | MAT'L (NOTE) | MATING DIA REF | PLATING (NOTE)     | NUM LOUV | MAT'L THK                               | REF        | PART NO.   |            |  |  |  |  |  |  |
| THIS DRAWING IS A CONTROLLED DOCUMENT. |               |          |        |        |              |                | DWN RA JAYNE       | 06-12-92 | TE Connectivity                         |            |            |            |  |  |  |  |  |  |
| DIMENSIONS: mm [INCHES]                |               |          |        |        |              |                | CHK -              | -        | CONTACT BAND,MALE                       |            |            |            |  |  |  |  |  |  |
|                                        |               |          |        |        |              |                | APVD -             | -        |                                         |            |            |            |  |  |  |  |  |  |
|                                        |               |          |        |        |              |                | PRODUCT SPEC       |          |                                         |            |            |            |  |  |  |  |  |  |
|                                        |               |          |        |        |              |                | APPLICATION SPEC   |          | SIZE CAGE CODE DRAWING NO RESTRICTED TO |            |            |            |  |  |  |  |  |  |
|                                        |               |          |        |        |              |                | -                  |          |                                         |            |            |            |  |  |  |  |  |  |
| MATERIAL SEE TABLE                     |               |          |        |        |              |                | WEIGHT -           | A2       | 00779                                   | C=192048   | -          |            |  |  |  |  |  |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |               |          |        |        |              |                | 0 PLC ± -          |          | CUSTOMER DRAWING                        |            |            |            |  |  |  |  |  |  |
|                                        |               |          |        |        |              |                | 1 PLC ± -          |          |                                         |            |            |            |  |  |  |  |  |  |
|                                        |               |          |        |        |              |                | 2 PLC ± 0.5[.02]   |          | SCALE NTS SHEET 1 of 1 REV J            |            |            |            |  |  |  |  |  |  |
|                                        |               |          |        |        |              |                | 3 PLC ± 0.25[.010] |          |                                         |            |            |            |  |  |  |  |  |  |
|                                        |               |          |        |        |              |                | 4 PLC ± -          |          |                                         |            |            |            |  |  |  |  |  |  |
|                                        |               |          |        |        |              |                | ANGLES ± -         |          |                                         |            |            |            |  |  |  |  |  |  |
|                                        |               |          |        |        |              |                | FINISH             |          |                                         |            |            |            |  |  |  |  |  |  |
|                                        |               |          |        |        |              |                | SEE TABLE          |          |                                         |            |            |            |  |  |  |  |  |  |

1471-9 (1/15)