







LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
-	-	C		REVISED PER ECO 13-001843.	08FEB2013	MGM
						CT



SINGLE POLARIZATION



DOUBLE POLARIZATION



CAVITY IDENTIFICATION WHEN VIEWED FROM REAR OF CONNECTOR

CHROMIUM-BLACK	DOUBLE	SOLDERING	10	11	33.45	Ø12	Ø14.9	2	2101550-2
CHROMIUM-BLACK	SINGLE	SOLDERING	10	11	33.45	Ø12	Ø14.9	2	2101550-1
FINISH	POLARIZATION	TERMINATION	Q	S	L	d	D	SHELL SIZE	TE PART NUMBER

1. DWV RATING 875 VAC @ SEA LEVEL
2. WIRE SIZE: 24 AWG MAX
3. WORKING TEMPERATURE: -55°C ~ +125°C

4 MATERIAL:
CONTACT : COPPER ALLOY
SHELL : COPPER ALLOY
INSULATOR : PEEK

5 FINISH
CONTACT: GOLD OVER NICKEL
SHELL : BLACK CHROMIUM

6 PART IS MARKED WITH TE PART NUMBER, CHINA, DATE CODE AND LOT I.D.

7 ALL TOLERANCES TO BE ±0.20 MM UNLESS NOTED.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	21AUG2009	TE Connectivity			
DIMENSIONS: mm				CHK	21AUG2009				
				TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
				0 PLC ± - 7		CIRCULAR HD PLUG WITH PINS, SOLDER CUP 7 POS.			
MATERIAL 4				1 PLC ± -		SIZE			
				2 PLC ± 0.20		CAGE CODE			
FINISH 5				3 PLC ± -		DRAWING NO			
				4 PLC ± -		A2 00779 C=2101550			
CUSTOMER DRAWING				ANGLES ± 3°		RESTRICTED TO			
				FINISH		SCALE NTS			
						SHEET 1 of 1			
						REV C			