



PANEL MOUNTING  
MAX. PANEL THICKNESS 4mm



| SWITCH FUNCTION |        |
|-----------------|--------|
| POS. 1          | POS. 2 |
|                 |        |
| OFF             | (ON)   |
| OPEN            | 1-2    |

(ON) = MOMENTARY





▲ CIRCUIT: SPST

▲ DOMED ACTUATOR  
COLOR: BLACK


▲ BODY COLOR:  
BLACK ANODIZED

M12x1.0  
THREAD



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 2A @ 36 VDC
6. ELECTRICAL LIFE: 200,000 CYCLES
7. CONTACT RESISTANCE: 50 mΩ MAX. @ 1A 12VDC (INITIAL)
8. INSULATION RESISTANCE: 1,000 MΩ MIN. @ 500VDC.
9. DIELECTRIC STRENGTH: 2,000 VAC rms.
10. OPERATING TEMPERATURE: -20°C TO +70°C.
11. PANEL THICKNESS MAX: 4.0 mm.
12. INGRESS PROTECTION: IP65
13. ▲ DENOTES CRITICAL PARAMETER.
14. 2011/65/EU (ROHS) COMPLIANT
15. ▲ HARDWARE INCLUDED, 1 O-RING & 1 HEX NUT.(NOT SHOWN)



E-SWITCH®

|     |        |                        |        |     |
|-----|--------|------------------------|--------|-----|
| B   | 22668  | UPDATED FLAT ALIGNMENT | 1/9/17 | MJR |
| A   | 00051  | RELEASE FOR PRODUCTION | 8/5/09 | CAB |
| REV | PCR NO | DESCRIPTION            | DATE   | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV5S64011

SCALE

2:1

DATE

8/5/2009

DR

EBP

DWG

52-PV5S64011

REV

B