



1A THREE TERMINAL NEGATIVE VOLTAGE REGULATORS
-5V, -6V, -8V, -9V, -10V, -12V, -15V, -18V, -20V, -24V

FEATURES:

- Suitable for C-MOS, TTL, and the other digital IC power supply.
- Internal thermal overload protecting.
- Internal short circuit current limiting.
- Output current in excess of 1.0A.


MAXIMUM RATINGS (Ta=25°C)

CHARACTERISTIC	SYMBOL	RATING	UNIT
Input Voltage	V _{IN}	-35	V
		-40	
Power Dissipation (Tc=25°C)	P _D	20.8	W
Operating Junction Temperature	T _j	-30~150	°C
Operating Temperature	T _{opr}	-30~75	°C
Storage Temperature	T _{stg}	-55~150	°C



KIA7905P/PI ~ KIA7924P/PI

EQUIVALENT CIRCUIT



KIA7905P/PI ~ KIA7924P/PI

ELECTRICAL CHARACTERISTICS

KIA7905P/PI

(Unless otherwise specified, $V_{IN} = -10V$, $I_{OUT} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN} = 2.2\mu F$, $C_{OUT} = 1\mu F$)

CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	1	$T_j = 25^{\circ}C$		-5.2	-5.0	-4.8	V
Input Regulation	Reg line	1	$T_j = 25^{\circ}C$	$-12V \leq V_{IN} \leq -8V$	-	5	50	mV
				$-25V \leq V_{IN} \leq -7V$	-	10	100	
Load Regulation	Reg load	1	$T_j = 25^{\circ}C$	$5mA \leq I_{OUT} \leq 1.5A$	-	10	100	mV
				$250mA \leq I_{OUT} \leq 750mA$	-	3	50	
Output Voltage	V_{OUT}	1	$-20V \leq V_{IN} \leq -7V$ $5mA \leq I_{OUT} \leq 1.0A$		-5.25	-5.0	-4.75	V
Quiescent Current	I_B	1	$T_j = 25^{\circ}C$		-	3	6	mA
Quiescent Current Change	ΔI_{BI}	1	$-25V \leq V_{IN} \leq -8V$		-	0.1	1.3	mA
	ΔI_{BO}		$5mA \leq I_{OUT} \leq 1.0A$		-	0.05	0.5	
Output Noise Voltage	V_{NO}	2	$T_a = 25^{\circ}C$, $10Hz \leq f \leq 100kHz$		-	100	-	μV_{rms}
Ripple Rejection Ratio	RR	3	$f = 120Hz$, $I_{OUT} = 20mA$,		54	60	-	dB
Short Circuit Current Limit	I_{SC}	1	$T_j = 25^{\circ}C$		-	1.9	-	A
Average Temperature Coefficient of Output Voltage	T_{CVO}	1	$I_{OUT} = 5.0mA$		-	-0.4	-	mV/ $^{\circ}C$
Dropout Voltage	V_D	1	$T_j = 25^{\circ}C$, $I_{OUT} = 1A$		-	2.0	-	V

KIA7905P/PI~KIA7924P/PI

ELECTRICAL CHARACTERISTICS

KIA7906P/PI

(Unless otherwise specified, $V_{IN}=-11V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-6.25	-6.0	-5.75	V
Input Regulation		Reg line	1	T _j =25℃	-13V ≤ V _{IN} ≤ -9V	-	5	60	mV
					-25V ≥ V _{IN} ≥ -8V	-	10	120	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	10	120	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	3	60	
Output Voltage		V _{OUT}	1	-21V ≤ V _{IN} ≤ -9V 5mA ≤ I _{OUT} ≤ 1.0A		-6.3	-6.0	-5.7	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-25V ≤ V _{IN} ≤ -9V		-	-	1.3	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	-	0.5	
Output Noise Voltage		V _{NO}	2	T _a =25℃, 10Hz ≤ f ≤ 100kHz		-	130	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.5	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905P/PI ~ KIA7924P/PI

ELECTRICAL CHARACTERISTICS

KIA7908P/PI

(Unless otherwise specified, $V_{IN} = -14V$, $I_{OUT} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN} = 2.2\mu F$, $C_{OUT} = 1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-8.3	-8.0	-7.7	V
Input Regulation		Reg line	1	T _j =25℃	-17V ≤ V _{IN} ≤ -11V	-	5	80	mV
					-25V ≤ V _{IN} ≤ -10.5V	-	10	100	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	12	160	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	4	80	
Output Voltage		V _{OUT}	1	-23V ≤ V _{IN} ≤ -11.5V 5mA ≤ I _{OUT} ≤ 1.0A		-8.4	-8.0	-7.6	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-25V ≤ V _{IN} ≤ -11.5V		-	0.1	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	0.05	0.5	
Output Noise Voltage		V _{NO}	2	T _a =25℃, 10Hz ≤ f ≤ 100kHz		-	175	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.6	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905P/PI ~ KIA7924P/PI

ELECTRICAL CHARACTERISTICS

KIA7909P/PI

(Unless otherwise specified, $V_{IN} = -15V$, $I_{OUT} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN} = 2.2\mu F$, $C_{OUT} = 1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-9.3	-9.0	-8.7	V
Input Regulation		Reg line	1	T _j =25℃	-19V ≤ V _{IN} ≤ -13V	-	5	90	mV
					-26V ≤ V _{IN} ≤ -11.5V	-	10	100	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	10	150	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	5	120	
Output Voltage		V _{OUT}	1	-24V ≤ V _{IN} ≤ -11.5V 5mA ≤ I _{OUT} ≤ 1.0A		-9.4	-9.0	-8.6	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-26.5V ≤ V _{IN} ≤ -13V		-	0.1	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	0.05	0.5	
Output Noise Voltage		V _{NO}	2	T _a =25℃, 10Hz ≤ f ≤ 100kHz		-	180	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.7	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905P/PI~KIA7924P/PI

ELECTRICAL CHARACTERISTICS

KIA7910IP/PI

(Unless otherwise specified, $V_{IN}=-16V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-10.4	-10	-9.6	V
Input Regulation		Reg line	1	T _j =25℃	-20V ≤ V _{IN} ≤ -14V	-	5	100	mV
					-27V ≤ V _{IN} ≤ -12.5V	-	10	110	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	10	180	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	6	120	
Output Voltage		V _{OUT}	1	-25V ≤ V _{IN} ≤ -12.5V 5mA ≤ I _{OUT} ≤ 1.0A		-10.5	-10	-9.5	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-27.5V ≤ V _{IN} ≤ -14V		-	0.1	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	0.05	0.5	
Output Noise Voltage		V _{NO}	2	T _a =25℃, 10Hz ≤ f ≤ 100kHz		-	190	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.7	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905P/PI ~ KIA7924P/PI

ELECTRICAL CHARACTERISTICS

KIA7912P/PI

(Unless otherwise specified, $V_{IN} = -18V$, $I_{OUT} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN} = 2.2\mu F$, $C_{OUT} = 1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-12.5	-12	-11.5	V
Input Regulation		Reg line	1	T _j =25℃	-22V ≤ V _{IN} ≤ -16V	-	6	120	mV
					-30V ≤ V _{IN} ≤ -14.5V	-	12	240	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	12	240	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	4	120	
Output Voltage		V _{OUT}	1	-27V ≤ V _{IN} ≤ -15.5V 5mA ≤ I _{OUT} ≤ 1.0A		-12.6	-12	-11.4	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-30V ≤ V _{IN} ≤ -15V		-	0.1	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	0.05	0.5	
Output Noise Voltage		V _{NO}	2	T _a =25℃, 10Hz ≤ f ≤ 100kHz		-	200	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.8	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905P/PI~KIA7924P/PI

ELECTRICAL CHARACTERISTICS

KIA7915P/PI

(Unless otherwise specified, $V_{IN}=-23V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-15.6	-15	-14.4	V
Input Regulation		Reg line	1	T _j =25℃	-26V ≤ V _{IN} ≤ -20V	-	6	150	mV
					-30V ≤ V _{IN} ≤ -17.5V	-	12	300	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	12	300	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	4	150	
Output Voltage		V _{OUT}	1	-30V ≤ V _{IN} ≤ -18V 5mA ≤ I _{OUT} ≤ 1.0A		-15.75	-15	-14.25	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-30V ≤ V _{IN} ≤ -17.5V		-	0.1	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	0.05	0.5	
Output Noise Voltage		V _{NO}	2	T _a =25℃, 10Hz ≤ f ≤ 100kHz		-	250	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-0.9	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905P/PI~KIA7924P/PI

ELECTRICAL CHARACTERISTICS

KIA7918P/PI

(Unless otherwise specified, $V_{IN}=-27V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=2.2\mu F$, $C_{OUT}=1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-18.7	-18	-17.3	V
Input Regulation		Reg line	1	T _j =25℃	-30V ≤ V _{IN} ≤ -24V	-	8	180	mV
					-33V ≤ V _{IN} ≤ -21V	-	15	360	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	15	360	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	5	180	
Output Voltage		V _{OUT}	1	-33V ≤ V _{IN} ≤ -22.5V 5mA ≤ I _{OUT} ≤ 1.0A		-18.85	-18	-17.15	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-33V ≤ V _{IN} ≤ -22V		-	-	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	-	0.5	
Output Noise Voltage		V _{NO}	2	T _a =25℃, 10Hz ≤ f ≤ 100kHz		-	300	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-1.0	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905P/PI ~ KIA7924P/PI

ELECTRICAL CHARACTERISTICS

KIA7920P/PI

(Unless otherwise specified, $V_{IN} = -30V$, $I_{OUT} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN} = 2.2\mu F$, $C_{OUT} = 1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-20.8	-20	-19.2	V
Input Regulation		Reg line	1	T _j =25℃	-32V ≤ V _{IN} ≤ -26V	-	10	180	mV
					-35V ≤ V _{IN} ≤ -24V	-	18	360	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	18	360	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	10	180	
Output Voltage		V _{OUT}	1	-35V ≤ V _{IN} ≤ -24V 5mA ≤ I _{OUT} ≤ 1.0A		-21.0	-20	-19.0	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-36.5V ≤ V _{IN} ≤ -25V		-	-	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	-	0.5	
Output Noise Voltage		V _{NO}	2	T _a =25℃, 10Hz ≤ f ≤ 100kHz		-	350	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-1.0	-	mV/℃
Dropout Voltage		V _D	1	T _j =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905P/PI~KIA7924P/PI

ELECTRICAL CHARACTERISTICS

KIA7924P/PI


(Unless otherwise specified, $V_{IN}=-33V$, $I_{OUT}=500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{IN}=0.33\mu F$, $C_{OUT}=0.1\mu F$)

CHARACTERISTIC		SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage		V _{OUT}	1	T _j =25℃		-25	-24	-23	V
Input Regulation		Reg line	1	T _j =25℃	-36V ≤ V _{IN} ≤ -30V	-	8	240	mV
					-38V ≤ V _{IN} ≤ -27V	-	15	480	
Load Regulation		Reg load	1	T _j =25℃	5mA ≤ I _{OUT} ≤ 1.5A	-	15	480	mV
					250mA ≤ I _{OUT} ≤ 750mA	-	5	240	
Output Voltage		V _{OUT}	1	-38V ≤ V _{IN} ≤ -27V 5mA ≤ I _{OUT} ≤ 1.0A		-25.2	-24	-22.5	V
Quiescent Current		I _B	1	T _j =25℃		-	3	6	mA
Quiescent Current Change	Line	ΔI _{BI}	1	-38V ≤ V _{IN} ≤ -27V		-	-	1.0	mA
	Load	ΔI _{BO}		5mA ≤ I _{OUT} ≤ 1.0A		-	-	0.5	
Output Noise Voltage		V _{NO}	2	T _a =25℃, 10Hz ≤ f ≤ 100kHz		-	400	-	μV _{rms}
Ripple Rejection Ratio		RR	3	f=120Hz, I _{OUT} =20mA,		54	60	-	dB
Short Circuit Current Limit		I _{SC}	1	T _j =25℃		-	1.9	-	A
Average Temperature Coefficient of Output Voltage		T _{CVO}	1	I _{OUT} =5mA		-	-1.0	-	mV/℃
Dropout Voltage		V _D	1	T _a =25℃, I _{OUT} =1A		-	2.0	-	V

KIA7905P/PI ~ KIA7924P/PI


TEST CIRCUIT

1. V_{OUT} , Reg•Line, Reg•Load, I_B , ΔI_B , V_D , T_{CVO}



- Notes : (1) To specify an output voltage, substitute voltage value for "XX"
 (2) Required for stability. For value given, capacitor must be solid tantalum. If aluminium electrolytics are used, at least ten times value shown should be selected. C_1 is required if regulator is located an appreciable distance from power supply filter.
 (3) To improve transient response. If large capacitors are used, a high current diode from input to output (1N4001 or similar) should be introduced to protect the device from momentary input short circuit.

2. V_{NO}



3. R•R

