


TLC2872Z, TLC2872Y Advanced LinCMOS™ RAIL-TO-RAIL DUAL OPERATIONAL AMPLIFIERS


SLOS117 – OCTOBER 1992

- Free-Air Operating Temperature
–40°C to 150°C
- Output Swing Includes Both Supply Rails
- Low Noise . . . 9 nV/√Hz Typ at f = 1 kHz
- Low Input Bias Current . . . 1 pA Typ
- Common-Mode Input Voltage Range
Includes Negative Rail
- High Unity-Gain Bandwidth . . . 2.2 MHz Typ
- High Slew Rate . . . 3.6 V/μs Typ
- Low Input Offset Voltage
300 μV Typ at T_A = 25°C
- Macromodel Included

D OR P PACKAGE
(TOP VIEW)



MAXIMUM OUTPUT VOLTAGE
VS
SUPPLY VOLTAGE



description

The TLC2872Z is a dual rail-to-rail output operational amplifier manufactured using Texas Instruments Advanced LinCMOS™ process. These devices offer comparable ac performance while having better noise, input offset voltage and power dissipation than existing CMOS operational amplifiers. In addition, the common-mode input voltage range is wider than typical standard CMOS type amplifiers. To take advantage of this improvement in performance, making this device available for a wider range of applications, V_{ICR} is specified with a larger maximum input offset voltage test limit of ±5 mV. The Advanced LinCMOS™ process uses a silicon-gate technology to obtain input offset voltage stability with temperature and time that far exceeds that obtainable using metal-gate technology. Also, this technology makes possible input impedance levels that meet or exceed levels offered by top-gate JFET and expensive dielectric-isolated devices.

The TLC2872Z, manufactured using Texas Instruments high-temperature process flow, allows extended temperature operation up to 150°C in a plastic package. This adds extra reliability at the extended temperature and reduces the need for expensive hermetically sealed ceramic packages.

The TLC2872Z, which exhibits high input impedance and low noise, is excellent for small signal conditioning of high impedance sources, such as piezoelectric transducers. In addition, the rail-to-rail output feature with single or split supplies makes this device a great choice for inputs to ADCs in either the unipolar or bipolar mode of operation. This feature, combined with its temperature performance, makes the TLC2872Z ideal for sonobuoys, pressure sensors, temperature controls, active VR sensors, accelerometers, and many other applications.

AVAILABLE OPTIONS

T _A	V _{IOmax} AT 25°C	PACKAGED DEVICES		CHIP FORM (Y)
		SMALL OUTLINE (D)	PLASTIC DIP (P)	
–40°C to 150°C	2.5 mV	TLC2872ZD	TLC2872ZP	TLC2872Y

The D packages are available taped and reeled. Add R suffix to device type (e.g., TLC2872DR).

Advanced LinCMOS™ is a trademark of Texas Instruments Incorporated.

PRODUCTION DATA Information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Copyright © 1992, Texas Instruments Incorporated

TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

2–1073

8961724 0093751 46T

TLC2872Z, TLC2872Y
Advanced LinCMOS™ RAIL-TO-RAIL
DUAL OPERATIONAL AMPLIFIERS

SLOS117 – OCTOBER 1992



description (continued)

The inputs and outputs of this device are designed to withstand 100-mA surge current without sustaining latch-up. In addition, internal ESD-protection circuits prevent functional failures up to 2000 V. The device is characterized for operation over the extended (Z) temperature range of -40°C to 150°C .

TLC2872Y chip information

This chip, when properly assembled, displays characteristics similar to TLC2872Z. Thermal compression or ultrasonic bonding may be used on the doped-aluminum bonding pads. Chips may be mounted with conductive epoxy or a gold-silicon preform.

BONDING PAD ASSIGNMENTS



CHIP THICKNESS: 15 TYPICAL

BONDING PADS: 4×4 MINIMUM

$T_J \text{ max} = 150^{\circ}\text{C}$

TOLERANCES ARE $\pm 10\%$.

ALL DIMENSIONS ARE IN MILS.


PIN (4) IS INTERNALLY CONNECTED
TO BACKSIDE OF CHIP.

TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

2-1074

■ 8961724 0093752 3T6 ■



TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

8961724 0093753 232

2-1075

TLC2872Z, TLC2872Y
Advanced LinCMOS™ RAIL-TO-RAIL
DUAL OPERATIONAL AMPLIFIER
SLOS117 – OCTOBER 1992

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

Supply voltage, V_{DD+}	8 V
Supply voltage, V_{DD-}	-8 V
Differential input voltage, V_{ID} (see Note 1)	±16 V
Input voltage range, V_I (any input, see Note 2)	±8 V
Input current, I_I (each input)	±5 mA
Output current, I_O	±50 mA
Total current into V_{DD+}	±50 mA
Total current out of V_{DD-}	±50 mA
Duration of short-circuit current at (or below) 25°C (see Note 3)	unlimited
Continuous total dissipation	See Dissipation Rating Table
Operating free-air temperature range, T_A	-40°C to 150°C
Storage temperature range	-65°C to 165°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	260°C

† Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. Differential voltages are at $IN+$ with respect to $IN-$. Excessive current will flow if input is brought below $V_{DD-} - 0.3$ V.
2. All voltage values, except differential voltages, are with respect to the midpoint between V_{DD+} and V_{DD-} .
3. The output may be shorted to either supply. Temperature and/or supply voltages must be limited to ensure that the maximum dissipation rating is not exceeded.

DISSIPATION RATING TABLE

PACKAGE	$T_A \leq 25^\circ\text{C}$ POWER RATING	DERATING FACTOR ABOVE $T_A = 25^\circ\text{C}$	$T_A = 70^\circ\text{C}$ POWER RATING	$T_A = 105^\circ\text{C}$ POWER RATING	$T_A = 125^\circ\text{C}$ POWER RATING	$T_A = 150^\circ\text{C}$ POWER RATING
D	812 mW	5.8 mW/°C	551 mW	348 mW	232 mW	87 mW
P	1120 mW	8 mW/°C	760 mW	480 mW	320 mW	120 mW

recommended operating conditions

	MIN	MAX	UNIT
Supply voltage, $V_{DD\pm}$	±2.2	±8	V
Input voltage range, V_I	V_{DD-}	$V_{DD+} - 1.5$	V
Common-mode input voltage, V_{IC}	V_{DD-}	$V_{DD+} - 1.5$	V
Operating free-air temperature, T_A	-40	150	°C



electrical characteristics at specified free-air temperature, $V_{DD} = 5\text{ V}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	T_A †	TLC2872Z			UNIT
			MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_{DD} \pm \pm 2.5\text{ V}$, $V_O = 0$, $V_{IC} = 0$, $R_S = 50\ \Omega$	25°C		300	2500	μV
		Full range			3000	
αV_{IO} Temperature coefficient of input offset voltage		25°C to 150°C		2		$\mu\text{V}/^\circ\text{C}$
Input offset voltage long-term drift (see Note 4)		25°C		0.002		$\mu\text{V}/\text{mo}$
I_{IO} Input offset current		25°C		0.0005		nA
		Full range			3	
I_{IB} Input bias current		25°C		0.001		nA
		Full range			5	
V_{ICR} Common-mode input voltage range	$R_S = 50\ \Omega$, $ V_{IO} \leq 5\text{ mV}$	25°C	0 to 4	–0.3 to 4.2		V
		Full range	0 to 3.5			
V_{OH} High-level output voltage	$I_{OH} = -20\ \mu\text{A}$	25°C	4.95	4.99		V
	$I_{OH} = -200\ \mu\text{A}$	25°C	4.85	4.93		
	$I_{OH} = -1\text{ mA}$	Full range	4.75			
		25°C	4.25	4.65		
V_{OL} Low-level output voltage	$V_{IC} = 2.5\text{ V}$, $I_{OL} = 50\ \mu\text{A}$	25°C		0.01	0.02	V
	$V_{IC} = 2.5\text{ V}$, $I_{OL} = 500\ \mu\text{A}$	25°C		0.09	0.15	
	$V_{IC} = 2.5\text{ V}$, $I_{OL} = 5\text{ mA}$	Full range			0.2	
		25°C		0.9	1.5	
A_{VD} Large-signal differential voltage amplification	$V_{IC} = 2.5\text{ V}$, $V_O = 1\text{ V to }4\text{ V}$	25°C	15	35		V/mV
		Full range	10			
		25°C		175		
r_{id} Differential input resistance		25°C		10^{12}		Ω
r_i Common-mode input resistance		25°C		10^{12}		Ω
c_i Common-mode input capacitance	$f = 10\text{ kHz}$, P package	25°C		8		pF
z_o Closed-loop output impedance	$f = 1\text{ MHz}$, $A_V = 10$	25°C		140		Ω
CMRR Common-mode rejection ratio	$V_{IC} = 0\text{ to }2.7\text{ V}$, $R_S = 50\ \Omega$, $V_O = 2.5\text{ V}$	25°C	70	75		dB
		Full range	70			
KSVR Supply voltage rejection ratio ($\Delta V_{DD}/\Delta V_{IO}$)	$V_{DD} = 4.4\text{ V to }16\text{ V}$, $V_{IC} = V_{DD}/2$, No load	25°C	80	95		dB
		Full range	80			
I_{DD} Supply current	$V_O = 2.5\text{ V}$, No load	25°C		2.2	3	mA
		Full range			3	

† Full range is –40°C to 150°C.

‡ Referenced to 2.5 V

NOTE 4: Typical values are based on the input offset voltage shift observed through 168 hours of operating life test at $T_A = 150^\circ\text{C}$ extrapolated to $T_A = 25^\circ\text{C}$ using the Arrhenius equation and assuming an activation energy of 0.96 eV.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

2–1077

8961724 0093755 005

TLC2872Z, TLC2872Y
Advanced LinCMOST™ RAIL-TO-RAIL
DUAL OPERATIONAL AMPLIFIER
SLOS117 – OCTOBER 1992

operating characteristics at specified free-air temperature, $V_{DD} = 5\text{ V}$

PARAMETER		TEST CONDITIONS		T _A [†]	TLC2872Z			UNIT
					MIN	TYP	MAX	
SR	Slew rate at unity gain	V _O = 0.5 V to 2.5 V, R _L = 10 kΩ [‡] , C _L = 100 pF [‡]		25°C	2.3	3.6	V/μs	
				Full range	1.1			
V _n	Equivalent input noise voltage	f = 10 Hz		25°C	50		nV/√Hz	
		f = 1 kHz		25°C	9			
V _{N(PP)}	Peak-to-peak equivalent input noise voltage	f = 0.1 to 1 Hz		25°C	1		μV	
		f = 0.1 to 10 Hz		25°C	1.4			
I _n	Equivalent input noise current			25°C	0.6		fA/√Hz	
THD + N	Total harmonic distortion plus noise	V _O = 0.5 V to 2.5 V, f = 20 kHz, R _L = 10 kΩ [‡]	A _V = 1	25°C	0.0013%			
			A _V = 10		0.004%			
			A _V = 100		0.03%			
Gain-bandwidth product		f = 10 kHz, C _L = 100 pF [‡]	R _L = 10 kΩ [‡]	25°C	2.18		MHz	
BOM	Maximum output-swing bandwidth	V _{O(PP)} = 2 V, R _L = 10 kΩ [‡]	A _V = 1, C _L = 100 pF [‡]	25°C	1		MHz	
	Settling time	A _V = -1, Step = 0.5 V to 2.5 V, R _L = 10 kΩ [‡] , C _L = 100 pF [‡]	To 0.1%	25°C	1.5		μs	
			To 0.01%		2.6			
φ _m	Phase margin at unity gain	R _L = 10 kΩ [‡] , C _L = 100 pF [‡]		25°C	50°		dB	
	Gain margin			25°C	10			

† Full range is -40°C to 150°C .

‡ Referenced to 2.5 V



2-1078

8961724 0093756 T41

electrical characteristics, $V_{DD} = 5\text{ V}$, $T_A = 25^\circ\text{C}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	TLC2872Y			UNIT
		MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_{IC} = 0, \quad V_O = 0,$ $R_S = 50\ \Omega$		300	2500	μV
Input offset voltage long-term drift (see Note 4)			0.002		$\mu\text{V}/\text{mo}$
I_{IO} Input offset current			0.0005		nA
I_{IB} Input bias current			0.001		nA
V_{ICR} Common-mode input voltage range	$R_S = 50\ \Omega, \quad V_{IO} \leq 5\text{ mV}$	0 to 4	-0.3 to 4.2		V
		0 to 3.5			
V_{OH} High-level output voltage	$I_{OH} = -20\ \mu\text{A}$	4.95	4.99		V
	$I_{OH} = -200\ \mu\text{A}$	4.85	4.93		
	$I_{OH} = -1\text{ mA}$	4.25	4.65		
V_{OL} Low-level output voltage	$V_{IC} = 2.5\text{ V}, \quad I_{OL} = 50\ \mu\text{A}$		0.01	0.02	V
	$V_{IC} = 2.5\text{ V}, \quad I_{OL} = 500\ \mu\text{A}$		0.09	0.15	
	$V_{IC} = 2.5\text{ V}, \quad I_{OL} = 5\text{ mA}$		0.9	1.5	
A_{VD} Large-signal differential voltage amplification	$V_{IC} = 2.5\text{ V}, \quad V_O = 1\text{ V to }4\text{ V}$	$R_L = 10\text{ k}\Omega^\dagger$	15	35	V/mV
		$R_L = 1\text{ M}\Omega^\dagger$	175		
r_{id} Differential input resistance			10^{12}		Ω
r_i Common-mode input resistance			10^{12}		Ω
c_i Common-mode input capacitance	$f = 10\text{ kHz}, \quad \text{P package}$		8		pF
z_o Closed-loop output impedance	$f = 1\text{ MHz}, \quad A_V = 10$		140		Ω
CMRR Common-mode rejection ratio	$V_{IC} = 0\text{ to }2.7\text{ V}, \quad V_O = 2.5\text{ V},$ $R_S = 50\ \Omega$	70	75		dB
k_{SVR} Supply voltage rejection ratio ($\Delta V_{DD\pm}/\Delta V_{IO}$)	$V_{DD} = 4.4\text{ V to }16\text{ V}, \quad V_{IC} = V_{DD}/2,$ No load	80	95		dB
I_{DD} Supply current	$V_O = 2.5\text{ V}, \quad \text{No load}$	2.2	3		mA

† Referenced to 2.5 V



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

2-1079

TLC2872Z, TLC2872Y
Advanced LinCMOS™ RAIL-TO-RAIL
DUAL OPERATIONAL AMPLIFIER
 SLOS117 – OCTOBER 1992

operating characteristics, $V_{DD} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS	TLC2872Y			UNIT
			MIN	TYP	MAX	
SR	Slew rate at unity gain	$V_O = 0.5\text{ V to }2.5\text{ V}$, $R_L = 10\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}^\dagger$	2.3	3.6		V/ μs
V_n	Equivalent input noise voltage	$f = 10\text{ Hz}$		50		nV/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		9		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ to }1\text{ Hz}$		1		μV
		$f = 0.1\text{ to }10\text{ Hz}$		1.4		
I_n	Equivalent input noise current			0.6		fA/ $\sqrt{\text{Hz}}$
THD + N	Total harmonic distortion plus noise	$V_O = 0.5\text{ V to }2.5\text{ V}$, $f = 20\text{ kHz}$, $R_L = 10\text{ k}\Omega^\dagger$	$A_V = 1$	0.0013%		
			$A_V = 10$	0.004%		
			$A_V = 100$	0.03%		
	Gain-bandwidth product	$f = 10\text{ kHz}$, $C_L = 100\text{ pF}^\dagger$		2.18		MHz
BOM	Maximum output-swing bandwidth	$V_{O(PP)} = 4.6\text{ V}$, $R_L = 10\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}^\dagger$	$A_V = 1$	1		MHz
	Settling time	$A_V = -1$, Step = $0.5\text{ V to }2.5\text{ V}$, $R_L = 10\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}^\dagger$	To 0.1%	1.5		μs
			To 0.01%	2.6		
ϕ_m	Phase margin at unity gain	$R_L = 10\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}^\dagger$		50°		
	Gain margin			10		dB

† Referenced to 2.5 V



TYPICAL CHARACTERISTICS

Table of Graphs

			FIGURE
V_{IO}	Input offset voltage	Distribution	1
αV_{IO}	Input offset voltage temperature coefficient	Distribution	2
I_{IB}/I_{IO}	Input bias and offset currents	vs Free-air temperature	3
V_I	Input voltage range	vs Free-air temperature	4
V_{OH}	High-level output voltage	vs Output current	5
V_{OL}	Low-level output voltage	vs Output current	6, 7
V_{OM}	Maximum output voltage	vs Frequency	8
I_{OS}	Short-circuit output current	vs Supply voltage vs Free-air temperature	9 10
A_{VD}	Large-signal differential voltage amplification	vs Load resistance vs Frequency vs Free-air temperature	11 12 13
I_{DD}	Supply current	vs Supply voltage vs Free-air temperature	14 15
SR	Slew rate	vs Load capacitance vs Free-air temperature	16 17
ϕ_m	Phase margin	vs Frequency vs Load capacitance	12 18
	Gain margin	vs Load capacitance	19

NOTE: All loads are referenced to 2.5 V.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

8961724 0093759 750

2-1081

TYPICAL CHARACTERISTICS

**DISTRIBUTION OF TLC2872Z
INPUT OFFSET VOLTAGE**




Figure 1

**DISTRIBUTION OF TLC2872Z
TEMPERATURE COEFFICIENT**




Figure 2

**INPUT BIAS AND OFFSET CURRENTS
vs
FREE-AIR TEMPERATURE**




Figure 3

**INPUT VOLTAGE RANGE
vs
FREE-AIR TEMPERATURE**




Figure 4

TYPICAL CHARACTERISTICS†




Figure 5




Figure 6




Figure 7




Figure 8

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

2-1083

8961724 0093761 309

TYPICAL CHARACTERISTICS†

**SHORT-CIRCUIT OUTPUT CURRENT
vs
SUPPLY VOLTAGE**




Figure 9

**SHORT-CIRCUIT OUTPUT CURRENT
vs
FREE-AIR TEMPERATURE**




Figure 10

**LARGE-SIGNAL DIFFERENTIAL
VOLTAGE AMPLIFICATION
vs
LOAD RESISTANCE**




Figure 11

**LARGE-SIGNAL DIFFERENTIAL
AMPLIFICATION and PHASE MARGIN
vs
FREQUENCY**




Figure 12

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

2-1084

8961724 0093762 245

TYPICAL CHARACTERISTICS

LARGE-SIGNAL DIFFERENTIAL
VOLTAGE AMPLIFICATION
vs
FREE-AIR TEMPERATURE




Figure 13

SUPPLY CURRENT
vs
SUPPLY VOLTAGE




Figure 14

SUPPLY CURRENT
vs
FREE-AIR TEMPERATURE




Figure 15

SLEW RATE
vs
LOAD CAPACITANCE




Figure 16

TYPICAL CHARACTERISTICS†




Figure 17




Figure 18




Figure 19

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

APPLICATION INFORMATION

macromodel information

Macromodel information provided was derived using *PSpice™ Parts™* model generation software. The Boyle macromodel (see Note 5) and subcircuit in Figure 20 were generated using the TLC2872Z typical electrical and operating characteristics at $T_A = 25^\circ\text{C}$. Using this information, output simulations of the following key parameters can be generated to a tolerance of 20% (in most cases):

- Maximum positive output voltage swing
- Maximum negative output voltage swing
- Slew rate
- Quiescent power dissipation
- Input bias current
- Open-loop voltage amplification
- Unity gain frequency
- Common-mode rejection ratio
- Phase margin
- DC output resistance
- AC output resistance
- Short-circuit output current limit

NOTE 5: G. R. Boyle, B. M. Cohn, D. O. Pederson, and J. E. Solomon, "Macromodeling of Integrated Circuit Operational Amplifiers", *IEEE Journal of Solid-State Circuits*, SC-9, 353 (1974).




Figure 20. Boyle Macromodel and Subcircuit

PSpice and *Parts* are trademarks of MicroSim Corporation.

Macromodels, simulation models, or other models provided by TI, directly or indirectly, are not warranted by TI as fully representing all of the specification and operating characteristics of the semiconductor product to which the model relates.

**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

2-1087

8961724 0093765 T54