


DRAWING NUMBER :
MP-0085

REVISION :
A


ENGINEERING DETAILS



NOTES:

1. ALL DIMENSION IN MM.
2. GENERAL TOLERANCE, UNLESS OTHERWISE SPECIFIED:
LINEAR : ± 0.2 ANGULAR : $\pm 5^\circ$
: ± 0.13 : ± 0.5
: ± 0.50
3. CRITICAL DIMENSIONS, WHERE Y IS IN NUMERICAL DIGITS.
4. CRITICAL POINTS, WHERE Z IS IN ALPHABETICAL ORDER.
5. CRITICAL POINTS.
6. MAX. 0.20MM ALLOWABLE PLASTIC FLASH ALL ROUND.
7. MAX. 0.05MM ALLOWABLE METALLIC BURR ALL ROUND.
8. EVERY LOT MUST COME WITH COC DECLARING THE SUPPLIER AND TYPE NUMBER OF THE MATERIAL USED.

Panel Dimension



TABLE

ITEM NO.	COLOR
6900371-W033	BLUE
6900370-W033	BLACK

MATERIAL SPECIFICATION (CONTACTS)

MATERIAL	TIN PLATED BRASS
MATERIAL No.	C2680
ELONGATION	30%
TEMPERING	-
TENSILE STRENGTH	36~45kgf/mm ²
HARDNESS VALUE	1/2H
PLATING THICKNESS	3~5um
SUPPLIER	GE PLASTICS GLOBAL

MATERIAL	PC
COLOR	REFER TO TABLE
FINISHING	-
MATERIAL No.	PC-945
UL LICENSE No.	E161759
FLAMMABILITY	UL94V-0
SUPPLIER	GE PLASTICS GLOBAL

DRAWN : XIA YX REV ECR BY DATE REV ECR BY DATE

RELEASED : 04/07/07 A IAM XIA 04/07/07

CHECKED : SIGN DATE

APPROVED : 6/17/07

ITEM NO. : VAC13KI INLET

FILENAME : F:\DATA\ENG\MP-0085

SCALE : 1 : 1

PROJ. : THIRD ANGLE

PAGE : 2/3

Item No. : REFER TO TABLE

Model No. : VAC13KI

Material Specification (Contacts)

MATERIAL	TIN PLATED BRASS
MATERIAL No.	C2680
ELONGATION	30%
TEMPERING	-
TENSILE STRENGTH	36~45kgf/mm ²
HARDNESS VALUE	1/2H
PLATING THICKNESS	3~5um
SUPPLIER	GE PLASTICS GLOBAL

Material Specification

MATERIAL	PC
COLOR	REFER TO TABLE
FINISHING	-
MATERIAL No.	PC-945
UL LICENSE No.	E161759
FLAMMABILITY	UL94V-0
SUPPLIER	GE PLASTICS GLOBAL

Voletex

Information contained herein shall not be disclosed to others, reproduced or used for any other purpose except as authorized in writing by an authorized officer of Voletex Inc.