


REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
	R3	REVISED PER ECR-17-005324	17APR2017	NK



- 1 CONTINUOUS STRIP ON REEL.
- 2 0.002032 [0.000080] MIN TIN PLATE.
- 3 0.002032 [0.000080] MIN TIN PLATE OVER 0.00127 [0.000050] MIN NICKEL UNDERPLATE.
- 4 WITH INTERLEAVING PAPER
- 5 0.00508 [0.000200] MIN SILVER PLATE OVER 0.00127 [0.000050] MIN NICKEL PLATE
- 6 0.000762 [0.000030] MIN GOLD OVER 0.00127 [0.000050] MIN NICKEL UNDERPLATE.
- 7 WIRE SIZE IS [#18-#14] AWG
- 8 INSULATION RANGE IS 2.29-3.18 [0.090-0.125] DIA
- 9 PRELIMINARY - NOT FOR PRODUCTION

OBSOLETE	5	081 BRASS	9	60793-7
	6	081 BRASS	9	60793-6
	2	081 BERYLLIUM COPPER	9	60793-5
	2	081 BRASS		60793-4
	3	081 BRASS		60793-3
	2	081 BRASS		60793-1
FINISH		MATERIAL		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PHILLIP M FORTNEY 11/NOV/96	STE TE Connectivity	
		CHK JEFF R RUTH 11/NOV/96		
		APVD GARY YETTER 11/NOV/96	NAME	
DIMENSIONS: mm [INCHES]		PRODUCT SPEC	SHUR PLUG, 4.57 [0.180] DIA	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE	CAGE CODE
0 PLC ± -		—	A3	00779
1 PLC ± -		—	DRAWING NO	
2 PLC ± 0.25 [010]		—	RESTRICTED TO	
3 PLC ± -		—	—	
4 PLC ± -		—	—	
ANGLES ± -		—	—	
MATERIAL		WEIGHT	CUSTOMER DRAWING	
SEE TABLE		0.000000	SCALE 5:1	
FINISH		SHEET 1 OF 1		REV R3
SEE TABLE				

SECTION A-A
SCALE 10:1

SECTION B-B
SCALE 10:1