





RECOMMENDED PC BOARD LAYOUT



- 1 NYLON, RED.
2 BRASS PER ASTM B36.
3 3.81 μ m [.000150] MIN TIN-LEAD OVER 2.54 μ m [.000100] MIN COPPER OR 1.27 μ m [.000050] MIN NICKEL.
4 0.76 μ m [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END, 3.81 μ m [.000150] MIN TIN-LEAD FOR A LENGTH OF 5.51 [.217] MIN FROM OPPOSITE END, BOTH OVER 1.27 μ m [.000050] MIN NICKEL.

5.08 [C.2001] TIN-LEAD FOR END, BOTH OVER		FINISH		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 P.C DEC # 0.25 [C.0101] 3 P.C DEC # - ANGLES # -		DR 07/07/92 L.SIZE CHK 7-24-92 R.STONE APPD 7-24-92 A.TRAVIS APPD 7-24-92 C.ROHDE PRODUCT SPEC		NAME AMP AMP Incorporated Harrisburg, PA 17105-3608	
MATERIAL HOUSING:  CONTACTS: 		APPLICATION SPEC WEIGHT -		PIN HEADER ASSEMBLY, 3 POSN, IN-LINE, RIGHT ANGLE, SMALL METRIC CONNECTOR, METRIMATE	
FINISH CONTACTS: SEE TABLE		SCALE 2:1		CUSTOMER DRAWING	
THIS DRAWING IS A CONTROLLED DOCUMENT. FOR AND THE COMPANY'S POLICY ON REVISIONS SHOULD BE CONTACTED FOR THE LATEST REVISION.		SIZE C CAGE CODE 00779 DRAWING NO C-207541		SHEET 1 OF 1	