


High Performance, High Precision Surface Mount 0603 Capacitor



PATENTED

ELECTRICAL SPECIFICATIONS

Operating Temperature: - 55 °C to + 125 °C

**Temperature Coefficient
of Capacitance (TCC):** 0 ± 30 ppm/°C

Insulation Resistance: 10¹¹ Ω min

Voltage: 2.5 x rated voltage (DC)
for 5 seconds

Ageing: none

ENVIRONMENTAL SPECIFICATIONS

Life Test: 1000 hours, + 125 °C at
2 x rated voltage (DC)

Thermal Shock: 100 Cycles, - 55 °C/+ 150 °C

Moisture Resistance: 1000 hours at rated DCV,
85 % RH, + 85 °C

FEATURES

- Terminations are Sn/Ag/Cu or Au. The standard product is lead (Pb)-free and RoHS compliant, but terminations containing lead are available
- New technology surface mount capacitor based on a special semiconductor process
- Construction reduces the parasitic inductance and brings the SRF values to ultra-high frequencies
- Capacitance is extremely stable in a wide range of frequencies from 1 MHz to several GHz
- High Q and low ESR
- Tight tolerance to ± 1 % or 0.05 pF
- Ultra high SRF
- Low parasitic inductance (~ 0.046 nH)
- Capacitance range: 0.8 pF to 560 pF and 1000 pF
Consult factory for 0.1 pF through 0.7 pF



RoHS*
COMPLIANT

APPLICATIONS

- Wireless communications
- Mobile phones
- Cordless phones
- GPS
- VCO
- Filter Networks
- Matching Networks
- Base station
- DC Blocking
- High speed circuitry
- Embedded Substrates

CAPACITANCE TOLERANCE CODE

FOR LESS THAN 10 pF			FOR 10 pF AND HIGHER		
A	B	C	F	G	J
± 0.05 pF	± 0.10 pF	± 0.25 pF	± 1 %	± 2 %	± 5 %

ORDERING INFORMATION

HPC	0603	A	100	G	X	X	T5	XX
MODEL	SIZE	TYPE	CAPACITANCE VALUE	CAPACITANCE TOLERANCE	TERMINATION	VOLTAGE	PACKAGING	SPECIAL ENGINEERING CONTROL CODE
			The first two digits are significant, the third is a multiplier. An "R" indicates a decimal point. Examples: 101 = 100 pF 4R7 = 4.7 pF	see chart	X = Tin/Lead termination W = Lead (Pb)-free termination	2 = 4 V 1 = 6 V Z = 10 V Y = 16 V X = 25 V M = 50 V L = 100 V	T5 = 5000 pcs tape and reel T1 = 1000 pcs tape and reel	Leave blank when no special requirements apply
"W" terminations preferred. "See Part Numbering System, Document 10147, for complete explanations."								

* Pb containing terminations are not RoHS compliant, exemptions may apply.




Not for new designs, this product will be discontinued soon

HPC0603A

High Performance, High Precision
Surface Mount 0603 Capacitor

Vishay

DIMENSIONS



For PCB pad design please see assembly/reflow recommendations document 10125.

DIMENSION	INCHES	MILLIMETERS
L	0.063 ± 0.002	1.60 ± 0.05
W	0.031 ± 0.002	0.80 ± 0.05
T	0.022 ± 0.002	0.56 ± 0.05
A	0.008 ± 0.002	0.20 ± 0.05
B	0.049 ± 0.002	1.24 ± 0.05
C	0.025 ± 0.002	0.64 ± 0.05

CAPACITANCE RANGE AND VOLTAGE

CAPACITANCE (pF)	CAPACITANCE CODE	VOLTAGE RATING & VOLTAGE CODE						
		100 V	50 V	25 V	16 V	10 V	6 V	4 V
		CODE:	CODE:	CODE:	CODE:	CODE:	CODE:	CODE:
0.8	0R8	L	M	X	Y	Z	1	2
0.9	0R9		M	X	Y	Z	1	2
1.0	1R0	L	M	X	Y	Z	1	2
1.2	1R2	L	M	X	Y	Z	1	2
1.5	1R5		M	X	Y	Z	1	2
1.8	1R8	L	M	X	Y	Z	1	2
2.2	2R2	L	M	X	Y	Z	1	2
2.7	2R7	L	M	X	Y	Z	1	2
3.3	3R3	L	M	X	Y	Z	1	2
3.9	3R9	L	M	X	Y	Z	1	2
4.7	4R7	L	M	X	Y	Z	1	2
5.6	5R6	L	M	X	Y	Z	1	2
6.8	6R8	L	M	X	Y	Z	1	2
8.2	8R2	L	M	X	Y	Z	1	2
10	100	L	M	X	Y	Z	1	2
12	120		M	X	Y	Z	1	2
15	150		M	X	Y	Z	1	2
18	180		M	X	Y	Z	1	2
22	220		M	X	Y	Z	1	2
27	270		M	X	Y	Z	1	2
33	330		M	X	Y	Z	1	2
39	390			X	Y	Z	1	2
47	470			X	Y	Z	1	2
56	560				Y	Z	1	2
68	680				Y	Z	1	2
82	820				Y	Z	1	2
100	101				Y	Z	1	2
120	121				Y	Z	1	2
150	151					Z	1	2
180	181					Z	1	2
220	221						1	2
270	271						1	2
330	331						1	2
390	391						1	2
470	471						1	2
560	561						1	2
1000	102							2

Note

1. Consult factory for 0.1 pF through 0.7 pF

**ELECTRICAL SPECIFICATIONS¹**


CAPACITANCE (pF) AT 1 MHz	TOLERANCE CODE**	SRF (GHz) TYP.	Ceff TYP.	Q	Ceff TYP.	Q	Ceff TYP.	Q	Ceff TYP.	Q	Ceff TYP.	Q
			200 MHz		500 MHz		1000 MHz		2000 MHz		2500 MHz	
0.8	A,B,C	26.4	0.80	6813	0.80	1491	0.80	519	0.80	174	0.81	124
0.9	A,B,C											
1.0	A,B,C	23.6	1.00	5826	1.00	1275	1.00	443	1.01	148	1.01	105
1.2	A,B,C	21.5	1.20	5232	1.20	1145	1.20	398	1.21	133	1.22	95
1.5	A,B,C	19.2	1.50	4724	1.50	1033	1.50	359	1.52	120	1.53	85
1.8	A,B,C	17.6	1.80	4465	1.80	977	1.81	339	1.82	113	1.84	80
2.2	A,B,C	15.9	2.20	3947	2.20	863	2.21	300	2.24	100	2.26	70
2.7	A,B,C	14.3	2.70	3480	2.70	761	2.71	264	2.75	88	2.78	62
3.3	A,B,C	13.0	3.30	4157	3.30	909	3.32	315	3.38	104	3.43	73
3.9	A,B,C	11.9	3.90	3517	3.91	769	3.93	266	4.01	88	4.08	62
4.7	A,B,C	10.9	4.70	2918	4.71	638	4.74	221	4.86	72	4.96	51
5.6	A,B,C	10.0	5.60	2449	5.61	535	5.66	185	5.84	60	5.98	42
6.8	A,B,C	9.0	6.80	2017	6.82	440	6.88	152	7.15	49	7.36	34
8.2	A,B,C	8.2	8.20	1672	8.23	365	8.32	126	8.71	40	9.03	28
10	F,G,J	7.5	10.0	1371	10.0	299	10.2	103	10.8	33	11.3	22
12	F,G,J	6.8	12.0	1142	12.1	249	12.3	85	13.1	27	13.9	18
15	F,G,J	6.1	15.0	914	15.1	199	15.4	68	16.8	21	18.0	14
18	F,G,J	5.6	18.0	761	18.1	165	18.6	56	20.7	17	22.6	11
22	F,G,J	5.0	22.0	623	22.2	135	22.9	46	26.1	13	29.2	9
27	F,G,J	4.5	27.1	507	27.3	110	28.4	37	33.5	11	38.8	6
33	F,G,J	4.1	33.1	415	33.5	90	35.1	30	43.3	8	52.5	5
39	F,G,J	3.8	39.1	351	39.7	76	41.9	25	54.2	6	69.5	4
47	F,G,J	3.4	47.2	291	48.0	63	51.3	20	71.0	5	99.7	3
56	F,G,J	3.1	56.2	244	57.4	52	62.3	17	93.8	4	151.4	2
68	F,G,J	2.9	68.2	201	70.1	43	77.5	13	133.2	3	289.5	1
82	F,G,J	2.6	82.5	166	85.1	35	96.2	11	200.2	2		
100	F,G,J	2.4	100.7	136	104.7	29	122.0	9	357.3	1		
120	F,G,J	2.2	121.0	113	126.9	24	153.1	7				
150	F,G,J	1.9	151.6	90	160.9	19	205.5	5				
180	F,G,J	1.8	182.4	75	195.9	15	266.7	4				
220	F,G,J	1.6	223.5	61	244.2	12	364.3	3				
270	F,G,J	1.4	275.4	50	307.3	10	525.4	2				
330	F,G,J	1.3	338.0	41	387.6	8	812.9	1				
390	F,G,J	1.2	401.3	34	473.0	6	1309.1	1				
470	F,G,J	1.1	486.5	28	596.1	5						
560	F,G,J	1.0	583.5	24	748.7	4						
1000	K											

2. 1. Additional non-standard values available on request


**A = ± 0.05 ; B = ± 0.10 ; C = ± 0.25 ; F = $\pm 1\%$; G = $\pm 2\%$; J = $\pm 5\%$; K = 10%




SRF VS. CAPACITANCE (TYPICAL)



ESR VS. FREQUENCY (TYPICAL)



Q VS. FREQUENCY (TYPICAL)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[HPC0603A220FXMT1](#) [HPC0603A1R5BXMT1](#) [HPC0603A6R8BXMT1](#) [HPC0603A180FXMT1](#) [HPC0603A1R0AXMT1](#)
[HPC0603A470FXMT1](#) [HPC0603A120FXMT1](#) [HPC0603A150FXMT1](#) [HPC0603A100FXMT1](#) [HPC0603A1R2BXMT1](#)
[HPC0603A2R2BXMT1](#) [HPC0603A8R2BXMT1](#) [HPC0603A2R4BXMT1](#) [HPC0603A0R8AWMT1](#)
[HPC0603A1R0AWMT1](#) [HPC0603A1R1AWMT1](#) [HPC0603A1R2BWMT1](#) [HPC0603A1R5BWMT1](#)
[HPC0603A2R0BWMT1](#) [HPC0603A2R4BWMT1](#) [HPC0603A3R0BWMT1](#) [HPC0603A3R9BWMT1](#)
[HPC0603A220FWMT1](#) [HPC0603A470FWMT1](#) [HPC0603A101GWYT1](#) [HPC0603A5R6BXMT1](#) [HPC0603A3R3AXMT1](#)
[HPC0603A101GXYT1](#) [HPC0603A4R7BXMT1](#) [HPC0603A2R7BXMT1](#) [HPC0603A0R8AXMT1](#) [HPC0603A1R8AXMT1](#)
[HPC0603A2R0BXMT1](#) [HPC0603A3R0BXMT1](#) [HPC0603A1R1AXMT1](#) [HPC0603A0R2AXMT1](#)
[HPC0603A0R3AXMT1](#) [HPC0603A0R4BXMT1](#) [HPC0603A0R5BXMT1](#) [HPC0603A101FWYT1](#) [HPC0603A471JX1T1](#)