

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

ACTUATOR-SWITCH

CATALOG LISTING

JV-311

JV-311

M

DRAWING
NUMBER

3

ISSUE

RELEASE NO. PR-11675-T REPLACES X76225-JV

CHECK

REVISIONS

A PRI11675
TSK
11 NOV 82

CHECK

12 NOV 82

12 NOV 82

12 NOV 82

12 NOV 82


12 NOV 82

12 NOV 82

12 NOV 82

FO-52848-A

DRAWN




NOTES

- 1 REVERSE ACTUATION ACTUATOR (V3-601 BASIC NOT FURNISHED)
- 2 1.050 REF FREE POSITION WITH BASIC SWITCH PLUNGER FULLY OVERTRAVELED A MINIMUM RETURN FORCE OF .5 OZ REQUIRED UPWARD AT THE .75 RADIUS BY AN EXTERNAL RETURN FORCE MECHANISM
- 3 .170 APPROX TRAVEL DOWNWARD FROM THE 1.050 REF FREE POSITION TO OPERATE BASIC SWITCH
- 4 ACTUATOR WILL NOT NECESSARILY RELEASE TYPE V3-601 BASIC WITHOUT CUSTOMER ADJUSTMENT OF ACTUATOR LEVER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

ELECTRICAL DATA

SCALE FULL

CONTACT ARRANGEMENT

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04	X	0.01/0.03
ONE PLACE	X,X	0.4/.016	X,X	0.004/0.016
TWO PLACES	X,X,X	0.16/.008	X,X,X	0.001/0.008
THREE PLACES	X,X,X,X		X,X,X,X	
ANGLES				

± 2°

US CUSTOMARY

DESIGN UNITS

WEIGHT .013 LB MAX