

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	00		A2	REVISED PER ECO-12-011861	28JUN2012	KH

- 1

HOUSING: LCP, UL94V-0, BLACK.
CONTACT: PHOSPHOR BRONZE.
POST: BRASS WIRE.
- 2





CONTACT: 0.76 μm GOLD PER ASTM B 488 IN CONTACT AREA,
1.27 μm MIN TIN-LEAD
ON PCB TAIL,
OVER 1.27μm MIN NICKEL PER
SAE AMS-QQ-N-290 OVER ALL.
POST:1.27 μm MIN NICKEL.
- 3

PLATED THROUGH HOLE PER 114-13056,
FIGURE 4.
- 4

CONTACT: 0.76 μm GOLD PER ASTM B 488 IN CONTACT AREA,
1.27 μm MIN MATTE TIN PER ASTM B 545
ON PCB TAIL,
OVER 1.27 μm MIN NICKEL PER
SAE AMS-QQ-N-290 OVER ALL.
POST:1.27 μm MIN NICKEL.
- 5

NOTE DELETED.
- 6

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



6	OBSOLETE	4	DIFFERENTIAL, NONSEQUENTIAL	1410233-4
		4	SINGLE END, NONSEQUENTIAL	1410233-3
6	OBSOLETE	2	DIFFERENTIAL, NONSEQUENTIAL	1410233-2
		2	SINGLE END, NONSEQUENTIAL	1410233-1
		FINISH	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.E. CONNER CHK D. DEFIBAUGH APVD F.P. MORANA	01OCT2001 23OCT2001 23OCT2001
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ±0.013 4 PLC ± ANGLES ±1°	
MATERIAL		FINISH	
1		2 4	
CUSTOMER DRAWING		WEIGHT	
		SIZE	
		A100779	
		DRAWING NO	
		114-13056	
		RESTRICTED TO	
		A100779	
		SCALE	
		8:1	
		SHEET	
		1	
		REV	
		A2	