

## Relay Module - RIF-2-RSC-LDP-125DC/4X21 - 2903319

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Pre-assembled relay module with screw connection, consisting of: relay base, power contact relay, and retaining bracket. Contact type: 4 changeover contacts. Input voltage: 125 V DC

RoHS

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 10 pc                                                                                                   |
| GTIN         | <br>4 046356 732215 |
| GTIN         | 4046356732215                                                                                           |

### Technical data

#### Note

|                         |                                                                           |
|-------------------------|---------------------------------------------------------------------------|
| Utilization restriction | EMC: class A product, see manufacturer's declaration in the download area |
|-------------------------|---------------------------------------------------------------------------|

#### Dimensions

|        |       |
|--------|-------|
| Width  | 27 mm |
| Height | 89 mm |
| Depth  | 75 mm |

#### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Ambient temperature (operation)         | -40 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

#### Coil side

|                                           |             |
|-------------------------------------------|-------------|
| Nominal input voltage $U_N$               | 125 V DC    |
| Input voltage range in reference to $U_N$ | see diagram |
| Typical input current at $U_N$            | 7.5 mA      |
| Typical response time                     | 13 ms       |
| Typical release time                      | 14 ms       |
| Coil voltage                              | 125 V DC    |

# Relay Module - RIF-2-RSC-LDP-125DC/4X21 - 2903319

## Technical data

### Coil side

|                           |               |
|---------------------------|---------------|
| Protective circuit        | Damping diode |
| Operating voltage display | Yellow LED    |

### Contact side

|                                       |                           |
|---------------------------------------|---------------------------|
| Contact type                          | 4 PDTs                    |
| Type of switch contact                | Single contact            |
| Contact material                      | AgNi                      |
| Maximum switching voltage             | 250 V AC/DC               |
| Minimum switching voltage             | 5 V (At 24 mA)            |
| Min. switching current                | 5 mA (at 24 V)            |
| Maximum inrush current                | 16 A (20 ms, N/O contact) |
| Limiting continuous current           | 6 A (see diagram)         |
| Interrupting rating (ohmic load) max. | 144 W (at 24 V DC)        |
|                                       | 124 W (at 48 V DC)        |
|                                       | 108 W (at 60 V DC)        |
|                                       | 52 W (at 110 V DC)        |
|                                       | 48 W (at 220 V DC)        |
|                                       | 1500 VA (for 250 V AC)    |
| Switching capacity                    | 2 A (at 24 V, DC13)       |
|                                       | 0.22 A (at 120 V, DC13)   |
|                                       | 0.11 A (at 250 V, DC13)   |
|                                       | 1.5 A (at 24 V, AC15)     |
|                                       | 1.5 A (at 120 V, AC15)    |
|                                       | 1 A (at 240 V, AC15)      |

### Connection data input side

|                                                                         |                                                                                |
|-------------------------------------------------------------------------|--------------------------------------------------------------------------------|
| Connection name                                                         | Input side                                                                     |
| Connection method                                                       | Screw connection                                                               |
| Stripping length                                                        | 8 mm                                                                           |
| Conductor cross section solid                                           | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>                                      |
| Conductor cross-section solid (2 conductors with same cross section)    | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                    |
| Conductor cross section flexible                                        | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>                                      |
|                                                                         | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> (Ferrule with plastic sleeve)        |
| Conductor cross section flexible (2 conductors with same cross section) | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                    |
|                                                                         | 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (TWIN ferrule with plastic sleeve) |
| Conductor cross section AWG                                             | 20 ... 10 (solid)                                                              |
|                                                                         | 20 ... 12 (flexible)                                                           |
| Torque                                                                  | 0.5 Nm ... 0.6 Nm                                                              |

### Connection data output side

|                   |                  |
|-------------------|------------------|
| Connection name   | Contact side     |
| Connection method | Screw connection |

# Relay Module - RIF-2-RSC-LDP-125DC/4X21 - 2903319

## Technical data

### Connection data output side

|                                                                         |                                                                                |
|-------------------------------------------------------------------------|--------------------------------------------------------------------------------|
| Stripping length                                                        | 8 mm                                                                           |
| Conductor cross section solid                                           | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>                                      |
| Conductor cross-section solid (2 conductors with same cross section)    | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                    |
| Conductor cross section flexible                                        | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>                                      |
|                                                                         | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> (Ferrule with plastic sleeve)        |
| Conductor cross section flexible (2 conductors with same cross section) | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                    |
|                                                                         | 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (TWIN ferrule with plastic sleeve) |
| Conductor cross section AWG                                             | 20 ... 10 (solid)                                                              |
|                                                                         | 20 ... 12 (flexible)                                                           |
| Torque                                                                  | 0.5 Nm ... 0.6 Nm                                                              |

### General

|                                          |                                       |
|------------------------------------------|---------------------------------------|
| Test voltage relay winding/relay contact | 2.5 kV <sub>rms</sub> (50 Hz, 1 min.) |
| Test voltage PDT/PDT                     | 2 kV <sub>rms</sub> (50 Hz, 1 min.)   |
| Operating mode                           | 100% operating factor                 |
| Degree of protection                     | IP20 (Relay base)                     |
|                                          | RT I (Relay)                          |
| Mechanical service life                  | approx. 2x 10 <sup>7</sup> cycles     |
| Mounting position                        | any                                   |
| Assembly instructions                    | In rows with zero spacing             |

### Standards and Regulations

|                                        |                  |
|----------------------------------------|------------------|
| Standards/regulations                  | DIN EN 50178     |
| Rated insulation voltage               | 250 V AC         |
| Rated surge voltage                    | 2.5 kV           |
| Insulation                             | Basic insulation |
| Degree of pollution                    | 2                |
| Overvoltage category                   | II               |
| Flammability rating according to UL 94 | V2               |


### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| China RoHS | Environmentally Friendly Use Period = 50                                                            |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

## Drawings


## Relay Module - RIF-2-RSC-LDP-125DC/4X21 - 2903319

Circuit diagram




DC coils

Diagram




Contact derating

Diagram




Diagram




Operating voltage range

Diagram



Interrupting rating

Diagram



Electrical service life

Service life reduction factor

# Relay Module - RIF-2-RSC-LDP-125DC/4X21 - 2903319

## Articles in set

Relay base - RIF-2-BSC/4X21 - 2900932



RIF-2... relay base, for industrial relay with 2 or 4 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

Single relay - REL-IR4/LDP-125DC/4X21 - 2903681



Plug-in industrial relay with power contacts, 4 PDTs, test key, status LED, freewheeling diode, mechanical switch position indicator, polarity: A1+, A2-, coil voltage: 125 V DC

Retaining bracket - RIF-RH-2 - 2900954



Relay retaining bracket, with ejector function and holder for marking material, suitable for RIF-2 relay base, for industrial relay

## Approvals

### Approvals

Approvals

DNV GL / EAC

Ex Approvals

### Approval details

|        |                                                                                     |                          |
|--------|-------------------------------------------------------------------------------------|--------------------------|
| DNV GL | <a href="http://exchange.dnv.com/tari/">http://exchange.dnv.com/tari/</a>           | TAA000018V               |
| EAC    |  | RU C-<br>DE.A*30.B.01082 |

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>