





RECOMMEND P.C.B. LAYOUT







CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION			
POS. 1	POS. 2	POS. 3	
DN	NONE	DN	
2-1	N/A	2-3	

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0 ± 0.4
 0.00 ± 0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 0.4(VA) max. @20 max. (AC or DC)
5. TRAVEL TO MAKE: 2.16 [.085]
6. ELECTRICAL LIFE: 30,000 ACUTATIONS AT FULL LOAD
7. INSULATION RESISTNACE: 1,000 mega-ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sed level
9. OPERATING TEMP.: -30°C to 85°C



E-SWITCH®

TITLE

500SSP1S2M6REA

SCALE

2:1

DATE

7/18/00

DR

MM

DWG

TS11035

REV

B

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED