



Electrical Characteristics

Nominal Impedance:	50 ohms
Frequency Range:	DC to 4 GHz
VSWR:	1.3:1 maximum
Insertion Loss:	0.2 dB at 3 GHz
Operating Voltage (rms):	500 V maximum at sea level
Dielectric Withstand Voltage (rms):	1500 V maximum at sea level
Contact Resistance:	1.5 milliohms maximum
Insulation Resistance:	5000 megohms minimum


Mechanical Characteristics

Mating Cycles:	500 cycles minimum
Interface Dimensions:	Conform to MIL-C-39012

Environmental Characteristics

Temperature Range:	-65 °C to +165 °C
--------------------	-------------------

PART	DESCRIPTION
1	Body
2	Ferrule
3	Contact
4	Dielectric
5	Solder Tag
6	Nut
7	Washer



Update on Solder Tag	JT	5	26 April '10
Update Dims	MS	4	7 Jan 09
Altered address	KA	3	15 Aug 07
CAD Issue	SN	2	02 May 02
First Issue	CBB	1	16 July 99
DESCRIPTION OF REVISION	APPVD	ISS	DATE

PART NUMBER:

VB60-2051

BNC Crimp Panel Mount Jack
(front entry) for RG58

SCALE: Not To Scale

DIMENSIONS: mm

TOLERANCES:

± 0.2mm unless
otherwise stated

DRAWN BY:

S Nash

CHECKED BY:

S Nash

APPROVED BY:

P D Couzens

DATE:

03 May 02



Connectivity Solutions

7-13 Russel Way,
Widford Industrial Estate,
Chelmsford, Essex,
CM1 3AA, UK.

Tel: +44 (0) 1245 359515

Fax: +44 (0) 1245 359388

EMERSON™
Network Power